

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905816

Luminaire Tested: DFN2DIP-PN3F0-080D030US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905816
REPORT IS A COMBINATION OF REPORTS P899521 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D030US835-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10575.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905816
CATALOG NUMBER: DFN2DIP-PN3F0-080D030US835-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P905816
 CATALOG NUMBER: DFN2DIP-PN3F0-080D030US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	79	79	79	75
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67	67	67	67	63
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56	56	56	56	53
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	48	48	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	41	41	41	38
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	36	36	36	33
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32	32	32	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	28	28	28	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	25	25	25	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	23	23	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3639	3639	3639
5°	3642	3586	3611
10°	3611	3535	3560
15°	3556	3474	3482
20°	3482	3391	3403
25°	3408	3291	3311
30°	3316	3199	3194
35°	3229	3090	3071
40°	3123	2980	2954
45°	3016	2870	2834
50°	2899	2754	2695
55°	2777	2620	2567
60°	2638	2461	2420
65°	2487	2296	2247
70°	2294	2095	2060
75°	2027	1854	1885
80°	1705	1546	1555
85°	1203	1023	1014

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3016 cd/sqm



TEST NUMBER: P905816

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	2.8
10°-20°	824.3	7.8
20°-30°	1211.5	11.5
30°-40°	1407.0	13.3
40°-50°	1405.3	13.3
50°-60°	1225.4	11.6
60°-70°	905.8	8.6
70°-80°	512.5	4.8
80°-90°	138.0	1.3
90°-100°	58.7	0.6
100°-110°	186.5	1.8
110°-120°	319.2	3.0
120°-130°	419.8	4.0
130°-140°	471.2	4.5
140°-150°	462.1	4.4
150°-160°	387.7	3.7
160°-170°	257.1	2.4
170°-180°	89.9	0.8
0°-30°	2328.8	22.0
0°-40°	3735.8	35.3
0°-60°	6366.4	60.2
0°-90°	7922.7	74.9
90°-120°	564.5	5.3
90°-150°	1917.7	18.1
90°-180°	2652.0	25.1
0°-180°	10575.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	137
90°	1	10	28	26	27	10
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	



TEST NUMBER: P905816

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P905816

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8



TEST NUMBER: P905816
 CATALOG NUMBER: DFN2DIP-PN3F0-080D030US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.76	14.90	14.47	15.63	16.49	13.32	14.46	14.03	15.19	16.06
	3H	15.43	16.46	16.16	17.20	18.10	14.95	15.98	15.67	16.72	17.61
	4H	16.03	17.00	16.77	17.75	18.66	15.55	16.51	16.29	17.26	18.17
	6H	16.44	17.33	17.19	18.09	19.02	15.95	16.84	16.70	17.60	18.53
	8H	16.55	17.40	17.32	18.18	19.11	16.06	16.91	16.82	17.69	18.61
	12H	16.61	17.42	17.38	18.19	19.14	16.11	16.92	16.88	17.69	18.65
4H	2H	14.25	15.22	15.00	15.97	16.88	13.90	14.87	14.64	15.62	16.53
	3H	16.13	16.94	16.89	17.73	18.65	15.73	16.54	16.49	17.33	18.25
	4H	16.85	17.59	17.63	18.38	19.33	16.44	17.17	17.21	17.96	18.91
	6H	17.38	18.02	18.17	18.83	19.79	16.96	17.59	17.75	18.40	19.37
	8H	17.53	18.13	18.33	18.93	19.91	17.11	17.70	17.90	18.51	19.48
	12H	17.62	18.15	18.43	18.98	19.96	17.18	17.72	17.99	18.54	19.52
8H	4H	17.07	17.67	17.86	18.47	19.45	16.70	17.30	17.49	18.10	19.08
	6H	17.71	18.20	18.53	19.05	20.02	17.33	17.82	18.15	18.67	19.65
	8H	17.92	18.36	18.76	19.21	20.20	17.54	17.98	18.38	18.83	19.82
	12H	18.06	18.45	18.90	19.29	20.34	17.66	18.05	18.50	18.89	19.94
12H	4H	17.07	17.60	17.88	18.43	19.41	16.71	17.24	17.52	18.07	19.05
	6H	17.74	18.18	18.57	19.02	20.01	17.37	17.81	18.21	18.66	19.65
	8H	17.99	18.37	18.82	19.21	20.26	17.61	18.00	18.45	18.84	19.89