

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924951

Luminaire Tested: DFN2DIP-PN3F0-090D050US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924951
REPORT IS A COMBINATION OF REPORTS P901072 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D050US950-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12020.4 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 130.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924951

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924951

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4148	4148	4148
5°	4152	4080	4107
10°	4109	3997	3971
15°	4050	3862	3763
20°	3973	3677	3508
25°	3893	3470	3262
30°	3788	3259	2951
35°	3684	3031	2677
40°	3579	2797	2364
45°	3457	2536	2080
50°	3330	2274	1802
55°	3197	1994	1536
60°	3044	1702	1263
65°	2867	1405	1135
70°	2653	1128	1024
75°	2383	988	928
80°	1992	820	799
85°	1353	534	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3457 cd/sqm

TEST NUMBER: P924951

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.6	2.8
10°-20°	913.0	7.6
20°-30°	1281.8	10.7
30°-40°	1397.3	11.6
40°-50°	1284.2	10.7
50°-60°	1008.6	8.4
60°-70°	656.5	5.5
70°-80°	337.9	2.8
80°-90°	89.1	0.7
90°-100°	53.1	0.4
100°-110°	197.9	1.6
110°-120°	524.8	4.4
120°-130°	870.4	7.2
130°-140°	924.6	7.7
140°-150°	859.3	7.1
150°-160°	690.9	5.7
160°-170°	445.2	3.7
170°-180°	153.2	1.3
0°-30°	2527.4	21.0
0°-40°	3924.6	32.6
0°-60°	6217.4	51.7
0°-90°	7301.0	60.7
90°-120°	775.8	6.5
90°-150°	3430.2	28.5
90°-180°	4719.0	39.3
0°-180°	12020.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	1	14	23	29	31	11
95°	76	37	45	51	50	90
105°	354	389	71	84	88	378
115°	670	690	719	179	96	659
125°	947	962	984	992	996	845
135°	1172	1191	1201	1213	1210	905
145°	1359	1358	1378	1386	1380	850
155°	1497	1486	1500	1507	1498	690
165°	1577	1570	1574	1582	1574	446
175°	1613	1605	1608	1616	1604	154
180°	1610	1610	1610	1610	1610	

TEST NUMBER: P924951

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	1.1	13.9	23.3	29.2	31.4
92.5°	29.2	24.5	28.0	30.3	31.4
95°	75.7	37.2	45.4	51.3	50.1
97.5°	136.2	40.8	59.3	63.0	64.0
100°	206.3	46.7	66.4	75.7	78.0
102.5°	283.1	280.8	68.8	81.5	85.1
105°	354.1	389.1	71.1	83.9	88.5
107.5°	436.8	465.8	73.5	86.1	90.9
110°	516.1	540.4	203.9	87.4	92.0



TEST NUMBER: P924951

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.6	611.5	591.8	89.7	93.2
115°	669.8	689.6	718.7	179.4	95.6
117.5°	738.5	761.8	781.7	614.9	309.9
120°	815.4	832.8	853.8	867.9	710.5
122.5°	880.5	899.2	922.6	929.6	930.8
125°	946.9	962.2	984.3	992.4	996.0
127.5°	1007.5	1023.8	1041.5	1053.0	1054.2
130°	1064.7	1083.4	1096.1	1108.9	1107.9
132.5°	1123.0	1138.1	1150.8	1161.4	1160.3
135°	1171.9	1190.6	1200.9	1212.7	1210.3
137.5°	1223.0	1237.1	1248.8	1260.4	1257.0
140°	1273.1	1282.6	1295.2	1305.7	1300.0
142.5°	1315.2	1323.4	1338.5	1347.7	1341.9
145°	1359.4	1358.2	1378.0	1386.2	1380.3
147.5°	1397.8	1394.3	1414.1	1419.9	1415.4
150°	1435.1	1427.0	1445.6	1452.6	1446.7
152.5°	1466.5	1457.2	1474.7	1481.8	1473.5
155°	1496.8	1486.4	1500.4	1507.3	1498.1
157.5°	1521.2	1512.0	1522.5	1530.7	1521.2
160°	1542.3	1535.3	1542.3	1549.2	1541.1
162.5°	1560.8	1554.0	1559.7	1567.9	1557.4
165°	1577.2	1570.3	1573.7	1581.8	1573.7
167.5°	1590.0	1583.0	1586.6	1594.7	1584.2
170°	1600.5	1593.5	1595.9	1604.0	1593.5
172.5°	1607.5	1600.5	1602.9	1611.0	1600.5
175°	1613.3	1605.1	1607.5	1615.6	1604.0
177.5°	1615.6	1607.5	1608.7	1616.8	1606.3
180°	1609.8	1609.8	1609.8	1609.8	1609.8

TEST NUMBER: P924951

CATALOG NUMBER: DFN2DIP-PN3F0-090D050US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.00	13.92	13.87	14.81	15.92	8.96	9.89	9.83	10.77	11.89
	3H	14.68	15.51	15.56	16.40	17.54	10.15	10.98	11.03	11.88	13.01
	4H	15.29	16.07	16.18	16.97	18.12	10.61	11.39	11.50	12.28	13.43
	6H	15.71	16.43	16.61	17.33	18.49	10.93	11.65	11.83	12.55	13.71
	8H	15.83	16.52	16.75	17.44	18.60	11.02	11.70	11.93	12.62	13.78
	12H	15.90	16.55	16.82	17.46	18.65	11.06	11.71	11.98	12.63	13.81
4H	2H	13.03	13.81	13.93	14.71	15.86	9.57	10.35	10.47	11.25	12.40
	3H	14.86	15.51	15.77	16.44	17.60	10.92	11.57	11.83	12.50	13.66
	4H	15.55	16.14	16.47	17.07	18.25	11.47	12.06	12.39	12.98	14.17
	6H	16.06	16.57	17.00	17.52	18.71	11.89	12.39	12.82	13.34	14.53
	8H	16.24	16.71	17.17	17.66	18.86	12.01	12.49	12.95	13.43	14.63
	12H	16.33	16.76	17.29	17.72	18.93	12.08	12.51	13.03	13.47	14.68
8H	4H	15.52	16.00	16.46	16.94	18.14	11.75	12.23	12.69	13.17	14.37
	6H	16.09	16.48	17.05	17.46	18.67	12.26	12.66	13.23	13.64	14.84
	8H	16.30	16.64	17.27	17.62	18.84	12.45	12.80	13.42	13.77	14.99
	12H	16.44	16.74	17.41	17.71	18.98	12.57	12.88	13.54	13.84	15.11
12H	4H	15.48	15.91	16.43	16.87	18.08	11.76	12.19	12.71	13.15	14.36
	6H	16.06	16.41	17.03	17.38	18.60	12.31	12.66	13.28	13.63	14.85
	8H	16.28	16.59	17.26	17.55	18.82	12.52	12.83	13.50	13.80	15.06

END OF REPORT