

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924963

Luminaire Tested: DFN2DIP-PN3F0-090D080US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924963
REPORT IS A COMBINATION OF REPORTS P901114 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D080US950-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14853.8 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 154.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924963
CATALOG NUMBER: DFN2DIP-PN3F0-090D080US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P924963
 CATALOG NUMBER: DFN2DIP-PN3F0-090D080US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41	36
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27	24
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4148	4148	4148
5°	4152	4080	4107
10°	4109	3997	3971
15°	4050	3862	3763
20°	3973	3677	3508
25°	3893	3470	3262
30°	3788	3259	2951
35°	3684	3031	2677
40°	3579	2797	2364
45°	3457	2536	2080
50°	3330	2274	1802
55°	3197	1994	1536
60°	3044	1702	1263
65°	2867	1405	1135
70°	2653	1128	1024
75°	2383	988	928
80°	1992	820	799
85°	1353	534	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3457 cd/sqm



TEST NUMBER: P924963

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.6	2.2
10°-20°	913.0	6.1
20°-30°	1281.8	8.6
30°-40°	1397.3	9.4
40°-50°	1284.2	8.6
50°-60°	1008.6	6.8
60°-70°	656.5	4.4
70°-80°	337.9	2.3
80°-90°	90.8	0.6
90°-100°	84.9	0.6
100°-110°	316.6	2.1
110°-120°	839.7	5.7
120°-130°	1392.7	9.4
130°-140°	1479.4	10.0
140°-150°	1374.9	9.3
150°-160°	1105.4	7.4
160°-170°	712.3	4.8
170°-180°	245.2	1.7
0°-30°	2527.4	17.0
0°-40°	3924.6	26.4
0°-60°	6217.4	41.9
0°-90°	7302.7	49.2
90°-120°	1241.3	8.4
90°-150°	5488.3	36.9
90°-180°	7551.0	50.8
0°-180°	14853.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	2	22	37	47	50	14
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P924963

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P924963

CATALOG NUMBER: DFN2DIP-PN3F0-090D080US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P924963
 CATALOG NUMBER: DFN2DIP-PN3F0-090D080US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.97	12.80	12.94	13.78	15.06	7.94	8.76	8.91	9.74	11.03
	3H	13.64	14.38	14.63	15.37	16.68	9.12	9.86	10.10	10.85	12.15
	4H	14.25	14.94	15.24	15.94	17.25	9.57	10.26	10.56	11.26	12.57
	6H	14.66	15.30	15.67	16.30	17.63	9.88	10.52	10.89	11.52	12.85
	8H	14.79	15.40	15.80	16.41	17.74	9.97	10.58	10.98	11.59	12.92
	12H	14.85	15.43	15.86	16.43	17.78	10.01	10.59	11.03	11.60	12.95
4H	2H	11.99	12.68	12.99	13.68	14.99	8.53	9.23	9.53	10.22	11.54
	3H	13.81	14.39	14.82	15.41	16.74	9.87	10.45	10.88	11.47	12.80
	4H	14.50	15.03	15.51	16.04	17.39	10.41	10.94	11.43	11.96	13.31
	6H	15.01	15.46	16.03	16.50	17.85	10.83	11.28	11.86	12.32	13.67
	8H	15.18	15.60	16.21	16.63	18.00	10.95	11.38	11.98	12.41	13.77
	12H	15.27	15.65	16.32	16.70	18.07	11.01	11.40	12.06	12.44	13.81
8H	4H	14.46	14.89	15.49	15.92	17.28	10.69	11.11	11.72	12.15	13.51
	6H	15.02	15.37	16.08	16.44	17.81	11.20	11.55	12.25	12.62	13.99
	8H	15.23	15.54	16.30	16.60	17.98	11.39	11.70	12.45	12.75	14.13
	12H	15.37	15.64	16.43	16.69	18.11	11.50	11.77	12.57	12.82	14.25
12H	4H	14.41	14.80	15.46	15.84	17.21	10.69	11.08	11.74	12.12	13.49
	6H	15.00	15.30	16.06	16.36	17.74	11.25	11.56	12.31	12.61	14.00
	8H	15.21	15.48	16.28	16.54	17.96	11.45	11.72	12.52	12.78	14.20