

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908410

Luminaire Tested: DFN2DIP-PN3F0-030D040US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908410
REPORT IS A COMBINATION OF REPORTS P899526 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D040US840-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6150.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 53.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908410

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908410

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1464	1464	1464
5°	1465	1439	1449
10°	1450	1410	1401
15°	1429	1363	1328
20°	1402	1297	1238
25°	1374	1225	1151
30°	1337	1150	1041
35°	1300	1070	945
40°	1263	987	834
45°	1220	895	734
50°	1175	802	636
55°	1128	704	542
60°	1074	601	446
65°	1012	496	400
70°	936	398	361
75°	840	349	327
80°	703	289	282
85°	478	188	208

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1266 cd/sqm

TEST NUMBER: P908410

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	1.9
10°-20°	322.1	5.2
20°-30°	452.3	7.4
30°-40°	493.0	8.0
40°-50°	453.1	7.4
50°-60°	355.9	5.8
60°-70°	231.6	3.8
70°-80°	119.2	1.9
80°-90°	34.1	0.6
90°-100°	79.1	1.3
100°-110°	251.2	4.1
110°-120°	429.8	7.0
120°-130°	565.3	9.2
130°-140°	634.5	10.3
140°-150°	622.2	10.1
150°-160°	522.0	8.5
160°-170°	346.2	5.6
170°-180°	121.0	2.0
0°-30°	891.8	14.5
0°-40°	1384.8	22.5
0°-60°	2193.8	35.7
0°-90°	2578.7	41.9
90°-120°	760.1	12.4
90°-150°	2582.2	42.0
90°-180°	3571.0	58.1
0°-180°	6150.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	14	38	35	37	6
95°	56	67	69	69	67	63
105°	232	235	237	239	239	245
115°	431	438	436	434	431	427
125°	627	637	634	630	629	561
135°	812	823	826	825	822	627
145°	985	993	999	1000	996	616
155°	1126	1130	1133	1138	1135	519
165°	1226	1224	1224	1232	1227	346
175°	1275	1272	1270	1278	1271	121
180°	1278	1278	1278	1278	1278	

TEST NUMBER: P908410

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	1.1	13.8	37.8	35.4	36.6
92.5°	23.8	32.3	33.5	34.6	34.6
95°	56.2	67.1	69.0	69.0	67.1
97.5°	93.6	103.6	107.9	107.9	107.9
100°	136.7	145.6	148.7	148.7	147.5
102.5°	182.2	188.7	193.0	194.1	193.0
105°	231.9	234.9	237.2	239.1	239.1
107.5°	281.1	285.8	285.8	286.5	281.1
110°	328.9	335.1	335.1	335.1	332.0

TEST NUMBER: P908410

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	380.5	387.1	385.9	382.8	380.5
115°	431.3	437.6	435.6	434.4	431.3
117.5°	481.8	490.3	484.9	481.8	478.8
120°	532.7	541.1	532.7	532.7	529.2
122.5°	578.9	589.7	584.3	581.2	578.9
125°	627.4	637.0	634.0	630.5	629.3
127.5°	674.8	686.7	682.5	677.8	674.8
130°	719.0	733.0	731.0	728.7	724.5
132.5°	768.7	779.5	780.3	774.9	771.8
135°	811.5	823.4	825.8	824.6	821.5
137.5°	859.3	868.9	870.8	870.0	865.5
140°	901.2	910.9	916.3	916.3	912.0
142.5°	944.4	954.0	957.0	958.3	954.0
145°	985.2	992.9	999.1	1000.3	996.0
147.5°	1021.8	1031.4	1036.0	1037.9	1033.7
150°	1059.6	1066.1	1070.4	1073.8	1070.4
152.5°	1093.1	1099.5	1105.0	1109.2	1105.0
155°	1126.5	1129.6	1133.1	1138.5	1135.0
157.5°	1155.5	1157.7	1159.6	1167.4	1162.0
160°	1181.2	1183.6	1184.7	1191.2	1186.6
162.5°	1205.1	1205.1	1206.3	1213.6	1208.2
165°	1225.6	1224.4	1224.4	1232.0	1226.7
167.5°	1244.1	1240.5	1240.5	1248.3	1242.8
170°	1257.9	1254.8	1253.6	1261.3	1254.8
172.5°	1267.5	1264.5	1263.2	1271.0	1264.5
175°	1275.3	1272.1	1269.8	1277.5	1271.0
177.5°	1279.5	1276.4	1274.0	1280.6	1274.0
180°	1277.5	1277.5	1277.5	1277.5	1277.5

TEST NUMBER: P908410

CATALOG NUMBER: DFN2DIP-PN3F0-030D040US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.63	8.40	8.66	9.43	10.81	3.59	4.36	4.62	5.39	6.78
	3H	9.29	9.98	10.33	11.02	12.43	4.77	5.46	5.81	6.50	7.90
	4H	9.89	10.55	10.95	11.59	13.00	5.21	5.86	6.27	6.91	8.32
	6H	10.31	10.91	11.37	11.96	13.38	5.53	6.12	6.59	7.17	8.60
	8H	10.43	11.00	11.50	12.06	13.48	5.61	6.18	6.68	7.24	8.66
	12H	10.49	11.03	11.56	12.09	13.53	5.65	6.19	6.72	7.25	8.69
4H	2H	7.64	8.29	8.69	9.33	10.74	4.18	4.83	5.23	5.87	7.28
	3H	9.45	9.99	10.52	11.06	12.49	5.51	6.06	6.58	7.13	8.55
	4H	10.14	10.63	11.21	11.70	13.14	6.05	6.55	7.13	7.61	9.06
	6H	10.64	11.07	11.72	12.15	13.59	6.46	6.89	7.54	7.98	9.42
	8H	10.81	11.21	11.89	12.29	13.74	6.59	6.99	7.67	8.06	9.52
	12H	10.90	11.26	12.00	12.35	13.81	6.65	7.01	7.74	8.10	9.56
8H	4H	10.10	10.50	11.18	11.57	13.03	6.33	6.72	7.41	7.80	9.26
	6H	10.66	10.98	11.76	12.10	13.56	6.83	7.16	7.94	8.28	9.74
	8H	10.87	11.15	11.98	12.26	13.73	7.02	7.31	8.13	8.41	9.88
	12H	11.00	11.25	12.11	12.35	13.86	7.13	7.38	8.24	8.48	9.99
12H	4H	10.05	10.41	11.15	11.50	12.96	6.33	6.69	7.43	7.78	9.24
	6H	10.63	10.92	11.74	12.02	13.49	6.88	7.17	7.99	8.27	9.74
	8H	10.84	11.10	11.96	12.19	13.71	7.08	7.34	8.20	8.44	9.95