

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908428

Luminaire Tested: DFN2DIP-PN3F0-030D090US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908428
REPORT IS A COMBINATION OF REPORTS P899595 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D090US840-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11042.9 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908428
CATALOG NUMBER: DFN2DIP-PN3F0-030D090US840-FLLFLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P908428

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27				27
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30	23				23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19				19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21	16				16
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18	14				14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11				11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9				9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8				8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10	8				8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1378	1378	1378
5°	1379	1358	1367
10°	1367	1339	1348
15°	1347	1316	1319
20°	1319	1284	1288
25°	1291	1246	1254
30°	1256	1211	1210
35°	1223	1170	1163
40°	1183	1129	1119
45°	1142	1087	1073
50°	1098	1043	1021
55°	1052	992	972
60°	999	932	917
65°	942	870	851
70°	869	794	780
75°	768	702	714
80°	646	585	589
85°	456	387	384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2847 cd/sqm



TEST NUMBER: P908428

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.0
10°-20°	312.2	2.8
20°-30°	458.8	4.2
30°-40°	532.8	4.8
40°-50°	532.2	4.8
50°-60°	464.1	4.2
60°-70°	343.1	3.1
70°-80°	194.1	1.8
80°-90°	59.4	0.5
90°-100°	177.9	1.6
100°-110°	565.2	5.1
110°-120°	967.2	8.8
120°-130°	1272.0	11.5
130°-140°	1427.7	12.9
140°-150°	1400.0	12.7
150°-160°	1174.4	10.6
160°-170°	778.9	7.1
170°-180°	272.2	2.5
0°-30°	881.9	8.0
0°-40°	1414.7	12.8
0°-60°	2411.0	21.8
0°-90°	3007.5	27.2
90°-120°	1710.2	15.5
90°-150°	5809.9	52.6
90°-180°	8035.0	72.8
0°-180°	11042.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	3	31	85	80	82	11
95°	126	151	155	155	151	141
105°	522	529	534	538	538	551
115°	971	984	980	978	971	960
125°	1412	1433	1426	1419	1416	1261
135°	1826	1853	1858	1855	1848	1411
145°	2217	2234	2248	2250	2241	1385
155°	2535	2542	2550	2562	2554	1167
165°	2757	2755	2755	2772	2760	778
175°	2869	2862	2857	2874	2860	273
180°	2874	2874	2874	2874	2874	



TEST NUMBER: P908428

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	2.6	31.2	84.9	79.7	82.3
92.5°	53.7	72.8	75.4	78.0	78.0
95°	126.5	150.8	155.1	155.1	150.8
97.5°	210.6	233.1	242.7	242.7	242.7
100°	307.6	327.6	334.5	334.5	331.9
102.5°	409.9	424.6	434.1	436.8	434.1
105°	521.7	528.6	533.8	538.2	538.2
107.5°	632.6	643.0	643.0	644.7	632.6
110°	740.0	754.0	754.0	754.0	747.0



TEST NUMBER: P908428

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	856.2	870.9	868.3	861.4	856.2
115°	970.6	984.4	980.1	977.5	970.6
117.5°	1084.1	1103.2	1091.1	1084.1	1077.1
120°	1198.5	1217.5	1198.5	1198.5	1190.6
122.5°	1302.4	1326.8	1314.6	1307.7	1302.4
125°	1411.7	1433.3	1426.4	1418.6	1416.0
127.5°	1518.2	1545.1	1535.6	1525.2	1518.2
130°	1617.9	1649.1	1644.8	1639.5	1630.0
132.5°	1729.7	1753.9	1755.7	1743.5	1736.7
135°	1825.8	1852.7	1858.0	1855.3	1848.5
137.5°	1933.3	1955.0	1959.3	1957.6	1947.2
140°	2027.8	2049.4	2061.5	2061.5	2052.0
142.5°	2124.9	2146.5	2153.4	2156.1	2146.5
145°	2216.8	2234.0	2247.9	2250.5	2241.0
147.5°	2299.1	2320.7	2331.1	2335.4	2325.9
150°	2384.0	2398.7	2408.2	2416.0	2408.2
152.5°	2459.3	2474.1	2486.2	2495.8	2486.2
155°	2534.8	2541.6	2549.5	2561.6	2553.8
157.5°	2599.7	2604.9	2609.3	2626.6	2614.4
160°	2657.8	2663.0	2665.6	2680.3	2669.9
162.5°	2711.5	2711.5	2714.1	2730.6	2718.5
165°	2757.4	2754.8	2754.8	2772.2	2760.1
167.5°	2799.0	2791.3	2791.3	2808.5	2796.4
170°	2830.2	2823.3	2820.8	2838.0	2823.3
172.5°	2851.9	2845.0	2842.4	2859.7	2845.0
175°	2869.2	2862.3	2857.1	2874.5	2859.7
177.5°	2878.7	2871.9	2866.6	2881.3	2866.6
180°	2874.5	2874.5	2874.5	2874.5	2874.5



TEST NUMBER: P908428
 CATALOG NUMBER: DFN2DIP-PN3F0-030D090US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.74	6.42	6.87	7.55	9.11	5.30	5.99	6.43	7.11	8.67
	3H	7.38	7.99	8.52	9.13	10.70	6.89	7.51	8.03	8.64	10.22
	4H	7.95	8.54	9.10	9.67	11.25	7.47	8.05	8.62	9.18	10.77
	6H	8.34	8.88	9.50	10.01	11.61	7.85	8.39	9.01	9.52	11.12
	8H	8.44	8.95	9.60	10.10	11.69	7.95	8.46	9.11	9.61	11.20
	12H	8.48	8.96	9.64	10.11	11.72	7.98	8.47	9.14	9.61	11.22
4H	2H	6.17	6.76	7.33	7.89	9.47	5.82	6.41	6.98	7.54	9.12
	3H	8.02	8.50	9.18	9.66	11.26	7.61	8.10	8.77	9.26	10.86
	4H	8.72	9.17	9.88	10.31	11.93	8.30	8.75	9.46	9.90	11.51
	6H	9.22	9.60	10.39	10.77	12.38	8.79	9.18	9.96	10.35	11.95
	8H	9.36	9.72	10.53	10.88	12.50	8.93	9.29	10.10	10.45	12.07
	12H	9.42	9.75	10.61	10.92	12.55	8.98	9.31	10.17	10.48	12.11
8H	4H	8.90	9.26	10.06	10.42	12.04	8.53	8.89	9.69	10.05	11.67
	6H	9.51	9.81	10.70	11.01	12.63	9.14	9.43	10.32	10.64	12.25
	8H	9.73	9.99	10.92	11.17	12.81	9.34	9.60	10.54	10.78	12.42
	12H	9.85	10.07	11.04	11.25	12.92	9.45	9.67	10.64	10.85	12.52
12H	4H	8.87	9.20	10.06	10.37	12.00	8.51	8.84	9.69	10.01	11.63
	6H	9.54	9.80	10.73	10.98	12.62	9.18	9.43	10.37	10.61	12.25
	8H	9.77	10.00	10.96	11.17	12.84	9.40	9.62	10.59	10.80	12.47