

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908433

Luminaire Tested: DFN2DIP-PN3F0-040D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908433
REPORT IS A COMBINATION OF REPORTS P901033 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-040D030US840-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6998.4 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908433

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908433

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1839	1810	1823
10°	1823	1785	1798
15°	1795	1754	1758
20°	1758	1712	1718
25°	1721	1662	1672
30°	1674	1615	1613
35°	1631	1560	1551
40°	1577	1505	1491
45°	1523	1449	1431
50°	1464	1391	1361
55°	1402	1323	1296
60°	1332	1243	1222
65°	1256	1159	1135
70°	1158	1058	1040
75°	1024	936	952
80°	861	780	786
85°	607	516	512

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1523 cd/sqm

TEST NUMBER: P908433

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	2.1
10°-20°	416.2	5.9
20°-30°	611.7	8.7
30°-40°	710.5	10.2
40°-50°	709.6	10.1
50°-60°	618.7	8.8
60°-70°	457.4	6.5
70°-80°	258.8	3.7
80°-90°	70.1	1.0
90°-100°	33.7	0.5
100°-110°	125.7	1.8
110°-120°	333.3	4.8
120°-130°	552.9	7.9
130°-140°	587.3	8.4
140°-150°	545.8	7.8
150°-160°	438.8	6.3
160°-170°	282.8	4.0
170°-180°	97.3	1.4
0°-30°	1175.9	16.8
0°-40°	1886.3	27.0
0°-60°	3214.6	45.9
0°-90°	4000.8	57.2
90°-120°	492.7	7.0
90°-150°	2178.7	31.1
90°-180°	2998.0	42.8
0°-180°	6998.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1468	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	1	9	15	19	20	6
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	

TEST NUMBER: P908433

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.8	1571.8	1571.8	1571.8	1571.8
2.5°	1580.9	1573.4	1556.7	1571.8	1568.9
5°	1571.8	1565.8	1549.1	1561.2	1558.3
7.5°	1561.2	1552.2	1535.5	1547.7	1544.7
10°	1544.7	1534.1	1516.0	1528.0	1523.5
12.5°	1521.9	1512.9	1494.8	1502.4	1499.2
15°	1496.2	1487.2	1467.5	1473.6	1466.1
17.5°	1464.5	1455.5	1435.8	1443.3	1435.8
20°	1429.7	1420.7	1399.6	1404.0	1398.2
22.5°	1395.0	1381.4	1361.7	1361.7	1358.7
25°	1354.1	1342.1	1316.5	1319.4	1316.5
27.5°	1308.8	1298.2	1278.7	1274.1	1266.7
30°	1263.5	1251.4	1228.8	1224.3	1218.2
32.5°	1215.2	1206.2	1181.9	1172.9	1166.7
35°	1168.3	1153.3	1129.0	1119.9	1112.4
37.5°	1115.4	1101.8	1077.5	1067.0	1059.4
40°	1061.1	1048.8	1024.6	1011.2	1005.1
42.5°	1008.1	995.9	971.9	956.6	947.7
45°	950.7	940.2	917.4	900.9	894.7
47.5°	894.7	884.1	860.0	843.3	834.4
50°	835.8	828.2	807.1	785.9	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.3	674.1	666.6
57.5°	660.5	653.0	633.2	615.1	609.0
60°	601.5	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.5	503.3	497.3
65°	485.2	476.1	461.0	447.4	439.9
67.5°	424.7	417.1	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.7
75°	253.9	251.0	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.1
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5

TEST NUMBER: P908433

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5

TEST NUMBER: P908433

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.98	10.91	10.88	11.83	12.99	9.54	10.47	10.44	11.39	12.55
	3H	11.64	12.48	12.55	13.40	14.59	11.16	11.99	12.07	12.92	14.11
	4H	12.23	13.02	13.15	13.95	15.15	11.74	12.53	12.66	13.46	14.66
	6H	12.63	13.36	13.56	14.29	15.50	12.14	12.87	13.07	13.80	15.01
	8H	12.73	13.43	13.67	14.38	15.59	12.24	12.93	13.18	13.89	15.10
	12H	12.78	13.44	13.73	14.39	15.62	12.28	12.94	13.23	13.89	15.12
4H	2H	10.45	11.24	11.38	12.17	13.37	10.10	10.89	11.02	11.82	13.01
	3H	12.31	12.97	13.25	13.93	15.15	11.91	12.57	12.85	13.53	14.74
	4H	13.03	13.63	13.97	14.58	15.82	12.61	13.21	13.56	14.16	15.40
	6H	13.54	14.06	14.50	15.04	16.27	13.12	13.64	14.08	14.61	15.85
	8H	13.69	14.17	14.65	15.14	16.40	13.26	13.75	14.22	14.72	15.97
	12H	13.76	14.20	14.74	15.19	16.45	13.32	13.76	14.30	14.75	16.01
8H	4H	13.22	13.71	14.19	14.68	15.93	12.85	13.34	13.82	14.31	15.56
	6H	13.85	14.25	14.84	15.26	16.52	13.48	13.88	14.46	14.89	16.14
	8H	14.07	14.42	15.06	15.42	16.69	13.69	14.04	14.68	15.04	16.31
	12H	14.20	14.51	15.20	15.51	16.82	13.80	14.11	14.80	15.11	16.42
12H	4H	13.21	13.65	14.19	14.64	15.90	12.85	13.29	13.83	14.28	15.53
	6H	13.88	14.23	14.88	15.24	16.51	13.52	13.87	14.51	14.87	16.14
	8H	14.12	14.43	15.12	15.43	16.74	13.75	14.06	14.75	15.06	16.37