

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908458

Luminaire Tested: DFN2DIP-PN3F0-040D090US840-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P908458  
REPORT IS A COMBINATION OF REPORTS P899598 AND P896399  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-040D090US840-RLLFLL  
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11477.1 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 105.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P908458  
CATALOG NUMBER: DFN2DIP-PN3F0-040D090US840-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P908458

CATALOG NUMBER: DFN2DIP-PN3F0-040D090US840-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	38	30
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26	
2	85	78	73	68	76	71	66	62	56	53	50	43	40	38	30	29	28	30	29	28	22	
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19	
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17	
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15	
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13	
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14	18	16	14	12	
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	10	
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10	
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11	14	12	11	9	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1952	1952	1952
5°	1954	1919	1932
10°	1933	1880	1869
15°	1905	1817	1770
20°	1869	1730	1651
25°	1832	1633	1535
30°	1782	1533	1388
35°	1733	1426	1259
40°	1684	1316	1112
45°	1626	1193	979
50°	1567	1070	848
55°	1504	938	723
60°	1432	801	594
65°	1349	661	534
70°	1248	531	482
75°	1121	465	437
80°	937	385	376
85°	637	251	278

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2847 cd/sqm



TEST NUMBER: P908458

CATALOG NUMBER: DFN2DIP-PN3F0-040D090US840-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.5	1.4
10°-20°	429.5	3.7
20°-30°	603.0	5.3
30°-40°	657.4	5.7
40°-50°	604.2	5.3
50°-60°	474.5	4.1
60°-70°	308.9	2.7
70°-80°	159.0	1.4
80°-90°	48.8	0.4
90°-100°	177.9	1.5
100°-110°	565.2	4.9
110°-120°	967.2	8.4
120°-130°	1272.0	11.1
130°-140°	1427.7	12.4
140°-150°	1400.0	12.2
150°-160°	1174.4	10.2
160°-170°	778.9	6.8
170°-180°	272.2	2.4
0°-30°	1189.0	10.4
0°-40°	1846.4	16.1
0°-60°	2925.1	25.5
0°-90°	3441.7	30.0
90°-120°	1710.2	14.9
90°-150°	5809.9	50.6
90°-180°	8035.0	70.0
0°-180°	11477.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1670	1670	1670	1670	1670	
5°	1670	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1209	663
35°	1242	1165	1032	937	903	777
45°	1015	914	756	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	3	31	85	80	82	11
95°	126	151	155	155	151	141
105°	522	529	534	538	538	551
115°	971	984	980	978	971	960
125°	1412	1433	1426	1419	1416	1261
135°	1826	1853	1858	1855	1848	1411
145°	2217	2234	2248	2250	2241	1385
155°	2535	2542	2550	2562	2554	1167
165°	2757	2755	2755	2772	2760	778
175°	2869	2862	2857	2874	2860	273
180°	2874	2874	2874	2874	2874	



TEST NUMBER: P908458

CATALOG NUMBER: DFN2DIP-PN3F0-040D090US840-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1669.5	1669.5	1669.5	1669.5	1669.5
2.5°	1677.1	1669.5	1652.8	1668.1	1665.0
5°	1669.5	1661.9	1642.2	1655.9	1651.4
7.5°	1655.9	1646.9	1625.8	1631.6	1624.2
10°	1637.8	1627.2	1597.0	1592.4	1583.5
12.5°	1615.2	1601.5	1560.6	1551.7	1535.0
15°	1587.9	1571.2	1519.9	1491.3	1476.2
17.5°	1556.2	1532.0	1468.4	1435.3	1411.1
20°	1519.9	1489.7	1414.1	1376.4	1343.1
22.5°	1480.7	1445.9	1358.2	1306.9	1284.3
25°	1441.4	1393.0	1293.2	1231.4	1208.6
27.5°	1394.6	1343.1	1232.8	1161.9	1127.0
30°	1344.7	1287.2	1166.3	1089.3	1048.5
32.5°	1296.4	1226.8	1103.0	1012.3	974.4
35°	1242.0	1164.9	1032.0	936.8	903.4
37.5°	1189.1	1105.9	965.4	861.1	823.4
40°	1133.2	1042.6	896.0	788.7	749.4
42.5°	1075.7	979.1	826.5	714.6	676.9
45°	1015.3	914.0	755.5	648.1	611.9
47.5°	958.0	850.7	687.5	580.2	546.9
50°	894.4	787.2	621.0	516.6	485.0
52.5°	832.4	719.1	557.5	457.8	429.1
55°	772.0	654.2	491.0	400.4	371.7
57.5°	710.1	589.3	432.1	347.5	323.4
60°	646.6	525.7	370.1	293.2	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.6	66.6
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	2.6	31.2	84.9	79.7	82.3
92.5°	53.7	72.8	75.4	78.0	78.0
95°	126.5	150.8	155.1	155.1	150.8
97.5°	210.6	233.1	242.7	242.7	242.7
100°	307.6	327.6	334.5	334.5	331.9
102.5°	409.9	424.6	434.1	436.8	434.1
105°	521.7	528.6	533.8	538.2	538.2
107.5°	632.6	643.0	643.0	644.7	632.6
110°	740.0	754.0	754.0	754.0	747.0



TEST NUMBER: P908458

CATALOG NUMBER: DFN2DIP-PN3F0-040D090US840-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	856.2	870.9	868.3	861.4	856.2
115°	970.6	984.4	980.1	977.5	970.6
117.5°	1084.1	1103.2	1091.1	1084.1	1077.1
120°	1198.5	1217.5	1198.5	1198.5	1190.6
122.5°	1302.4	1326.8	1314.6	1307.7	1302.4
125°	1411.7	1433.3	1426.4	1418.6	1416.0
127.5°	1518.2	1545.1	1535.6	1525.2	1518.2
130°	1617.9	1649.1	1644.8	1639.5	1630.0
132.5°	1729.7	1753.9	1755.7	1743.5	1736.7
135°	1825.8	1852.7	1858.0	1855.3	1848.5
137.5°	1933.3	1955.0	1959.3	1957.6	1947.2
140°	2027.8	2049.4	2061.5	2061.5	2052.0
142.5°	2124.9	2146.5	2153.4	2156.1	2146.5
145°	2216.8	2234.0	2247.9	2250.5	2241.0
147.5°	2299.1	2320.7	2331.1	2335.4	2325.9
150°	2384.0	2398.7	2408.2	2416.0	2408.2
152.5°	2459.3	2474.1	2486.2	2495.8	2486.2
155°	2534.8	2541.6	2549.5	2561.6	2553.8
157.5°	2599.7	2604.9	2609.3	2626.6	2614.4
160°	2657.8	2663.0	2665.6	2680.3	2669.9
162.5°	2711.5	2711.5	2714.1	2730.6	2718.5
165°	2757.4	2754.8	2754.8	2772.2	2760.1
167.5°	2799.0	2791.3	2791.3	2808.5	2796.4
170°	2830.2	2823.3	2820.8	2838.0	2823.3
172.5°	2851.9	2845.0	2842.4	2859.7	2845.0
175°	2869.2	2862.3	2857.1	2874.5	2859.7
177.5°	2878.7	2871.9	2866.6	2881.3	2866.6
180°	2874.5	2874.5	2874.5	2874.5	2874.5



TEST NUMBER: P908458  
 CATALOG NUMBER: DFN2DIP-PN3F0-040D090US840-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.19	7.88	8.31	8.99	10.53	3.16	3.85	4.28	4.96	6.49
	3H	8.86	9.47	9.98	10.59	12.14	4.33	4.95	5.46	6.07	7.61
	4H	9.45	10.04	10.59	11.16	12.71	4.77	5.36	5.91	6.47	8.03
	6H	9.86	10.40	11.01	11.52	13.09	5.08	5.62	6.22	6.74	8.30
	8H	9.98	10.49	11.13	11.63	13.19	5.16	5.68	6.31	6.81	8.37
	12H	10.04	10.52	11.19	11.65	13.23	5.20	5.69	6.35	6.81	8.40
4H	2H	7.19	7.78	8.34	8.90	10.45	3.73	4.32	4.88	5.44	6.99
	3H	9.00	9.49	10.15	10.63	12.20	5.07	5.55	6.21	6.70	8.26
	4H	9.68	10.13	10.83	11.26	12.85	5.60	6.05	6.75	7.18	8.77
	6H	10.19	10.57	11.34	11.72	13.30	6.01	6.39	7.16	7.55	9.12
	8H	10.36	10.71	11.51	11.86	13.45	6.13	6.49	7.29	7.64	9.23
	12H	10.44	10.76	11.61	11.92	13.52	6.19	6.51	7.36	7.67	9.27
8H	4H	9.64	10.00	10.80	11.14	12.74	5.87	6.23	7.02	7.37	8.97
	6H	10.19	10.49	11.37	11.68	13.27	6.37	6.67	7.55	7.86	9.45
	8H	10.41	10.66	11.59	11.83	13.44	6.56	6.82	7.74	7.98	9.60
	12H	10.53	10.76	11.72	11.92	13.57	6.67	6.89	7.85	8.06	9.70
12H	4H	9.59	9.91	10.76	11.07	12.67	5.87	6.19	7.04	7.35	8.95
	6H	10.17	10.43	11.35	11.59	13.20	6.42	6.68	7.60	7.85	9.46
	8H	10.38	10.60	11.56	11.77	13.41	6.62	6.85	7.80	8.01	9.66