

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903220

Luminaire Tested: DFN2DIP-PN4F0-060D050US830-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P903220  
REPORT IS A COMBINATION OF REPORTS P899631 AND P896497  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-060D050US830-FLLFLL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9769.4 lumens  
Efficiency: N/A  
Efficacy: 106.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 92.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P903220  
CATALOG NUMBER: DFN2DIP-PN4F0-060D050US830-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P903220  
 CATALOG NUMBER: DFN2DIP-PN4F0-060D050US830-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57			57
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	56	54	53	48			48
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45	40			40
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	41	38	34			34
4	76	65	57	51	70	61	53	48	53	47	43	46	41	38	39	36	33	29			29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29	26			26
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25	22			22
7	59	47	39	33	55	44	37	32	39	33	28	34	29	25	29	25	22	20			20
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18			18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16			16
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15			15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1606	1606	1606
5°	1609	1584	1595
10°	1596	1563	1574
15°	1572	1538	1540
20°	1541	1502	1506
25°	1509	1459	1466
30°	1470	1420	1416
35°	1432	1373	1362
40°	1386	1326	1311
45°	1340	1279	1259
50°	1290	1229	1199
55°	1237	1172	1144
60°	1178	1104	1081
65°	1113	1033	1006
70°	1030	947	926
75°	915	844	852
80°	778	714	710
85°	562	487	475

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1340 cd/sqm



TEST NUMBER: P903220

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US830-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.1	2.1
10°-20°	582.7	6.0
20°-30°	856.4	8.8
30°-40°	994.6	10.2
40°-50°	993.4	10.2
50°-60°	866.2	8.9
60°-70°	640.3	6.6
70°-80°	362.3	3.7
80°-90°	99.9	1.0
90°-100°	92.2	0.9
100°-110°	293.0	3.0
110°-120°	501.5	5.1
120°-130°	659.5	6.8
130°-140°	740.3	7.6
140°-150°	725.9	7.4
150°-160°	609.0	6.2
160°-170°	403.9	4.1
170°-180°	141.2	1.4
0°-30°	1646.2	16.9
0°-40°	2640.9	27.0
0°-60°	4500.5	46.1
0°-90°	5602.9	57.4
90°-120°	886.7	9.1
90°-150°	3012.5	30.8
90°-180°	4167.0	42.7
0°-180°	9769.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2200	2200	2200	2200	2200	
5°	2200	2192	2169	2186	2182	209
15°	2095	2082	2055	2063	2053	590
25°	1896	1879	1843	1847	1843	872
35°	1636	1615	1581	1568	1557	1021
45°	1331	1316	1284	1261	1253	1027
55°	1007	994	969	944	933	901
65°	679	667	646	626	616	672
75°	355	351	340	328	332	379
85°	87	85	83	76	74	97
90°	1	16	44	41	43	9
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P903220

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US830-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2200.5	2200.5	2200.5	2200.5	2200.5
2.5°	2213.3	2202.7	2179.3	2200.5	2196.4
5°	2200.5	2192.2	2168.8	2185.7	2181.6
7.5°	2185.7	2173.1	2149.8	2166.8	2162.6
10°	2162.6	2147.8	2122.3	2139.2	2132.9
12.5°	2130.7	2118.1	2092.7	2103.3	2099.0
15°	2094.7	2082.2	2054.6	2063.1	2052.6
17.5°	2050.3	2037.8	2010.2	2020.6	2010.2
20°	2001.6	1989.0	1959.4	1965.7	1957.4
22.5°	1953.1	1934.0	1906.4	1906.4	1902.1
25°	1895.8	1879.1	1843.0	1847.1	1843.0
27.5°	1832.3	1817.5	1790.1	1783.9	1773.3
30°	1769.1	1751.9	1720.3	1714.0	1705.4
32.5°	1701.2	1688.7	1654.7	1641.9	1633.4
35°	1635.7	1614.6	1580.6	1567.8	1557.3
37.5°	1561.6	1542.5	1508.6	1493.7	1483.2
40°	1485.4	1468.4	1434.5	1415.7	1407.1
42.5°	1411.4	1394.3	1360.7	1339.4	1326.7
45°	1331.1	1316.2	1284.3	1261.2	1252.6
47.5°	1252.6	1237.8	1204.0	1180.6	1168.0
50°	1170.1	1159.5	1129.9	1100.2	1089.7
52.5°	1089.7	1074.9	1047.4	1024.2	1009.4
55°	1007.3	994.5	969.1	943.8	933.2
57.5°	924.7	914.2	886.6	861.2	852.6
60°	842.1	833.8	804.2	780.8	774.5
62.5°	761.7	746.9	725.8	704.6	696.2
65°	679.3	666.6	645.5	626.3	615.8
67.5°	594.6	583.9	565.1	550.3	541.7
70°	516.3	507.8	488.7	473.9	465.6
72.5°	435.9	427.4	416.9	402.1	395.8
75°	355.3	351.4	340.5	328.0	332.2
77.5°	283.5	275.0	270.7	264.5	258.2
80°	211.7	209.4	205.2	198.9	194.6
82.5°	143.9	143.9	141.9	133.4	133.4
85°	86.6	84.6	82.6	76.1	74.1
87.5°	38.2	33.9	29.6	23.4	21.1
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3



TEST NUMBER: P903220

CATALOG NUMBER: DFN2DIP-PN4F0-060D050US830-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4



TEST NUMBER: P903220  
 CATALOG NUMBER: DFN2DIP-PN4F0-060D050US830-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.58	10.51	10.47	11.42	12.58	9.14	10.07	10.03	10.98	12.14
	3H	11.25	12.08	12.15	13.00	14.19	10.76	11.60	11.66	12.52	13.71
	4H	11.84	12.63	12.76	13.55	14.75	11.35	12.14	12.27	13.07	14.26
	6H	12.24	12.97	13.17	13.90	15.11	11.75	12.48	12.68	13.41	14.62
	8H	12.35	13.05	13.29	14.00	15.20	11.86	12.55	12.80	13.50	14.71
	12H	12.40	13.06	13.35	14.01	15.24	11.90	12.56	12.85	13.51	14.74
4H	2H	10.05	10.84	10.97	11.76	12.96	9.70	10.49	10.62	11.41	12.61
	3H	11.92	12.58	12.86	13.54	14.75	11.52	12.18	12.45	13.14	14.35
	4H	12.64	13.24	13.59	14.20	15.43	12.22	12.83	13.17	13.78	15.01
	6H	13.16	13.68	14.12	14.66	15.89	12.74	13.26	13.70	14.23	15.47
	8H	13.32	13.80	14.28	14.77	16.02	12.89	13.37	13.85	14.34	15.59
	12H	13.39	13.83	14.37	14.82	16.07	12.95	13.39	13.93	14.38	15.63
8H	4H	12.84	13.33	13.80	14.30	15.55	12.47	12.96	13.43	13.93	15.18
	6H	13.48	13.88	14.47	14.89	16.14	13.11	13.51	14.09	14.52	15.77
	8H	13.70	14.06	14.70	15.06	16.33	13.32	13.68	14.32	14.68	15.94
	12H	13.84	14.15	14.84	15.15	16.46	13.44	13.75	14.44	14.75	16.06
12H	4H	12.83	13.27	13.81	14.26	15.51	12.47	12.91	13.45	13.90	15.15
	6H	13.51	13.87	14.51	14.87	16.13	13.15	13.50	14.14	14.50	15.77
	8H	13.76	14.07	14.76	15.07	16.38	13.39	13.70	14.39	14.69	16.01