

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908543

Luminaire Tested: DFN2DIP-PN3F0-070D090US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908543
REPORT IS A COMBINATION OF REPORTS P901124 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D090US840-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15006.5 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908543

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908543

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	105	105	105	105		95	95	95	95		78	78	78		62	62	62		47	47	47
1	96	92	88	85		87	84	81	78		69	67	65		55	53	52		42	41	40
2	88	81	75	70		80	74	69	64		61	57	54		49	46	44		38	36	35
3	80	71	64	59		73	65	59	54		54	49	46		43	40	38		34	32	30
4	74	63	56	50		67	58	51	46		48	43	39		39	35	33		30	28	26
5	68	56	49	43		61	52	45	40		43	38	34		35	31	28		27	25	23
6	62	51	43	37		57	47	40	35		39	34	30		32	28	25		25	22	20
7	58	46	38	33		52	42	35	31		35	30	26		29	25	22		23	20	18
8	54	42	34	29		49	38	32	27		32	27	24		27	23	20		21	18	16
9	50	38	31	26		45	35	29	24		30	25	21		24	21	18		20	17	15
10	47	35	28	23		43	32	26	22		27	22	19		23	19	16		18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3415	3415	3415
5°	3419	3359	3381
10°	3383	3290	3270
15°	3334	3179	3098
20°	3271	3027	2889
25°	3205	2857	2686
30°	3119	2683	2429
35°	3033	2496	2204
40°	2947	2302	1946
45°	2846	2088	1712
50°	2742	1872	1484
55°	2633	1642	1265
60°	2506	1401	1040
65°	2361	1157	934
70°	2184	929	843
75°	1962	814	764
80°	1640	675	658
85°	1114	439	486

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2846 cd/sqm

TEST NUMBER: P908543

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US840-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.8	1.8
10°-20°	751.7	5.0
20°-30°	1055.3	7.0
30°-40°	1150.4	7.7
40°-50°	1057.3	7.0
50°-60°	830.4	5.5
60°-70°	540.5	3.6
70°-80°	278.2	1.9
80°-90°	76.4	0.5
90°-100°	101.2	0.7
100°-110°	377.0	2.5
110°-120°	1000.0	6.7
120°-130°	1658.6	11.1
130°-140°	1761.8	11.7
140°-150°	1637.4	10.9
150°-160°	1316.4	8.8
160°-170°	848.2	5.7
170°-180°	292.0	1.9
0°-30°	2080.9	13.9
0°-40°	3231.2	21.5
0°-60°	5118.9	34.1
0°-90°	6014.0	40.1
90°-120°	1478.2	9.9
90°-150°	6535.9	43.6
90°-180°	8992.0	59.9
0°-180°	15006.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2922	2922	2922	2922	2922	
5°	2922	2908	2874	2898	2890	277
15°	2779	2750	2660	2610	2583	783
25°	2522	2438	2263	2155	2115	1160
35°	2173	2038	1806	1639	1581	1360
45°	1777	1600	1322	1134	1071	1372
55°	1351	1145	859	701	651	1207
65°	912	698	460	370	362	904
75°	486	301	212	193	190	515
85°	114	58	50	50	50	130
90°	2	27	44	56	60	14
95°	144	71	86	98	95	171
105°	675	741	135	160	169	721
115°	1276	1314	1370	342	182	1256
125°	1804	1833	1876	1891	1898	1609
135°	2233	2268	2288	2311	2306	1725
145°	2590	2588	2626	2641	2630	1620
155°	2852	2832	2859	2872	2854	1314
165°	3005	2992	2999	3014	2999	849
175°	3074	3058	3063	3078	3056	293
180°	3067	3067	3067	3067	3067	

TEST NUMBER: P908543

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2921.6	2921.6	2921.6	2921.6	2921.6
2.5°	2934.8	2921.6	2892.5	2919.1	2913.8
5°	2921.6	2908.4	2874.0	2897.8	2889.9
7.5°	2897.8	2882.1	2845.1	2855.4	2842.3
10°	2866.1	2847.6	2794.8	2786.7	2771.0
12.5°	2826.5	2802.7	2731.2	2715.4	2686.2
15°	2778.8	2749.7	2659.9	2609.7	2583.3
17.5°	2723.3	2681.0	2569.9	2511.7	2469.4
20°	2659.9	2606.9	2474.8	2408.8	2350.5
22.5°	2591.2	2530.3	2376.8	2287.0	2247.6
25°	2522.4	2437.7	2263.2	2155.0	2115.2
27.5°	2440.5	2350.5	2157.5	2033.3	1972.4
30°	2353.3	2252.6	2041.0	1906.4	1834.9
32.5°	2268.6	2146.9	1930.3	1771.5	1705.3
35°	2173.4	2038.5	1806.0	1639.4	1581.0
37.5°	2080.9	1935.3	1689.6	1506.9	1441.1
40°	1983.0	1824.5	1567.8	1380.2	1311.4
42.5°	1882.6	1713.4	1446.3	1250.5	1184.7
45°	1776.9	1599.5	1322.1	1134.2	1070.8
47.5°	1676.4	1488.7	1203.2	1015.2	957.2
50°	1565.3	1377.7	1086.7	904.1	848.9
52.5°	1456.7	1258.4	975.6	801.1	750.9
55°	1351.0	1144.8	859.2	700.7	650.6
57.5°	1242.7	1031.2	756.3	608.1	565.8
60°	1131.7	920.1	647.7	513.1	470.7
62.5°	1023.3	811.8	555.1	428.4	407.3
65°	912.2	697.9	460.1	370.3	362.1
67.5°	806.5	592.2	370.3	325.1	317.3
70°	695.4	489.2	306.6	280.2	269.5
72.5°	589.7	393.8	256.4	235.4	230.0
75°	486.5	301.2	211.5	193.0	190.5
77.5°	383.4	214.0	166.6	155.9	150.7
80°	288.1	153.4	126.8	116.4	116.4
82.5°	200.9	103.2	87.3	81.9	81.9
85°	113.6	58.1	50.2	50.2	50.2
87.5°	42.3	21.0	21.0	18.5	18.5
90°	2.1	26.7	44.2	55.6	59.8
92.5°	55.6	46.7	53.2	57.8	59.8
95°	144.2	70.9	86.4	97.8	95.4
97.5°	259.6	77.8	113.1	119.9	122.0
100°	392.9	88.9	126.5	144.2	148.7
102.5°	539.3	535.0	131.0	155.2	162.1
105°	674.7	741.4	135.4	159.8	168.6
107.5°	832.3	887.7	140.0	164.2	173.2
110°	983.3	1029.8	388.5	166.5	175.3

TEST NUMBER: P908543

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1125.4	1165.2	1127.5	170.8	177.6
115°	1276.2	1313.8	1369.5	341.8	182.1
117.5°	1407.1	1451.5	1489.3	1171.8	590.4
120°	1553.7	1586.9	1627.0	1653.6	1353.9
122.5°	1677.9	1713.4	1758.0	1771.1	1773.5
125°	1804.3	1833.3	1875.5	1891.1	1897.6
127.5°	1919.8	1950.9	1984.4	2006.5	2008.6
130°	2028.6	2064.3	2088.5	2112.9	2110.9
132.5°	2139.6	2168.6	2192.8	2212.9	2210.8
135°	2232.9	2268.5	2288.3	2310.7	2306.2
137.5°	2330.5	2357.0	2379.4	2401.6	2395.0
140°	2425.8	2443.8	2468.0	2488.0	2477.0
142.5°	2506.0	2521.5	2550.2	2567.9	2556.9
145°	2590.3	2587.9	2625.7	2641.2	2630.1
147.5°	2663.3	2656.8	2694.4	2705.5	2696.7
150°	2734.5	2719.0	2754.5	2767.6	2756.6
152.5°	2794.3	2776.6	2809.8	2823.3	2807.7
155°	2852.1	2832.3	2858.8	2872.1	2854.4
157.5°	2898.7	2881.0	2901.0	2916.6	2898.7
160°	2938.7	2925.3	2938.7	2951.9	2936.4
162.5°	2974.1	2960.8	2971.9	2987.5	2967.5
165°	3005.2	2991.9	2998.6	3014.1	2998.6
167.5°	3029.7	3016.3	3023.0	3038.6	3018.6
170°	3049.7	3036.3	3040.7	3056.3	3036.3
172.5°	3062.9	3049.7	3054.1	3069.7	3049.7
175°	3073.9	3058.4	3062.9	3078.4	3056.3
177.5°	3078.4	3062.9	3065.2	3080.8	3060.8
180°	3067.4	3067.4	3067.4	3067.4	3067.4

TEST NUMBER: P908543

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.37	11.13	11.42	12.17	13.58	6.34	7.09	7.38	8.14	9.55
	3H	12.04	12.71	13.09	13.77	15.20	7.52	8.19	8.57	9.24	10.67
	4H	12.64	13.28	13.71	14.34	15.77	7.96	8.60	9.02	9.65	11.09
	6H	13.05	13.64	14.13	14.70	16.15	8.27	8.86	9.35	9.92	11.37
	8H	13.17	13.73	14.25	14.81	16.25	8.36	8.92	9.44	9.99	11.43
	12H	13.23	13.76	14.31	14.83	16.30	8.39	8.93	9.48	9.99	11.46
4H	2H	10.38	11.02	11.45	12.08	13.51	6.92	7.56	7.99	8.62	10.05
	3H	12.20	12.73	13.28	13.81	15.26	8.26	8.79	9.34	9.87	11.32
	4H	12.88	13.37	13.96	14.44	15.91	8.80	9.29	9.88	10.36	11.83
	6H	13.39	13.80	14.48	14.90	16.36	9.21	9.62	10.30	10.72	12.19
	8H	13.56	13.95	14.65	15.04	16.51	9.33	9.72	10.42	10.81	12.29
	12H	13.64	14.00	14.75	15.10	16.58	9.39	9.74	10.50	10.84	12.33
8H	4H	12.84	13.23	13.93	14.32	15.80	9.07	9.46	10.16	10.55	12.03
	6H	13.40	13.72	14.51	14.85	16.33	9.58	9.90	10.69	11.03	12.51
	8H	13.61	13.89	14.73	15.01	16.50	9.76	10.04	10.88	11.16	12.65
	12H	13.74	13.99	14.87	15.10	16.63	9.87	10.12	11.00	11.23	12.76
12H	4H	12.79	13.14	13.90	14.24	15.73	9.07	9.42	10.18	10.53	12.01
	6H	13.37	13.65	14.49	14.77	16.26	9.62	9.91	10.75	11.02	12.51
	8H	13.58	13.83	14.71	14.94	16.48	9.83	10.07	10.95	11.18	12.72

END OF REPORT