

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911146

Luminaire Tested: DFN2DIP-PN3F0-030D060US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911146
REPORT IS A COMBINATION OF REPORTS P899554 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D060US850-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8716.7 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911146

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911146

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1607	1607	1607
5°	1609	1581	1591
10°	1592	1549	1539
15°	1569	1496	1458
20°	1539	1425	1359
25°	1509	1345	1264
30°	1468	1263	1143
35°	1428	1175	1037
40°	1387	1084	916
45°	1340	983	806
50°	1290	881	698
55°	1239	773	595
60°	1179	660	489
65°	1111	544	440
70°	1028	437	397
75°	923	383	359
80°	772	318	310
85°	525	206	228

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2082 cd/sqm

TEST NUMBER: P911146

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	1.5
10°-20°	353.8	4.1
20°-30°	496.7	5.7
30°-40°	541.4	6.2
40°-50°	497.6	5.7
50°-60°	390.8	4.5
60°-70°	254.4	2.9
70°-80°	130.9	1.5
80°-90°	39.4	0.5
90°-100°	130.2	1.5
100°-110°	413.7	4.7
110°-120°	708.0	8.1
120°-130°	931.2	10.7
130°-140°	1045.3	12.0
140°-150°	1025.0	11.8
150°-160°	859.8	9.9
160°-170°	570.2	6.5
170°-180°	199.3	2.3
0°-30°	979.3	11.2
0°-40°	1520.7	17.4
0°-60°	2409.2	27.6
0°-90°	2833.9	32.5
90°-120°	1252.0	14.4
90°-150°	4253.5	48.8
90°-180°	5883.0	67.5
0°-180°	8716.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	2	23	62	58	60	9
95°	93	110	114	114	110	103
105°	382	387	391	394	394	403
115°	710	721	718	716	710	703
125°	1034	1049	1044	1039	1037	924
135°	1337	1356	1360	1358	1353	1033
145°	1623	1636	1646	1648	1641	1014
155°	1856	1861	1866	1875	1870	854
165°	2019	2017	2017	2030	2021	569
175°	2101	2096	2092	2104	2094	200
180°	2104	2104	2104	2104	2104	

TEST NUMBER: P911146

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	1.9	22.8	62.2	58.3	60.2
92.5°	39.4	53.3	55.2	57.1	57.1
95°	92.6	110.3	113.6	113.6	110.3
97.5°	154.2	170.7	177.7	177.7	177.7
100°	225.2	239.8	244.9	244.9	243.0
102.5°	300.1	310.9	317.8	319.7	317.8
105°	381.9	387.0	390.8	394.0	394.0
107.5°	463.1	470.8	470.8	472.0	463.1
110°	541.9	551.9	551.9	551.9	546.8

TEST NUMBER: P911146

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.8	637.6	635.7	630.6	626.8
115°	710.5	720.7	717.5	715.6	710.5
117.5°	793.7	807.7	798.7	793.7	788.6
120°	877.4	891.4	877.4	877.4	871.7
122.5°	953.5	971.3	962.4	957.4	953.5
125°	1033.5	1049.3	1044.2	1038.6	1036.7
127.5°	1111.6	1131.2	1124.2	1116.7	1111.6
130°	1184.5	1207.4	1204.2	1200.4	1193.4
132.5°	1266.4	1284.1	1285.3	1276.5	1271.4
135°	1336.8	1356.4	1360.2	1358.3	1353.2
137.5°	1415.4	1431.3	1434.5	1433.2	1425.6
140°	1484.6	1500.5	1509.3	1509.3	1502.4
142.5°	1555.6	1571.5	1576.6	1578.4	1571.5
145°	1622.9	1635.6	1645.8	1647.6	1640.7
147.5°	1683.1	1699.0	1706.6	1709.7	1702.8
150°	1745.3	1756.1	1763.1	1768.7	1763.1
152.5°	1800.5	1811.3	1820.2	1827.2	1820.2
155°	1855.7	1860.8	1866.4	1875.4	1869.7
157.5°	1903.3	1907.1	1910.3	1923.0	1914.1
160°	1945.9	1949.6	1951.5	1962.3	1954.7
162.5°	1985.1	1985.1	1987.0	1999.1	1990.2
165°	2018.7	2016.8	2016.8	2029.6	2020.7
167.5°	2049.2	2043.6	2043.6	2056.2	2047.3
170°	2072.1	2067.0	2065.1	2077.7	2067.0
172.5°	2087.9	2082.8	2080.9	2093.6	2082.8
175°	2100.6	2095.6	2091.7	2104.4	2093.6
177.5°	2107.5	2102.6	2098.7	2109.4	2098.7
180°	2104.4	2104.4	2104.4	2104.4	2104.4

TEST NUMBER: P911146

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.86	7.56	7.96	8.65	10.16	2.82	3.53	3.92	4.62	6.12
	3H	8.52	9.15	9.63	10.25	11.77	3.99	4.62	5.10	5.73	7.25
	4H	9.12	9.71	10.23	10.82	12.34	4.43	5.03	5.55	6.14	7.66
	6H	9.53	10.08	10.65	11.18	12.72	4.74	5.29	5.87	6.40	7.94
	8H	9.65	10.17	10.78	11.29	12.82	4.83	5.35	5.96	6.47	8.00
	12H	9.70	10.20	10.84	11.31	12.87	4.86	5.36	6.00	6.48	8.03
4H	2H	6.86	7.45	7.98	8.56	10.08	3.40	4.00	4.52	5.10	6.62
	3H	8.67	9.17	9.80	10.29	11.83	4.73	5.23	5.86	6.36	7.89
	4H	9.35	9.81	10.48	10.93	12.48	5.27	5.72	6.40	6.84	8.40
	6H	9.85	10.24	10.99	11.38	12.93	5.67	6.07	6.81	7.21	8.76
	8H	10.02	10.39	11.16	11.52	13.09	5.80	6.16	6.94	7.30	8.86
	12H	10.11	10.44	11.26	11.58	13.15	5.85	6.18	7.01	7.33	8.90
8H	4H	9.31	9.67	10.45	10.81	12.37	5.53	5.90	6.67	7.03	8.60
	6H	9.86	10.16	11.02	11.34	12.90	6.04	6.34	7.20	7.52	9.08
	8H	10.07	10.34	11.24	11.49	13.07	6.23	6.49	7.39	7.64	9.23
	12H	10.20	10.43	11.37	11.58	13.20	6.34	6.57	7.51	7.72	9.34
12H	4H	9.25	9.58	10.41	10.73	12.30	5.53	5.86	6.69	7.01	8.58
	6H	9.84	10.10	11.00	11.25	12.84	6.09	6.35	7.25	7.51	9.09
	8H	10.05	10.28	11.22	11.43	13.05	6.29	6.52	7.46	7.67	9.29

END OF REPORT