

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911150

Luminaire Tested: DFN2DIP-PN3F0-030D070US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911150
REPORT IS A COMBINATION OF REPORTS P899568 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D070US850-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9698.2 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911150

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P911150

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	32	32
2	85	78	72	68	76	70	66	61	56	52	49	42	40	38	29	28	27
3	78	69	62	57	70	62	56	52	49	45	42	37	35	32	26	25	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	24	22	20
5	65	54	47	41	59	49	43	38	39	35	31	30	27	24	21	19	18
6	60	49	41	36	54	44	38	33	35	31	27	27	24	21	20	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	33	27	46	36	30	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1607	1607	1607
5°	1609	1581	1591
10°	1592	1549	1539
15°	1569	1496	1458
20°	1539	1425	1359
25°	1509	1345	1264
30°	1468	1263	1143
35°	1428	1175	1037
40°	1387	1084	916
45°	1340	983	806
50°	1290	881	698
55°	1239	773	595
60°	1179	660	489
65°	1111	544	440
70°	1028	437	397
75°	923	383	359
80°	772	318	310
85°	525	206	228

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2432 cd/sqm

TEST NUMBER: P911150

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	1.3
10°-20°	353.8	3.6
20°-30°	496.7	5.1
30°-40°	541.4	5.6
40°-50°	497.6	5.1
50°-60°	390.8	4.0
60°-70°	254.4	2.6
70°-80°	130.9	1.4
80°-90°	40.4	0.4
90°-100°	151.9	1.6
100°-110°	482.7	5.0
110°-120°	826.1	8.5
120°-130°	1086.4	11.2
130°-140°	1219.5	12.6
140°-150°	1195.8	12.3
150°-160°	1003.1	10.3
160°-170°	665.3	6.9
170°-180°	232.5	2.4
0°-30°	979.3	10.1
0°-40°	1520.7	15.7
0°-60°	2409.2	24.8
0°-90°	2834.9	29.2
90°-120°	1460.7	15.1
90°-150°	4962.4	51.2
90°-180°	6863.0	70.8
0°-180°	9698.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	2	27	72	68	70	10
95°	108	129	132	132	129	120
105°	446	452	456	460	460	470
115°	829	841	837	835	829	820
125°	1206	1224	1218	1212	1210	1077
135°	1560	1582	1587	1585	1579	1205
145°	1893	1908	1920	1922	1914	1183
155°	2165	2171	2178	2188	2181	997
165°	2355	2353	2353	2368	2357	664
175°	2451	2445	2440	2455	2443	233
180°	2455	2455	2455	2455	2455	

TEST NUMBER: P911150

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	2.2	26.6	72.5	68.1	70.3
92.5°	45.9	62.2	64.4	66.7	66.7
95°	108.0	128.8	132.5	132.5	128.8
97.5°	179.9	199.1	207.3	207.3	207.3
100°	262.7	279.8	285.7	285.7	283.5
102.5°	350.1	362.6	370.8	373.1	370.8
105°	445.6	451.5	455.9	459.7	459.7
107.5°	540.3	549.2	549.2	550.7	540.3
110°	632.1	644.0	644.0	644.0	638.0



TEST NUMBER: P911150

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	731.3	743.9	741.7	735.7	731.3
115°	829.0	840.8	837.2	835.0	829.0
117.5°	925.9	942.2	931.9	925.9	920.0
120°	1023.6	1039.9	1023.6	1023.6	1017.0
122.5°	1112.4	1133.2	1122.9	1116.9	1112.4
125°	1205.7	1224.2	1218.3	1211.7	1209.5
127.5°	1296.8	1319.7	1311.6	1302.7	1296.8
130°	1381.9	1408.5	1404.9	1400.4	1392.2
132.5°	1477.4	1498.1	1499.6	1489.3	1483.3
135°	1559.6	1582.4	1587.0	1584.7	1578.8
137.5°	1651.3	1669.8	1673.5	1672.0	1663.2
140°	1732.0	1750.6	1760.9	1760.9	1752.8
142.5°	1814.9	1833.4	1839.3	1841.5	1833.4
145°	1893.4	1908.1	1920.0	1922.2	1914.1
147.5°	1963.7	1982.2	1991.1	1994.8	1986.7
150°	2036.2	2048.8	2057.0	2063.6	2057.0
152.5°	2100.6	2113.2	2123.5	2131.7	2123.5
155°	2165.0	2170.9	2177.6	2187.9	2181.3
157.5°	2220.6	2225.0	2228.6	2243.5	2233.1
160°	2270.1	2274.6	2276.8	2289.3	2280.4
162.5°	2316.0	2316.0	2318.3	2332.2	2321.9
165°	2355.2	2353.0	2353.0	2367.8	2357.4
167.5°	2390.8	2384.1	2384.1	2398.9	2388.6
170°	2417.4	2411.5	2409.3	2424.1	2411.5
172.5°	2435.9	2429.9	2427.7	2442.6	2429.9
175°	2450.7	2444.8	2440.4	2455.1	2442.6
177.5°	2458.9	2452.9	2448.5	2461.1	2448.5
180°	2455.1	2455.1	2455.1	2455.1	2455.1

TEST NUMBER: P911150

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.41	7.10	7.54	8.21	9.75	2.38	3.07	3.50	4.18	5.72
	3H	8.08	8.69	9.21	9.81	11.37	3.55	4.16	4.68	5.29	6.84
	4H	8.67	9.25	9.81	10.38	11.94	3.99	4.57	5.13	5.69	7.26
	6H	9.08	9.62	10.23	10.74	12.31	4.30	4.83	5.45	5.96	7.53
	8H	9.20	9.71	10.35	10.85	12.42	4.38	4.89	5.53	6.03	7.60
	12H	9.26	9.74	10.41	10.87	12.46	4.42	4.90	5.57	6.03	7.62
4H	2H	6.41	6.99	7.56	8.12	9.68	2.95	3.54	4.10	4.66	6.22
	3H	8.22	8.71	9.37	9.85	11.43	4.28	4.77	5.44	5.92	7.49
	4H	8.90	9.35	10.06	10.48	12.08	4.82	5.27	5.98	6.40	8.00
	6H	9.40	9.79	10.57	10.94	12.53	5.23	5.61	6.39	6.77	8.35
	8H	9.57	9.93	10.73	11.08	12.68	5.35	5.70	6.51	6.85	8.46
	12H	9.66	9.98	10.83	11.14	12.75	5.40	5.73	6.58	6.89	8.49
8H	4H	8.86	9.21	10.02	10.36	11.97	5.09	5.44	6.25	6.59	8.19
	6H	9.41	9.71	10.59	10.90	12.50	5.59	5.89	6.77	7.08	8.68
	8H	9.62	9.88	10.81	11.05	12.67	5.78	6.03	6.96	7.20	8.82
	12H	9.75	9.98	10.94	11.15	12.80	5.89	6.11	7.07	7.28	8.93
12H	4H	8.80	9.13	9.98	10.29	11.89	5.08	5.41	6.26	6.57	8.17
	6H	9.39	9.64	10.57	10.81	12.43	5.64	5.89	6.82	7.07	8.68
	8H	9.60	9.82	10.78	10.99	12.64	5.84	6.06	7.03	7.23	8.88

END OF REPORT