

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903328

Luminaire Tested: DFN2DIP-PN4F0-090D050US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903328
REPORT IS A COMBINATION OF REPORTS P899637 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D050US830-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12568.8 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 126
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903328
CATALOG NUMBER: DFN2DIP-PN4F0-090D050US830-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P903328

CATALOG NUMBER: DFN2DIP-PN4F0-090D050US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				67
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	61	56				56
2	93	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47				47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40				40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	37	34				34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30				30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23				23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	30	26	23	21				21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17				17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2409	2409	2409
5°	2413	2376	2392
10°	2394	2344	2360
15°	2359	2306	2310
20°	2311	2253	2259
25°	2264	2189	2199
30°	2204	2130	2124
35°	2148	2060	2043
40°	2079	1989	1967
45°	2010	1918	1889
50°	1935	1844	1799
55°	1856	1758	1716
60°	1766	1655	1621
65°	1669	1550	1509
70°	1545	1421	1389
75°	1373	1267	1278
80°	1167	1070	1066
85°	844	730	713

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2010 cd/sqm



TEST NUMBER: P903328

CATALOG NUMBER: DFN2DIP-PN4F0-090D050US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.7	2.5
10°-20°	874.1	7.0
20°-30°	1284.6	10.2
30°-40°	1492.0	11.9
40°-50°	1490.1	11.9
50°-60°	1299.3	10.3
60°-70°	960.5	7.6
70°-80°	543.4	4.3
80°-90°	147.7	1.2
90°-100°	92.2	0.7
100°-110°	293.0	2.3
110°-120°	501.5	4.0
120°-130°	659.5	5.2
130°-140°	740.3	5.9
140°-150°	725.9	5.8
150°-160°	609.0	4.8
160°-170°	403.9	3.2
170°-180°	141.2	1.1
0°-30°	2469.3	19.6
0°-40°	3961.3	31.5
0°-60°	6750.7	53.7
0°-90°	8402.3	66.9
90°-120°	886.7	7.1
90°-150°	3012.5	24.0
90°-180°	4167.0	33.2
0°-180°	12568.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3301	3301	3301	3301	3301	
5°	3301	3288	3253	3278	3272	313
15°	3142	3123	3082	3095	3079	885
25°	2844	2818	2765	2771	2765	1309
35°	2454	2422	2371	2352	2336	1532
45°	1996	1974	1926	1892	1879	1541
55°	1511	1492	1454	1416	1400	1351
65°	1019	1000	968	940	924	1007
75°	533	527	511	492	498	569
85°	130	127	124	114	111	145
90°	1	16	44	41	43	12
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	



TEST NUMBER: P903328

CATALOG NUMBER: DFN2DIP-PN4F0-090D050US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3300.7	3300.7	3300.7	3300.7	3300.7
2.5°	3319.9	3304.1	3269.1	3300.7	3294.7
5°	3300.7	3288.2	3253.3	3278.5	3272.4
7.5°	3278.5	3259.7	3224.6	3250.3	3243.9
10°	3243.9	3221.6	3183.5	3208.8	3199.4
12.5°	3196.0	3177.1	3139.1	3154.9	3148.6
15°	3142.2	3123.3	3081.8	3094.6	3078.8
17.5°	3075.4	3056.6	3015.2	3031.0	3015.2
20°	3002.4	2983.5	2939.0	2948.5	2936.0
22.5°	2929.6	2901.1	2859.6	2859.6	2853.2
25°	2843.7	2818.5	2764.7	2770.7	2764.7
27.5°	2748.5	2726.2	2685.2	2675.8	2659.9
30°	2653.5	2627.9	2580.4	2571.0	2558.2
32.5°	2551.8	2533.0	2482.1	2463.0	2450.1
35°	2453.5	2421.9	2371.0	2351.8	2336.0
37.5°	2342.4	2313.8	2262.9	2240.7	2224.9
40°	2228.2	2202.6	2151.7	2123.5	2110.7
42.5°	2117.0	2091.5	2041.0	2009.0	1990.2
45°	1996.5	1974.3	1926.5	1891.8	1879.1
47.5°	1879.1	1856.8	1805.9	1770.9	1752.1
50°	1755.1	1739.3	1694.8	1650.4	1634.6
52.5°	1634.6	1612.3	1571.2	1536.2	1514.0
55°	1511.0	1491.8	1453.7	1415.7	1399.9
57.5°	1387.0	1371.2	1329.8	1291.8	1278.9
60°	1263.1	1250.7	1206.2	1171.2	1161.8
62.5°	1142.5	1120.3	1088.6	1057.1	1044.2
65°	1019.0	999.8	968.1	939.5	923.7
67.5°	892.0	875.9	847.5	825.4	812.6
70°	774.5	761.7	733.1	710.9	698.4
72.5°	653.9	641.1	625.3	603.1	593.7
75°	533.1	527.0	510.9	492.0	498.4
77.5°	425.3	412.6	406.1	396.7	387.3
80°	317.5	314.1	307.7	298.3	292.0
82.5°	215.8	215.8	212.8	200.0	200.0
85°	130.0	127.0	123.9	114.1	111.1
87.5°	57.2	50.8	44.5	35.1	31.7
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3



TEST NUMBER: P903328

CATALOG NUMBER: DFN2DIP-PN4F0-090D050US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4



TEST NUMBER: P903328
 CATALOG NUMBER: DFN2DIP-PN4F0-090D050US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.76	12.80	12.56	13.62	14.62	11.32	12.36	12.12	13.18	14.18
	3H	13.44	14.37	14.25	15.20	16.23	12.95	13.88	13.76	14.71	15.75
	4H	14.03	14.91	14.86	15.75	16.80	13.55	14.42	14.37	15.26	16.31
	6H	14.44	15.25	15.28	16.10	17.16	13.95	14.76	14.79	15.61	16.67
	8H	14.55	15.33	15.40	16.19	17.25	14.06	14.84	14.91	15.70	16.76
	12H	14.61	15.35	15.46	16.20	17.29	14.11	14.85	14.97	15.70	16.79
4H	2H	12.24	13.12	13.07	13.96	15.01	11.89	12.77	12.72	13.61	14.66
	3H	14.13	14.86	14.97	15.73	16.80	13.72	14.46	14.57	15.33	16.39
	4H	14.85	15.52	15.71	16.39	17.48	14.43	15.10	15.29	15.97	17.06
	6H	15.38	15.96	16.25	16.85	17.94	14.95	15.53	15.83	16.42	17.52
	8H	15.53	16.07	16.41	16.96	18.07	15.10	15.65	15.98	16.53	17.64
	12H	15.62	16.10	16.51	17.01	18.12	15.18	15.66	16.07	16.57	17.68
8H	4H	15.06	15.60	15.94	16.49	17.60	14.69	15.23	15.57	16.12	17.23
	6H	15.70	16.15	16.61	17.08	18.19	15.33	15.77	16.23	16.70	17.81
	8H	15.93	16.32	16.84	17.25	18.37	15.54	15.94	16.46	16.86	17.99
	12H	16.07	16.42	16.99	17.33	18.51	15.67	16.02	16.58	16.93	18.11
12H	4H	15.05	15.54	15.95	16.45	17.56	14.69	15.18	15.59	16.09	17.20
	6H	15.73	16.13	16.65	17.05	18.18	15.37	15.77	16.28	16.69	17.81
	8H	15.99	16.34	16.90	17.25	18.43	15.61	15.96	16.53	16.88	18.06