

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903384

Luminaire Tested: DFN2DIP-PN4F0-100D100US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903384
REPORT IS A COMBINATION OF REPORTS P899729 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D100US830-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17672.7 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 175.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903384

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903384

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2677	2677	2677
5°	2681	2640	2658
10°	2660	2605	2623
15°	2621	2562	2567
20°	2568	2503	2510
25°	2515	2432	2444
30°	2449	2366	2359
35°	2387	2289	2270
40°	2310	2210	2186
45°	2233	2131	2099
50°	2150	2049	1999
55°	2062	1953	1907
60°	1963	1839	1801
65°	1855	1722	1677
70°	1717	1579	1543
75°	1526	1407	1420
80°	1296	1189	1184
85°	937	812	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2335 cd/sqm

TEST NUMBER: P903384

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	2.0
10°-20°	971.2	5.5
20°-30°	1427.3	8.1
30°-40°	1657.7	9.4
40°-50°	1655.7	9.4
50°-60°	1443.7	8.2
60°-70°	1067.2	6.0
70°-80°	603.8	3.4
80°-90°	167.9	0.9
90°-100°	184.5	1.0
100°-110°	586.1	3.3
110°-120°	1003.0	5.7
120°-130°	1319.1	7.5
130°-140°	1480.6	8.4
140°-150°	1451.9	8.2
150°-160°	1217.9	6.9
160°-170°	807.7	4.6
170°-180°	282.3	1.6
0°-30°	2743.7	15.5
0°-40°	4401.4	24.9
0°-60°	7500.8	42.4
0°-90°	9339.7	52.8
90°-120°	1773.5	10.0
90°-150°	6025.1	34.1
90°-180°	8333.0	47.2
0°-180°	17672.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3668	3668	3668	3668	3668	
5°	3668	3654	3615	3643	3636	348
15°	3491	3470	3424	3438	3421	983
25°	3160	3132	3072	3078	3072	1454
35°	2726	2691	2634	2613	2596	1702
45°	2218	2194	2140	2102	2088	1712
55°	1679	1658	1615	1573	1555	1501
65°	1132	1111	1076	1044	1026	1119
75°	592	586	568	547	554	632
85°	144	141	138	127	124	161
90°	3	32	88	83	85	17
95°	131	156	161	161	156	146
105°	541	548	554	558	558	571
115°	1006	1021	1016	1014	1006	996
125°	1464	1486	1479	1471	1468	1308
135°	1894	1921	1927	1924	1917	1464
145°	2299	2317	2331	2334	2324	1436
155°	2629	2636	2644	2656	2648	1210
165°	2860	2857	2857	2875	2862	807
175°	2976	2968	2963	2981	2966	283
180°	2981	2981	2981	2981	2981	

TEST NUMBER: P903384

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3667.5	3667.5	3667.5	3667.5	3667.5
2.5°	3688.8	3671.2	3632.3	3667.5	3660.7
5°	3667.5	3653.7	3614.7	3642.8	3636.0
7.5°	3642.8	3621.8	3582.9	3611.4	3604.3
10°	3604.3	3579.6	3537.3	3565.4	3554.9
12.5°	3551.1	3530.2	3487.9	3505.5	3498.3
15°	3491.3	3470.3	3424.3	3438.5	3421.0
17.5°	3417.2	3396.3	3350.2	3367.8	3350.2
20°	3335.9	3315.0	3265.6	3276.1	3262.2
22.5°	3255.2	3223.4	3177.3	3177.3	3170.2
25°	3159.8	3131.7	3071.8	3078.5	3071.8
27.5°	3053.8	3029.1	2983.5	2973.1	2955.4
30°	2948.4	2919.9	2867.1	2856.7	2842.4
32.5°	2835.4	2814.4	2757.9	2736.6	2722.3
35°	2726.1	2691.0	2634.4	2613.1	2595.5
37.5°	2602.6	2570.8	2514.3	2489.6	2472.0
40°	2475.8	2447.3	2390.9	2359.5	2345.2
42.5°	2352.3	2323.8	2267.8	2232.2	2211.3
45°	2218.4	2193.7	2140.5	2102.0	2087.8
47.5°	2087.8	2063.1	2006.6	1967.7	1946.7
50°	1950.1	1932.5	1883.1	1833.7	1816.2
52.5°	1816.2	1791.5	1745.8	1706.9	1682.2
55°	1678.9	1657.6	1615.2	1572.9	1555.4
57.5°	1541.2	1523.5	1477.5	1435.3	1421.1
60°	1403.4	1389.6	1340.2	1301.3	1290.8
62.5°	1269.5	1244.8	1209.7	1174.5	1160.3
65°	1132.2	1110.9	1075.7	1043.9	1026.3
67.5°	991.2	973.2	941.8	917.1	902.9
70°	860.5	846.3	814.5	789.9	776.0
72.5°	726.6	712.4	694.8	670.1	659.6
75°	592.3	585.6	567.6	546.7	553.7
77.5°	472.6	458.4	451.2	440.7	430.3
80°	352.8	349.1	342.0	331.5	324.4
82.5°	239.9	239.9	236.5	222.3	222.3
85°	144.4	141.1	137.7	126.9	123.5
87.5°	63.6	56.5	49.4	38.9	35.2
90°	2.7	32.3	88.0	82.7	85.4
92.5°	55.7	75.5	78.2	80.9	80.9
95°	131.2	156.4	160.9	160.9	156.4
97.5°	218.4	241.8	251.7	251.7	251.7
100°	319.1	339.7	346.9	346.9	344.2
102.5°	425.1	440.4	450.3	452.9	450.3
105°	541.0	548.2	553.6	558.1	558.1
107.5°	656.0	666.8	666.8	668.6	656.0
110°	767.5	781.8	781.8	781.8	774.7

TEST NUMBER: P903384

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	887.9	903.1	900.5	893.2	887.9
115°	1006.5	1020.9	1016.4	1013.7	1006.5
117.5°	1124.3	1144.1	1131.4	1124.3	1117.0
120°	1242.8	1262.6	1242.8	1242.8	1234.8
122.5°	1350.7	1375.8	1363.3	1356.1	1350.7
125°	1464.0	1486.4	1479.2	1471.1	1468.5
127.5°	1574.5	1602.3	1592.4	1581.7	1574.5
130°	1677.8	1710.1	1705.7	1700.3	1690.4
132.5°	1793.8	1818.9	1820.7	1808.2	1800.9
135°	1893.5	1921.4	1926.7	1924.1	1916.8
137.5°	2005.0	2027.4	2031.9	2030.1	2019.3
140°	2102.9	2125.3	2138.0	2138.0	2128.1
142.5°	2203.6	2226.0	2233.2	2235.9	2226.0
145°	2298.8	2316.8	2331.2	2333.8	2323.9
147.5°	2384.2	2406.7	2417.4	2422.0	2412.1
150°	2472.3	2487.6	2497.5	2505.5	2497.5
152.5°	2550.4	2565.7	2578.3	2588.2	2578.3
155°	2628.7	2635.8	2643.9	2656.5	2648.4
157.5°	2696.0	2701.4	2705.9	2723.9	2711.3
160°	2756.3	2761.6	2764.3	2779.6	2768.8
162.5°	2812.0	2812.0	2814.6	2831.7	2819.1
165°	2859.6	2856.8	2856.8	2874.8	2862.3
167.5°	2902.7	2894.6	2894.6	2912.6	2900.0
170°	2935.1	2927.9	2925.2	2943.2	2927.9
172.5°	2957.5	2950.3	2947.6	2965.6	2950.3
175°	2975.5	2968.3	2963.0	2980.9	2965.6
177.5°	2985.4	2978.2	2972.8	2988.0	2972.8
180°	2980.9	2980.9	2980.9	2980.9	2980.9

TEST NUMBER: P903384

CATALOG NUMBER: DFN2DIP-PN4F0-100D100US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.96	11.85	11.89	12.80	14.03	10.52	11.41	11.45	12.36	13.59
	3H	12.62	13.42	13.57	14.38	15.63	12.14	12.94	13.08	13.89	15.15
	4H	13.21	13.97	14.17	14.93	16.19	12.73	13.48	13.69	14.44	15.71
	6H	13.62	14.31	14.59	15.28	16.56	13.13	13.82	14.10	14.79	16.06
	8H	13.72	14.39	14.70	15.37	16.64	13.23	13.89	14.21	14.88	16.15
	12H	13.78	14.40	14.76	15.38	16.68	13.28	13.90	14.26	14.88	16.18
4H	2H	11.42	12.18	12.39	13.14	14.40	11.07	11.83	12.04	12.79	14.05
	3H	13.29	13.92	14.27	14.92	16.19	12.89	13.52	13.87	14.51	15.79
	4H	14.01	14.59	15.00	15.57	16.87	13.59	14.17	14.58	15.16	16.46
	6H	14.53	15.03	15.53	16.04	17.34	14.11	14.60	15.10	15.61	16.91
	8H	14.68	15.15	15.68	16.15	17.46	14.26	14.72	15.25	15.72	17.03
	12H	14.76	15.18	15.77	16.20	17.52	14.32	14.74	15.33	15.76	17.08
8H	4H	14.21	14.67	15.21	15.68	16.99	13.84	14.30	14.84	15.31	16.62
	6H	14.85	15.23	15.87	16.28	17.59	14.47	14.85	15.49	15.90	17.21
	8H	15.07	15.41	16.10	16.44	17.77	14.69	15.02	15.71	16.06	17.38
	12H	15.20	15.50	16.24	16.53	17.90	14.80	15.10	15.84	16.13	17.50
12H	4H	14.20	14.62	15.21	15.64	16.95	13.84	14.25	14.85	15.27	16.59
	6H	14.88	15.22	15.91	16.25	17.58	14.51	14.85	15.54	15.88	17.21
	8H	15.12	15.42	16.16	16.45	17.82	14.75	15.05	15.78	16.07	17.45

END OF REPORT