

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903406

Luminaire Tested: DFN2DIP-PN4F0-110D060US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903406
REPORT IS A COMBINATION OF REPORTS P899660 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D060US830-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13817.7 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 159.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903406

CATALOG NUMBER: DFN2DIP-PN4F0-110D060US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903406

CATALOG NUMBER: DFN2DIP-PN4F0-110D060US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	94	90	95	92	88	85	81	78	76	71	69	67	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39
5	72	61	53	47	68	58	50	45	51	46	41	46	41	38	40	37	34
6	67	55	47	41	63	52	45	39	47	41	36	42	37	33	37	33	30
7	62	50	42	36	58	47	40	35	43	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	25
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	48	37	30	26	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3128	3128	3128
5°	3133	3079	3099
10°	3102	3019	2998
15°	3059	2919	2843
20°	3003	2782	2652
25°	2945	2628	2468
30°	2867	2471	2234
35°	2791	2301	2028
40°	2714	2125	1793
45°	2624	1931	1579
50°	2531	1734	1370
55°	2433	1524	1170
60°	2321	1304	963
65°	2192	1080	868
70°	2035	872	786
75°	1838	769	717
80°	1552	647	624
85°	1081	434	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2624 cd/sqm

TEST NUMBER: P903406

CATALOG NUMBER: DFN2DIP-PN4F0-110D060US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	2.9
10°-20°	1102.5	8.0
20°-30°	1547.8	11.2
30°-40°	1687.2	12.2
40°-50°	1550.8	11.2
50°-60°	1217.9	8.8
60°-70°	792.7	5.7
70°-80°	408.1	3.0
80°-90°	109.3	0.8
90°-100°	110.7	0.8
100°-110°	351.6	2.5
110°-120°	601.8	4.4
120°-130°	791.4	5.7
130°-140°	888.4	6.4
140°-150°	871.1	6.3
150°-160°	730.8	5.3
160°-170°	484.6	3.5
170°-180°	169.4	1.2
0°-30°	3051.9	22.1
0°-40°	4739.1	34.3
0°-60°	7507.8	54.3
0°-90°	8817.8	63.8
90°-120°	1064.1	7.7
90°-150°	3615.0	26.2
90°-180°	5000.0	36.2
0°-180°	13817.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4285	4285	4285	4285	4285	
5°	4285	4266	4215	4250	4239	406
15°	4076	4033	3901	3828	3789	1148
25°	3700	3575	3319	3161	3102	1701
35°	3188	2990	2649	2404	2319	1995
45°	2606	2346	1939	1663	1570	2013
55°	1981	1679	1260	1028	954	1771
65°	1338	1024	675	543	531	1326
75°	713	442	310	283	279	755
85°	167	85	74	74	74	191
90°	2	19	53	50	51	14
95°	79	94	96	96	94	88
105°	325	329	332	335	335	343
115°	604	613	610	608	604	597
125°	878	892	888	883	881	785
135°	1136	1153	1156	1154	1150	878
145°	1379	1390	1399	1400	1394	862
155°	1577	1582	1586	1594	1589	726
165°	1716	1714	1714	1725	1717	484
175°	1785	1781	1778	1789	1779	170
180°	1789	1789	1789	1789	1789	

TEST NUMBER: P903406

CATALOG NUMBER: DFN2DIP-PN4F0-110D060US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4285.1	4285.1	4285.1	4285.1	4285.1
2.5°	4304.4	4285.1	4242.3	4281.4	4273.6
5°	4285.1	4265.8	4215.1	4250.1	4238.6
7.5°	4250.1	4227.0	4172.7	4188.0	4168.6
10°	4203.6	4176.4	4099.1	4087.1	4064.1
12.5°	4145.6	4110.6	4005.7	3982.6	3939.8
15°	4075.6	4032.9	3901.2	3827.6	3788.8
17.5°	3994.2	3932.1	3769.1	3683.9	3621.8
20°	3901.2	3823.4	3629.6	3532.9	3447.3
22.5°	3800.4	3711.1	3486.1	3354.4	3296.4
25°	3699.6	3575.3	3319.4	3160.6	3102.2
27.5°	3579.5	3447.3	3164.3	2982.0	2892.8
30°	3451.5	3303.8	2993.6	2796.1	2691.1
32.5°	3327.3	3148.7	2831.0	2598.2	2501.1
35°	3187.8	2989.8	2648.8	2404.4	2318.8
37.5°	3052.0	2838.5	2478.0	2210.2	2113.6
40°	2908.4	2676.0	2299.5	2024.2	1923.4
42.5°	2761.1	2513.0	2121.4	1834.2	1737.5
45°	2606.0	2346.0	1939.1	1663.4	1570.5
47.5°	2458.7	2183.5	1764.6	1488.9	1403.8
50°	2295.8	2020.5	1593.9	1326.1	1245.0
52.5°	2136.6	1845.7	1431.0	1175.1	1101.4
55°	1981.4	1679.0	1260.2	1027.7	954.1
57.5°	1822.7	1512.4	1109.2	892.0	829.8
60°	1659.7	1349.5	950.0	752.5	690.4
62.5°	1500.9	1190.7	814.3	628.3	597.4
65°	1337.9	1023.6	674.8	543.1	531.1
67.5°	1182.9	868.6	543.1	476.8	465.3
70°	1019.9	717.6	449.7	411.0	395.4
72.5°	864.8	577.7	376.1	345.2	337.3
75°	713.4	441.9	310.2	283.0	279.4
77.5°	562.4	314.0	244.4	228.8	220.9
80°	422.5	225.1	186.0	170.8	170.8
82.5°	294.5	151.4	128.0	120.2	120.2
85°	166.6	85.2	73.6	73.6	73.6
87.5°	62.1	30.8	30.8	27.1	27.1
90°	1.6	19.4	52.9	49.6	51.2
92.5°	33.5	45.3	46.9	48.5	48.5
95°	78.7	93.8	96.5	96.5	93.8
97.5°	131.0	145.1	151.0	151.0	151.0
100°	191.4	203.8	208.1	208.1	206.5
102.5°	255.1	264.2	270.1	271.7	270.1
105°	324.6	328.9	332.2	334.9	334.9
107.5°	393.6	400.1	400.1	401.1	393.6
110°	460.5	469.1	469.1	469.1	464.8

TEST NUMBER: P903406

CATALOG NUMBER: DFN2DIP-PN4F0-110D060US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	532.7	541.9	540.3	535.9	532.7
115°	603.9	612.6	609.8	608.2	603.9
117.5°	674.6	686.5	678.8	674.6	670.2
120°	745.7	757.6	745.7	745.7	740.8
122.5°	810.4	825.5	817.9	813.7	810.4
125°	878.4	891.8	887.5	882.7	881.1
127.5°	944.7	961.4	955.5	949.0	944.7
130°	1006.7	1026.1	1023.4	1020.2	1014.3
132.5°	1076.3	1091.4	1092.4	1084.9	1080.5
135°	1136.1	1152.8	1156.0	1154.4	1150.1
137.5°	1203.0	1216.4	1219.2	1218.0	1211.6
140°	1261.8	1275.3	1282.8	1282.8	1276.9
142.5°	1322.1	1335.6	1339.9	1341.5	1335.6
145°	1379.3	1390.1	1398.7	1400.3	1394.4
147.5°	1430.5	1444.0	1450.5	1453.1	1447.2
150°	1483.4	1492.5	1498.5	1503.3	1498.5
152.5°	1530.2	1539.5	1547.0	1552.9	1547.0
155°	1577.2	1581.5	1586.3	1593.9	1589.0
157.5°	1617.6	1620.9	1623.5	1634.4	1626.8
160°	1653.8	1657.0	1658.6	1667.7	1661.3
162.5°	1687.2	1687.2	1688.8	1699.0	1691.5
165°	1715.7	1714.1	1714.1	1724.9	1717.4
167.5°	1741.6	1736.8	1736.8	1747.6	1740.0
170°	1761.0	1756.7	1755.1	1765.9	1756.7
172.5°	1774.5	1770.2	1768.6	1779.3	1770.2
175°	1785.3	1781.0	1777.7	1788.6	1779.3
177.5°	1791.2	1787.0	1783.7	1792.8	1783.7
180°	1788.6	1788.6	1788.6	1788.6	1788.6

TEST NUMBER: P903406

CATALOG NUMBER: DFN2DIP-PN4F0-110D060US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.32	13.27	13.15	14.13	15.19	8.28	9.24	9.12	10.09	11.15
	3H	14.01	14.86	14.86	15.73	16.82	9.48	10.34	10.33	11.20	12.29
	4H	14.62	15.43	15.49	16.30	17.40	9.94	10.74	10.80	11.61	12.71
	6H	15.05	15.80	15.93	16.67	17.79	10.27	11.01	11.14	11.89	13.00
	8H	15.18	15.89	16.07	16.79	17.90	10.36	11.07	11.25	11.96	13.07
	12H	15.25	15.93	16.14	16.81	17.95	10.41	11.08	11.30	11.97	13.11
4H	2H	12.35	13.16	13.22	14.03	15.13	8.89	9.70	9.76	10.57	11.67
	3H	14.19	14.86	15.08	15.77	16.88	10.26	10.93	11.14	11.83	12.94
	4H	14.89	15.50	15.79	16.40	17.54	10.81	11.42	11.70	12.32	13.46
	6H	15.42	15.94	16.33	16.87	18.01	11.24	11.76	12.14	12.69	13.83
	8H	15.60	16.09	16.51	17.01	18.16	11.37	11.86	12.28	12.78	13.93
	12H	15.70	16.14	16.63	17.08	18.24	11.44	11.88	12.37	12.82	13.98
8H	4H	14.87	15.36	15.78	16.28	17.44	11.10	11.59	12.01	12.51	13.67
	6H	15.44	15.85	16.38	16.81	17.97	11.63	12.03	12.56	12.99	14.15
	8H	15.66	16.02	16.61	16.97	18.15	11.82	12.18	12.76	13.13	14.30
	12H	15.81	16.13	16.76	17.07	18.29	11.94	12.26	12.89	13.20	14.43
12H	4H	14.83	15.27	15.76	16.21	17.37	11.11	11.55	12.04	12.49	13.65
	6H	15.42	15.78	16.37	16.73	17.90	11.68	12.04	12.62	12.99	14.16
	8H	15.65	15.96	16.60	16.91	18.13	11.89	12.21	12.84	13.15	14.38