

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903424

Luminaire Tested: DFN2DIP-PN4F0-110D110US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903424
REPORT IS A COMBINATION OF REPORTS P899749 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D110US830-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19439.9 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 205.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903424

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903424

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		71	71	71		59
1	98	94	90	87	91	87	84	81	74	72	70		63	61	59		52
2	90	82	76	71	83	76	71	66	65	61	58		55	52	50		46
3	82	72	65	59	75	67	61	55	58	53	49		49	45	42		41
4	75	64	56	50	69	60	52	47	51	46	41		43	39	36		36
5	69	57	49	43	63	53	46	40	46	40	36		39	35	31		33
6	63	51	43	37	58	48	40	35	41	36	31		35	31	27		30
7	59	46	38	33	54	43	36	31	37	32	28		32	28	24		27
8	54	42	34	29	50	39	32	27	34	29	24		29	25	22		25
9	51	38	31	26	47	36	29	24	31	26	22		27	23	19		23
10	47	35	28	23	44	33	26	22	29	23	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2945	2945	2945
5°	2950	2904	2924
10°	2926	2865	2885
15°	2883	2819	2824
20°	2824	2754	2761
25°	2767	2676	2688
30°	2694	2603	2595
35°	2625	2517	2498
40°	2541	2431	2404
45°	2457	2344	2309
50°	2364	2253	2199
55°	2268	2148	2097
60°	2159	2023	1981
65°	2040	1894	1844
70°	1889	1737	1697
75°	1678	1548	1562
80°	1426	1308	1303
85°	1031	893	871

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2567 cd/sqm

TEST NUMBER: P903424

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.7	2.0
10°-20°	1068.3	5.5
20°-30°	1570.0	8.1
30°-40°	1823.5	9.4
40°-50°	1821.2	9.4
50°-60°	1588.0	8.2
60°-70°	1173.9	6.0
70°-80°	664.2	3.4
80°-90°	184.6	0.9
90°-100°	202.9	1.0
100°-110°	644.7	3.3
110°-120°	1103.3	5.7
120°-130°	1451.0	7.5
130°-140°	1628.6	8.4
140°-150°	1597.1	8.2
150°-160°	1339.7	6.9
160°-170°	888.5	4.6
170°-180°	310.5	1.6
0°-30°	3018.1	15.5
0°-40°	4841.6	24.9
0°-60°	8250.9	42.4
0°-90°	10273.6	52.8
90°-120°	1950.9	10.0
90°-150°	6627.6	34.1
90°-180°	9166.0	47.2
0°-180°	19439.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4034	4034	4034	4034	4034	
5°	4034	4019	3976	4007	4000	383
15°	3840	3817	3767	3782	3763	1082
25°	3476	3445	3379	3386	3379	1599
35°	2999	2960	2898	2874	2855	1873
45°	2440	2413	2355	2312	2297	1883
55°	1847	1823	1777	1730	1711	1651
65°	1245	1222	1183	1148	1129	1231
75°	652	644	624	601	609	696
85°	159	155	152	140	136	177
90°	3	36	97	91	94	19
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2114	2119	2116	2109	1610
145°	2529	2548	2564	2567	2556	1580
155°	2892	2899	2908	2922	2913	1331
165°	3146	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	

TEST NUMBER: P903424

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4034.3	4034.3	4034.3	4034.3	4034.3
2.5°	4057.6	4038.3	3995.5	4034.3	4026.8
5°	4034.3	4019.0	3976.2	4007.0	3999.7
7.5°	4007.0	3984.0	3941.2	3972.5	3964.7
10°	3964.7	3937.5	3891.0	3921.8	3910.3
12.5°	3906.3	3883.2	3836.7	3856.0	3848.2
15°	3840.4	3817.3	3766.7	3782.3	3763.0
17.5°	3758.9	3735.9	3685.2	3704.6	3685.2
20°	3669.6	3646.5	3592.2	3603.7	3588.5
22.5°	3580.7	3545.7	3495.0	3495.0	3487.2
25°	3475.7	3444.9	3379.0	3386.5	3379.0
27.5°	3359.2	3332.1	3281.8	3270.3	3251.0
30°	3243.2	3211.9	3153.8	3142.3	3126.7
32.5°	3118.9	3095.9	3033.7	3010.2	2994.6
35°	2998.7	2960.1	2897.8	2874.4	2855.1
37.5°	2862.9	2827.9	2765.8	2738.6	2719.2
40°	2723.4	2692.1	2630.0	2595.4	2579.7
42.5°	2587.6	2556.3	2494.5	2455.4	2432.4
45°	2440.2	2413.0	2354.6	2312.2	2296.6
47.5°	2296.6	2269.5	2207.2	2164.5	2141.4
50°	2145.1	2125.8	2071.4	2017.1	1997.8
52.5°	1997.8	1970.6	1920.4	1877.5	1850.4
55°	1846.7	1823.3	1776.8	1730.2	1710.9
57.5°	1695.3	1675.9	1625.3	1578.8	1563.1
60°	1543.8	1528.6	1474.2	1431.4	1419.9
62.5°	1396.5	1369.3	1330.6	1291.9	1276.3
65°	1245.4	1221.9	1183.3	1148.3	1129.0
67.5°	1090.2	1070.5	1035.9	1008.8	993.2
70°	946.6	930.9	896.0	868.8	853.6
72.5°	799.3	783.6	764.3	737.2	725.6
75°	651.5	644.1	624.3	601.3	609.2
77.5°	519.8	504.2	496.3	484.8	473.3
80°	388.1	384.0	376.2	364.7	356.8
82.5°	263.8	263.8	260.1	244.5	244.5
85°	158.9	155.1	151.5	139.5	135.8
87.5°	69.9	62.1	54.3	42.8	38.6
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.3	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	609.0	613.9	613.9
107.5°	721.6	733.5	733.5	735.5	721.6
110°	844.2	860.1	860.1	860.1	852.2

TEST NUMBER: P903424

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US830-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	976.7	993.4	990.5	982.6	976.7
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.4	1244.5	1236.7	1228.8
120°	1367.2	1388.9	1367.2	1367.2	1358.3
122.5°	1485.8	1513.4	1499.6	1491.7	1485.8
125°	1610.3	1635.0	1627.1	1618.3	1615.2
127.5°	1731.9	1762.6	1751.7	1739.8	1731.9
130°	1845.6	1881.2	1876.2	1870.3	1859.4
132.5°	1973.1	2000.8	2002.8	1989.0	1981.0
135°	2082.8	2113.5	2119.4	2116.5	2108.6
137.5°	2205.5	2230.1	2235.1	2233.1	2221.3
140°	2313.2	2337.9	2351.7	2351.7	2340.9
142.5°	2423.9	2448.6	2456.5	2459.5	2448.6
145°	2528.7	2548.4	2564.3	2567.2	2556.4
147.5°	2622.6	2647.3	2659.2	2664.1	2653.3
150°	2719.5	2736.3	2747.1	2756.1	2747.1
152.5°	2805.5	2822.3	2836.1	2847.0	2836.1
155°	2891.5	2899.4	2908.3	2922.2	2913.2
157.5°	2965.6	2971.6	2976.5	2996.2	2982.4
160°	3031.9	3037.8	3040.7	3057.6	3045.7
162.5°	3093.1	3093.1	3096.2	3114.9	3101.1
165°	3145.5	3142.5	3142.5	3162.3	3148.5
167.5°	3193.0	3184.1	3184.1	3203.9	3190.0
170°	3228.6	3220.7	3217.7	3237.4	3220.7
172.5°	3253.3	3245.4	3242.4	3262.2	3245.4
175°	3273.1	3265.2	3259.2	3279.0	3262.2
177.5°	3283.9	3276.0	3270.1	3286.9	3270.1
180°	3279.0	3279.0	3279.0	3279.0	3279.0

TEST NUMBER: P903424

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.29	12.18	12.22	13.13	14.36	10.85	11.74	11.78	12.69	13.92
	3H	12.95	13.75	13.90	14.71	15.96	12.47	13.27	13.41	14.23	15.48
	4H	13.55	14.30	14.50	15.26	16.52	13.06	13.81	14.02	14.78	16.04
	6H	13.95	14.64	14.92	15.61	16.89	13.46	14.15	14.43	15.12	16.40
	8H	14.06	14.72	15.03	15.70	16.98	13.56	14.22	14.54	15.21	16.48
	12H	14.11	14.74	15.09	15.72	17.01	13.61	14.24	14.59	15.22	16.51
4H	2H	11.75	12.51	12.72	13.47	14.73	11.40	12.16	12.37	13.12	14.38
	3H	13.63	14.25	14.60	15.25	16.52	13.22	13.85	14.20	14.85	16.12
	4H	14.34	14.92	15.33	15.90	17.21	13.93	14.50	14.91	15.49	16.79
	6H	14.86	15.36	15.86	16.37	17.67	14.44	14.93	15.43	15.94	17.24
	8H	15.01	15.48	16.01	16.48	17.79	14.59	15.05	15.58	16.05	17.37
	12H	15.09	15.51	16.11	16.53	17.85	14.65	15.07	15.67	16.09	17.41
8H	4H	14.54	15.01	15.54	16.01	17.32	14.17	14.63	15.17	15.64	16.95
	6H	15.18	15.56	16.20	16.61	17.92	14.80	15.18	15.82	16.23	17.54
	8H	15.40	15.74	16.43	16.77	18.10	15.02	15.35	16.05	16.39	17.72
	12H	15.54	15.83	16.57	16.86	18.23	15.13	15.43	16.17	16.46	17.83
12H	4H	14.53	14.95	15.54	15.97	17.29	14.17	14.59	15.18	15.60	16.92
	6H	15.21	15.55	16.24	16.58	17.91	14.84	15.18	15.87	16.21	17.54
	8H	15.45	15.75	16.49	16.78	18.15	15.08	15.38	16.11	16.41	17.78

END OF REPORT