

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911248

Luminaire Tested: DFN2DIP-PN3F0-070D040US850-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P911248  
REPORT IS A COMBINATION OF REPORTS P899533 AND P896399  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-070D040US850-FLLFLL  
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11611.2 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 99.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.946  
Total Harmonic Distortion (THDi): 0.132  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P911248  
CATALOG NUMBER: DFN2DIP-PN3F0-070D040US850-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P911248

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US850-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66			
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56			
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47			
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40			
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34			
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30			
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26			
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23			
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21			
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19			
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3531	3531	3531
5°	3535	3479	3504
10°	3504	3430	3455
15°	3450	3371	3379
20°	3378	3290	3302
25°	3307	3194	3213
30°	3218	3104	3100
35°	3134	2999	2980
40°	3030	2892	2866
45°	2926	2785	2750
50°	2813	2672	2615
55°	2694	2542	2491
60°	2560	2388	2348
65°	2413	2228	2180
70°	2226	2032	1999
75°	1967	1798	1829
80°	1655	1500	1509
85°	1167	993	984

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2926 cd/sqm



TEST NUMBER: P911248

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US850-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.3	2.4
10°-20°	799.9	6.9
20°-30°	1175.6	10.1
30°-40°	1365.3	11.8
40°-50°	1363.6	11.7
50°-60°	1189.1	10.2
60°-70°	879.0	7.6
70°-80°	497.3	4.3
80°-90°	135.3	1.2
90°-100°	86.8	0.7
100°-110°	275.8	2.4
110°-120°	472.0	4.1
120°-130°	620.8	5.3
130°-140°	696.8	6.0
140°-150°	683.3	5.9
150°-160°	573.2	4.9
160°-170°	380.1	3.3
170°-180°	132.9	1.1
0°-30°	2259.8	19.5
0°-40°	3625.1	31.2
0°-60°	6177.8	53.2
0°-90°	7689.4	66.2
90°-120°	834.7	7.2
90°-150°	2835.6	24.4
90°-180°	3922.0	33.8
0°-180°	11611.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	133
90°	1	15	42	39	40	11
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	



TEST NUMBER: P911248

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US850-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6



TEST NUMBER: P911248

CATALOG NUMBER: DFN2DIP-PN3F0-070D040US850-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9



TEST NUMBER: P911248  
 CATALOG NUMBER: DFN2DIP-PN3F0-070D040US850-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.99	14.02	13.80	14.85	15.87	12.55	13.58	13.36	14.41	15.43
	3H	14.66	15.58	15.48	16.42	17.47	14.18	15.10	14.99	15.94	16.98
	4H	15.25	16.12	16.08	16.97	18.03	14.76	15.64	15.60	16.48	17.54
	6H	15.65	16.46	16.50	17.31	18.38	15.16	15.97	16.01	16.82	17.89
	8H	15.76	16.53	16.62	17.40	18.47	15.27	16.04	16.13	16.91	17.98
	12H	15.81	16.54	16.67	17.41	18.51	15.32	16.05	16.18	16.91	18.01
4H	2H	13.47	14.34	14.31	15.19	16.24	13.12	13.99	13.96	14.84	15.89
	3H	15.34	16.07	16.19	16.95	18.02	14.94	15.67	15.79	16.55	17.62
	4H	16.06	16.72	16.92	17.60	18.70	15.64	16.31	16.51	17.18	18.28
	6H	16.58	17.15	17.46	18.05	19.16	16.16	16.73	17.03	17.63	18.73
	8H	16.73	17.27	17.61	18.16	19.28	16.30	16.84	17.18	17.73	18.85
	12H	16.81	17.29	17.71	18.20	19.33	16.37	16.85	17.27	17.77	18.89
8H	4H	16.27	16.80	17.15	17.70	18.81	15.90	16.43	16.78	17.33	18.44
	6H	16.90	17.34	17.81	18.28	19.39	16.52	16.97	17.43	17.90	19.02
	8H	17.11	17.51	18.03	18.44	19.57	16.73	17.13	17.65	18.05	19.19
	12H	17.25	17.60	18.17	18.52	19.70	16.85	17.20	17.77	18.12	19.30
12H	4H	16.26	16.74	17.16	17.65	18.78	15.90	16.38	16.80	17.29	18.42
	6H	16.93	17.32	17.85	18.25	19.38	16.56	16.96	17.48	17.88	19.02
	8H	17.17	17.52	18.09	18.44	19.62	16.80	17.15	17.72	18.07	19.25