

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911266

Luminaire Tested: DFN2DIP-PN3F0-070D080US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911266
REPORT IS A COMBINATION OF REPORTS P899590 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D080US850-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14450.2 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 130.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911266
CATALOG NUMBER: DFN2DIP-PN3F0-070D080US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P911266

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39				39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34				34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29				29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25				25
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22				22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16				16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15				15
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3751	3751	3751
5°	3754	3688	3713
10°	3715	3613	3591
15°	3662	3491	3402
20°	3592	3324	3172
25°	3520	3138	2950
30°	3425	2946	2668
35°	3331	2741	2421
40°	3236	2528	2137
45°	3125	2293	1880
50°	3011	2056	1630
55°	2891	1803	1389
60°	2752	1539	1142
65°	2592	1271	1026
70°	2398	1020	926
75°	2154	893	839
80°	1802	742	723
85°	1224	482	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3125 cd/sqm



TEST NUMBER: P911266

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.7	2.1
10°-20°	825.5	5.7
20°-30°	1158.9	8.0
30°-40°	1263.3	8.7
40°-50°	1161.1	8.0
50°-60°	911.9	6.3
60°-70°	593.5	4.1
70°-80°	305.5	2.1
80°-90°	86.0	0.6
90°-100°	173.6	1.2
100°-110°	551.7	3.8
110°-120°	944.1	6.5
120°-130°	1241.6	8.6
130°-140°	1393.7	9.6
140°-150°	1366.6	9.5
150°-160°	1146.4	7.9
160°-170°	760.3	5.3
170°-180°	265.7	1.8
0°-30°	2285.1	15.8
0°-40°	3548.4	24.6
0°-60°	5621.4	38.9
0°-90°	6606.5	45.7
90°-120°	1669.4	11.6
90°-150°	5671.3	39.2
90°-180°	7844.0	54.3
0°-180°	14450.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3208	3208	3208	3208	3208	
5°	3208	3194	3156	3182	3174	304
15°	3052	3020	2921	2866	2837	860
25°	2770	2677	2485	2366	2323	1274
35°	2387	2239	1983	1800	1736	1494
45°	1951	1756	1452	1246	1176	1507
55°	1484	1257	944	770	714	1326
65°	1002	766	505	407	398	993
75°	534	331	232	212	209	565
85°	125	64	55	55	55	143
90°	3	30	83	78	80	14
95°	124	147	151	151	147	137
105°	509	516	521	525	525	537
115°	947	961	957	954	947	937
125°	1378	1399	1392	1385	1382	1231
135°	1782	1809	1814	1811	1804	1378
145°	2164	2181	2194	2197	2188	1352
155°	2474	2481	2489	2500	2493	1139
165°	2692	2689	2689	2706	2694	759
175°	2801	2794	2789	2806	2792	266
180°	2806	2806	2806	2806	2806	



TEST NUMBER: P911266

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3208.4	3208.4	3208.4	3208.4	3208.4
2.5°	3222.9	3208.4	3176.4	3205.7	3199.8
5°	3208.4	3193.9	3156.1	3182.3	3173.6
7.5°	3182.3	3165.0	3124.4	3135.7	3121.3
10°	3147.5	3127.2	3069.2	3060.3	3043.0
12.5°	3104.0	3077.8	2999.3	2982.0	2949.9
15°	3051.6	3019.6	2921.0	2865.9	2836.9
17.5°	2990.6	2944.2	2822.2	2758.3	2711.8
20°	2921.0	2862.8	2717.7	2645.3	2581.2
22.5°	2845.6	2778.7	2610.1	2511.6	2468.2
25°	2770.1	2677.0	2485.4	2366.5	2322.8
27.5°	2680.1	2581.2	2369.3	2232.9	2166.0
30°	2584.3	2473.7	2241.4	2093.6	2015.1
32.5°	2491.3	2357.6	2119.7	1945.4	1872.7
35°	2386.8	2238.6	1983.3	1800.4	1736.3
37.5°	2285.2	2125.3	1855.5	1654.8	1582.5
40°	2177.6	2003.6	1721.7	1515.7	1440.1
42.5°	2067.4	1881.6	1588.3	1373.3	1301.0
45°	1951.3	1756.5	1451.9	1245.5	1175.9
47.5°	1840.9	1634.9	1321.3	1114.9	1051.1
50°	1719.0	1512.9	1193.4	992.9	932.2
52.5°	1599.7	1381.9	1071.4	879.8	824.7
55°	1483.6	1257.2	943.5	769.5	714.4
57.5°	1364.7	1132.4	830.5	667.8	621.4
60°	1242.7	1010.4	711.3	563.5	516.9
62.5°	1123.7	891.5	609.6	470.4	447.3
65°	1001.8	766.4	505.3	406.7	397.7
67.5°	885.6	650.3	406.7	357.0	348.4
70°	763.7	537.2	336.7	307.7	296.0
72.5°	647.5	432.5	281.6	258.5	252.6
75°	534.2	330.8	232.2	211.9	209.2
77.5°	421.1	235.0	183.0	171.2	165.5
80°	316.4	168.5	139.3	127.9	127.9
82.5°	220.6	113.3	95.8	89.9	89.9
85°	124.8	63.8	55.1	55.1	55.1
87.5°	46.5	23.1	23.1	20.3	20.3
90°	2.6	30.5	83.0	77.9	80.4
92.5°	52.5	71.1	73.6	76.1	76.1
95°	123.5	147.2	151.4	151.4	147.2
97.5°	205.6	227.6	236.9	236.9	236.9
100°	300.3	319.7	326.5	326.5	323.9
102.5°	400.1	414.5	423.7	426.3	423.7
105°	509.3	516.0	521.1	525.3	525.3
107.5°	617.5	627.7	627.7	629.4	617.5
110°	722.4	735.9	735.9	735.9	729.2



TEST NUMBER: P911266

CATALOG NUMBER: DFN2DIP-PN3F0-070D080US850-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	835.7	850.2	847.6	840.8	835.7
115°	947.4	960.9	956.7	954.2	947.4
117.5°	1058.2	1076.8	1065.0	1058.2	1051.4
120°	1169.9	1188.5	1169.9	1169.9	1162.2
122.5°	1271.4	1295.1	1283.2	1276.5	1271.4
125°	1377.9	1399.1	1392.3	1384.7	1382.3
127.5°	1482.1	1508.2	1498.9	1488.8	1482.1
130°	1579.3	1609.7	1605.5	1600.5	1591.2
132.5°	1688.5	1712.1	1713.8	1702.0	1695.2
135°	1782.3	1808.6	1813.7	1811.1	1804.3
137.5°	1887.2	1908.4	1912.6	1910.9	1900.7
140°	1979.5	2000.5	2012.4	2012.4	2003.1
142.5°	2074.2	2095.3	2102.1	2104.7	2095.3
145°	2163.9	2180.7	2194.3	2196.8	2187.5
147.5°	2244.2	2265.4	2275.4	2279.8	2270.5
150°	2327.1	2341.4	2350.7	2358.4	2350.7
152.5°	2400.7	2415.1	2426.9	2436.3	2426.9
155°	2474.3	2481.1	2488.7	2500.5	2492.9
157.5°	2537.7	2542.8	2547.0	2563.9	2552.1
160°	2594.4	2599.5	2602.0	2616.4	2606.3
162.5°	2646.9	2646.9	2649.4	2665.5	2653.6
165°	2691.7	2689.1	2689.1	2706.1	2694.2
167.5°	2732.2	2724.7	2724.7	2741.6	2729.7
170°	2762.7	2756.0	2753.4	2770.4	2756.0
172.5°	2783.9	2777.2	2774.6	2791.5	2777.2
175°	2800.8	2794.0	2788.9	2805.9	2791.5
177.5°	2810.1	2803.3	2798.2	2812.6	2798.2
180°	2805.9	2805.9	2805.9	2805.9	2805.9



TEST NUMBER: P911266
 CATALOG NUMBER: DFN2DIP-PN3F0-070D080US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.29	12.08	12.28	13.09	14.42	7.25	8.05	8.25	9.05	10.39
	3H	12.95	13.67	13.96	14.68	16.04	8.43	9.14	9.44	10.16	11.51
	4H	13.56	14.23	14.58	15.25	16.61	8.88	9.55	9.90	10.57	11.93
	6H	13.97	14.59	15.01	15.61	16.99	9.19	9.81	10.22	10.83	12.21
	8H	14.10	14.68	15.13	15.72	17.09	9.28	9.87	10.31	10.91	12.28
	12H	14.15	14.71	15.20	15.75	17.14	9.32	9.88	10.36	10.91	12.30
4H	2H	11.30	11.97	12.33	12.99	14.35	7.84	8.51	8.87	9.53	10.89
	3H	13.12	13.68	14.15	14.72	16.10	9.18	9.74	10.22	10.79	12.16
	4H	13.80	14.32	14.85	15.35	16.75	9.72	10.23	10.76	11.27	12.67
	6H	14.31	14.75	15.36	15.81	17.21	10.13	10.57	11.19	11.63	13.03
	8H	14.48	14.89	15.54	15.95	17.36	10.26	10.67	11.31	11.72	13.13
	12H	14.57	14.94	15.64	16.01	17.42	10.32	10.69	11.39	11.76	13.17
8H	4H	13.77	14.18	14.82	15.23	16.64	9.99	10.41	11.05	11.46	12.87
	6H	14.32	14.66	15.40	15.76	17.17	10.50	10.84	11.58	11.94	13.35
	8H	14.54	14.83	15.62	15.91	17.34	10.69	10.99	11.78	12.07	13.49
	12H	14.67	14.93	15.76	16.01	17.47	10.80	11.06	11.89	12.14	13.61
12H	4H	13.72	14.09	14.79	15.16	16.57	10.00	10.37	11.07	11.44	12.85
	6H	14.30	14.60	15.38	15.68	17.10	10.55	10.85	11.64	11.93	13.35
	8H	14.51	14.78	15.60	15.85	17.32	10.76	11.02	11.84	12.09	13.56