

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913872

Luminaire Tested: DFN2DIP-PN3F0-030D060US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913872
REPORT IS A COMBINATION OF REPORTS P899553 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D060US927-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6559.3 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913872

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913872

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1081	1081	1081
5°	1082	1065	1073
10°	1073	1050	1058
15°	1056	1032	1034
20°	1034	1007	1011
25°	1012	978	983
30°	985	950	949
35°	959	918	912
40°	928	885	878
45°	896	852	842
50°	861	818	801
55°	825	778	763
60°	784	731	719
65°	739	682	667
70°	682	622	612
75°	602	551	560
80°	507	459	462
85°	357	304	301

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1487 cd/sqm

TEST NUMBER: P913872

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.3
10°-20°	244.9	3.7
20°-30°	359.9	5.5
30°-40°	418.0	6.4
40°-50°	417.5	6.4
50°-60°	364.0	5.5
60°-70°	269.1	4.1
70°-80°	152.3	2.3
80°-90°	44.4	0.7
90°-100°	93.0	1.4
100°-110°	295.6	4.5
110°-120°	505.8	7.7
120°-130°	665.2	10.1
130°-140°	746.6	11.4
140°-150°	732.2	11.2
150°-160°	614.2	9.4
160°-170°	407.3	6.2
170°-180°	142.4	2.2
0°-30°	691.8	10.5
0°-40°	1109.8	16.9
0°-60°	1891.3	28.8
0°-90°	2357.0	35.9
90°-120°	894.4	13.6
90°-150°	3038.4	46.3
90°-180°	4202.0	64.1
0°-180°	6559.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	925	925	925	925	925	
5°	925	921	911	918	917	88
15°	880	875	863	867	862	248
25°	797	790	774	776	774	367
35°	687	678	664	659	654	429
45°	559	553	540	530	526	432
55°	423	418	407	397	392	378
65°	286	280	271	263	259	282
75°	149	148	143	138	140	159
85°	36	36	35	32	31	41
90°	1	16	44	42	43	6
95°	66	79	81	81	79	74
105°	273	276	279	282	282	288
115°	508	515	512	511	508	502
125°	738	750	746	742	740	660
135°	955	969	972	970	967	738
145°	1159	1168	1176	1177	1172	724
155°	1326	1329	1333	1340	1336	610
165°	1442	1441	1441	1450	1443	407
175°	1500	1497	1494	1503	1496	143
180°	1503	1503	1503	1503	1503	

TEST NUMBER: P913872

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	924.7	924.7	924.7	924.7	924.7
2.5°	930.1	925.7	915.8	924.7	923.0
5°	924.7	921.2	911.4	918.5	916.8
7.5°	918.5	913.2	903.4	910.6	908.8
10°	908.8	902.5	891.9	899.0	896.4
12.5°	895.4	890.1	879.5	883.8	882.1
15°	880.3	875.0	863.4	867.0	862.5
17.5°	861.6	856.3	844.7	849.1	844.7
20°	841.1	835.8	823.4	826.0	822.5
22.5°	820.8	812.8	801.1	801.1	799.3
25°	796.7	789.6	774.5	776.3	774.5
27.5°	770.0	763.7	752.3	749.6	745.2
30°	743.4	736.3	722.9	720.3	716.7
32.5°	714.9	709.6	695.4	690.0	686.4
35°	687.4	678.5	664.2	658.9	654.4
37.5°	656.2	648.2	634.0	627.7	623.3
40°	624.2	617.1	602.8	594.9	591.4
42.5°	593.1	586.0	571.8	562.8	557.5
45°	559.4	553.1	539.7	530.0	526.4
47.5°	526.4	520.2	506.0	496.1	490.8
50°	491.7	487.3	474.8	462.4	458.0
52.5°	458.0	451.7	440.2	430.4	424.1
55°	423.3	418.0	407.3	396.6	392.2
57.5°	388.6	384.1	372.6	361.9	358.3
60°	353.9	350.4	337.9	328.1	325.5
62.5°	320.1	313.9	305.0	296.1	292.6
65°	285.5	280.1	271.2	263.2	258.8
67.5°	249.9	245.4	237.4	231.2	227.7
70°	217.0	213.4	205.4	199.2	195.7
72.5°	183.2	179.6	175.2	169.0	166.4
75°	149.3	147.7	143.1	137.8	139.7
77.5°	119.1	115.6	113.8	111.1	108.5
80°	89.0	88.0	86.2	83.6	81.8
82.5°	60.4	60.4	59.7	56.0	56.0
85°	36.4	35.6	34.7	32.0	31.1
87.5°	16.0	14.3	12.4	9.8	8.9
90°	1.3	16.3	44.4	41.7	43.0
92.5°	28.1	38.1	39.5	40.8	40.8
95°	66.1	78.8	81.1	81.1	78.8
97.5°	110.1	121.9	126.9	126.9	126.9
100°	160.9	171.3	174.9	174.9	173.6
102.5°	214.4	222.0	227.0	228.4	227.0
105°	272.8	276.5	279.2	281.5	281.5
107.5°	330.8	336.3	336.3	337.2	330.8
110°	387.1	394.3	394.3	394.3	390.6

TEST NUMBER: P913872

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	447.7	455.4	454.1	450.4	447.7
115°	507.6	514.8	512.5	511.2	507.6
117.5°	567.0	576.9	570.5	567.0	563.3
120°	626.8	636.8	626.8	626.8	622.7
122.5°	681.1	693.8	687.5	683.9	681.1
125°	738.2	749.6	745.9	741.9	740.5
127.5°	794.0	808.0	803.0	797.6	794.0
130°	846.1	862.4	860.2	857.5	852.5
132.5°	904.6	917.3	918.1	911.8	908.2
135°	954.9	968.9	971.6	970.3	966.6
137.5°	1011.1	1022.4	1024.7	1023.7	1018.3
140°	1060.5	1071.8	1078.2	1078.2	1073.2
142.5°	1111.2	1122.5	1126.2	1127.5	1122.5
145°	1159.3	1168.3	1175.6	1176.9	1172.0
147.5°	1202.3	1213.6	1219.1	1221.3	1216.3
150°	1246.7	1254.4	1259.4	1263.4	1259.4
152.5°	1286.1	1293.9	1300.2	1305.2	1300.2
155°	1325.6	1329.2	1333.2	1339.7	1335.5
157.5°	1359.5	1362.3	1364.5	1373.6	1367.3
160°	1390.0	1392.7	1394.0	1401.7	1396.3
162.5°	1418.0	1418.0	1419.4	1428.0	1421.6
165°	1442.0	1440.7	1440.7	1449.8	1443.4
167.5°	1463.8	1459.8	1459.8	1468.8	1462.4
170°	1480.1	1476.5	1475.1	1484.2	1476.5
172.5°	1491.4	1487.8	1486.4	1495.5	1487.8
175°	1500.5	1496.9	1494.1	1503.2	1495.5
177.5°	1505.5	1501.9	1499.1	1506.8	1499.1
180°	1503.2	1503.2	1503.2	1503.2	1503.2

TEST NUMBER: P913872

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.04	6.79	7.11	7.86	9.32	5.60	6.35	6.67	7.42	8.88
	3H	7.68	8.35	8.76	9.43	10.91	7.20	7.87	8.28	8.95	10.43
	4H	8.26	8.90	9.35	9.98	11.46	7.78	8.41	8.87	9.50	10.98
	6H	8.65	9.24	9.75	10.32	11.82	8.16	8.75	9.26	9.83	11.33
	8H	8.75	9.31	9.85	10.41	11.90	8.26	8.82	9.36	9.92	11.41
	12H	8.79	9.32	9.90	10.42	11.93	8.30	8.83	9.40	9.92	11.43
4H	2H	6.48	7.12	7.58	8.20	9.68	6.13	6.77	7.23	7.85	9.33
	3H	8.33	8.86	9.43	9.97	11.47	7.93	8.46	9.03	9.57	11.06
	4H	9.04	9.52	10.14	10.62	12.14	8.62	9.11	9.73	10.21	11.72
	6H	9.54	9.96	10.65	11.08	12.59	9.12	9.53	10.23	10.66	12.16
	8H	9.68	10.07	10.80	11.19	12.71	9.26	9.65	10.37	10.76	12.29
	12H	9.75	10.10	10.88	11.23	12.76	9.31	9.66	10.44	10.79	12.32
8H	4H	9.22	9.61	10.33	10.72	12.25	8.85	9.24	9.96	10.35	11.88
	6H	9.84	10.16	10.97	11.32	12.84	9.46	9.79	10.60	10.94	12.46
	8H	10.05	10.34	11.20	11.47	13.01	9.67	9.95	10.81	11.09	12.63
	12H	10.18	10.42	11.32	11.56	13.13	9.78	10.02	10.92	11.16	12.73
12H	4H	9.20	9.55	10.33	10.68	12.21	8.84	9.19	9.97	10.32	11.85
	6H	9.87	10.15	11.01	11.28	12.83	9.50	9.78	10.64	10.92	12.46
	8H	10.10	10.34	11.24	11.48	13.06	9.73	9.97	10.87	11.11	12.68

END OF REPORT