

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913891

Luminaire Tested: DFN2DIP-PN3F0-040D030US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913891
REPORT IS A COMBINATION OF REPORTS P901034 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-040D030US927-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5046.2 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913891

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913891

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1531	1531	1531
5°	1532	1505	1516
10°	1516	1475	1466
15°	1495	1425	1389
20°	1466	1357	1295
25°	1437	1281	1204
30°	1398	1203	1089
35°	1360	1119	988
40°	1321	1032	872
45°	1276	936	768
50°	1229	839	665
55°	1180	736	567
60°	1123	628	466
65°	1058	519	419
70°	979	416	378
75°	879	365	343
80°	735	302	295
85°	499	197	218

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1276 cd/sqm

TEST NUMBER: P913891

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	2.4
10°-20°	336.9	6.7
20°-30°	473.1	9.4
30°-40°	515.7	10.2
40°-50°	473.9	9.4
50°-60°	372.2	7.4
60°-70°	242.3	4.8
70°-80°	124.7	2.5
80°-90°	33.3	0.7
90°-100°	26.5	0.5
100°-110°	98.6	2.0
110°-120°	261.5	5.2
120°-130°	433.7	8.6
130°-140°	460.7	9.1
140°-150°	428.1	8.5
150°-160°	344.2	6.8
160°-170°	221.8	4.4
170°-180°	76.3	1.5
0°-30°	932.7	18.5
0°-40°	1448.4	28.7
0°-60°	2294.6	45.5
0°-90°	2694.8	53.4
90°-120°	386.5	7.7
90°-150°	1709.0	33.9
90°-180°	2351.0	46.6
0°-180°	5046.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	7	12	15	16	5
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P913891

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9

TEST NUMBER: P913891

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P913891

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.90	9.76	9.83	10.71	11.93	4.87	5.73	5.80	6.67	7.90
	3H	10.57	11.34	11.52	12.30	13.55	6.05	6.82	7.00	7.78	9.02
	4H	11.18	11.91	12.14	12.87	14.12	6.50	7.22	7.46	8.19	9.44
	6H	11.60	12.27	12.57	13.23	14.50	6.82	7.48	7.79	8.45	9.72
	8H	11.72	12.36	12.70	13.34	14.61	6.90	7.54	7.88	8.52	9.79
	12H	11.78	12.39	12.77	13.36	14.65	6.95	7.55	7.93	8.53	9.82
4H	2H	8.92	9.65	9.89	10.61	11.86	5.46	6.19	6.43	7.15	8.41
	3H	10.75	11.35	11.72	12.34	13.61	6.81	7.41	7.78	8.40	9.67
	4H	11.43	11.98	12.42	12.97	14.26	7.35	7.90	8.34	8.89	10.18
	6H	11.95	12.42	12.94	13.43	14.72	7.77	8.24	8.76	9.25	10.54
	8H	12.12	12.56	13.12	13.56	14.87	7.89	8.33	8.89	9.33	10.64
	12H	12.21	12.61	13.23	13.63	14.94	7.95	8.35	8.97	9.37	10.68
8H	4H	11.40	11.84	12.40	12.85	14.15	7.63	8.07	8.63	9.07	10.38
	6H	11.96	12.33	12.98	13.37	14.68	8.14	8.51	9.16	9.55	10.85
	8H	12.18	12.50	13.21	13.53	14.85	8.33	8.65	9.36	9.68	11.00
	12H	12.31	12.59	13.34	13.62	14.99	8.44	8.73	9.48	9.75	11.12
12H	4H	11.36	11.75	12.37	12.77	14.08	7.64	8.03	8.65	9.05	10.36
	6H	11.94	12.26	12.97	13.29	14.61	8.19	8.51	9.22	9.54	10.86
	8H	12.16	12.44	13.19	13.46	14.83	8.40	8.68	9.43	9.70	11.07