

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905989

Luminaire Tested: DFN2DIP-PN4F0-070D060US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905989
REPORT IS A COMBINATION OF REPORTS P901171 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-070D060US835-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12870.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 111.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905989

CATALOG NUMBER: DFN2DIP-PN4F0-070D060US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P905989

CATALOG NUMBER: DFN2DIP-PN4F0-070D060US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		72	72	72		60
1	99	94	90	87	91	88	84	81	75	73	70		63	62	60		53
2	90	82	76	71	83	77	71	67	66	62	58		56	53	50		46
3	82	72	65	59	76	67	61	56	58	53	49		49	46	42		41
4	75	64	56	50	69	60	53	47	52	46	42		44	40	36		37
5	69	57	49	43	64	53	46	41	46	40	36		39	35	32		33
6	63	51	43	37	59	48	41	35	42	36	31		36	31	28		30
7	59	46	38	33	54	43	36	31	38	32	28		32	28	24		27
8	54	42	34	29	50	39	32	28	34	29	25		30	25	22		25
9	51	38	31	26	47	36	29	25	32	26	22		27	23	20		23
10	47	35	28	23	44	33	27	22	29	24	20		25	21	18		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1988	1988	1988
5°	1991	1961	1974
10°	1975	1935	1948
15°	1946	1903	1906
20°	1907	1859	1864
25°	1868	1806	1815
30°	1819	1757	1752
35°	1773	1700	1686
40°	1716	1641	1623
45°	1659	1583	1559
50°	1596	1521	1484
55°	1531	1450	1416
60°	1458	1366	1338
65°	1377	1279	1245
70°	1275	1172	1146
75°	1133	1045	1055
80°	963	883	879
85°	696	603	588

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1659 cd/sqm

TEST NUMBER: P905989

CATALOG NUMBER: DFN2DIP-PN4F0-070D060US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	2.0
10°-20°	721.3	5.6
20°-30°	1060.0	8.2
30°-40°	1231.1	9.6
40°-50°	1229.6	9.6
50°-60°	1072.2	8.3
60°-70°	792.6	6.2
70°-80°	448.4	3.5
80°-90°	121.9	0.9
90°-100°	66.8	0.5
100°-110°	248.9	1.9
110°-120°	660.2	5.1
120°-130°	1094.9	8.5
130°-140°	1163.0	9.0
140°-150°	1080.9	8.4
150°-160°	869.0	6.8
160°-170°	560.0	4.4
170°-180°	192.7	1.5
0°-30°	2037.7	15.8
0°-40°	3268.8	25.4
0°-60°	5570.6	43.3
0°-90°	6933.6	53.9
90°-120°	975.8	7.6
90°-150°	4314.7	33.5
90°-180°	5936.0	46.1
0°-180°	12870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	120
90°	1	18	29	37	40	12
95°	95	47	57	65	63	113
105°	445	489	89	105	111	476
115°	842	867	904	226	120	829
125°	1191	1210	1238	1248	1253	1062
135°	1474	1498	1511	1525	1522	1139
145°	1710	1708	1733	1744	1736	1069
155°	1883	1870	1887	1896	1884	868
165°	1984	1975	1980	1990	1980	560
175°	2029	2019	2022	2032	2018	193
180°	2025	2025	2025	2025	2025	

TEST NUMBER: P905989

CATALOG NUMBER: DFN2DIP-PN4F0-070D060US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	1.4	17.6	29.2	36.7	39.5
92.5°	36.7	30.8	35.1	38.1	39.5
95°	95.2	46.8	57.1	64.6	63.0
97.5°	171.4	51.3	74.6	79.2	80.6
100°	259.4	58.6	83.5	95.2	98.1
102.5°	356.0	353.2	86.5	102.5	107.0
105°	445.4	489.4	89.4	105.4	111.4
107.5°	549.5	586.0	92.4	108.4	114.3
110°	649.2	679.8	256.5	110.0	115.7

TEST NUMBER: P905989

CATALOG NUMBER: DFN2DIP-PN4F0-070D060US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.9	769.2	744.3	112.7	117.3
115°	842.5	867.4	904.1	225.7	120.2
117.5°	928.9	958.2	983.2	773.6	389.7
120°	1025.7	1047.6	1074.1	1091.6	893.8
122.5°	1107.6	1131.1	1160.5	1169.2	1170.8
125°	1191.2	1210.3	1238.1	1248.4	1252.7
127.5°	1267.4	1287.9	1310.0	1324.6	1326.0
130°	1339.2	1362.7	1378.7	1394.9	1393.5
132.5°	1412.5	1431.6	1447.6	1460.8	1459.4
135°	1474.1	1497.6	1510.6	1525.4	1522.4
137.5°	1538.4	1556.0	1570.8	1585.4	1581.1
140°	1601.4	1613.3	1629.3	1642.5	1635.2
142.5°	1654.3	1664.6	1683.6	1695.2	1687.9
145°	1710.0	1708.4	1733.3	1743.6	1736.3
147.5°	1758.2	1753.8	1778.7	1786.0	1780.3
150°	1805.2	1794.9	1818.4	1827.1	1819.8
152.5°	1844.7	1833.0	1854.9	1863.8	1853.5
155°	1882.8	1869.7	1887.3	1896.0	1884.3
157.5°	1913.6	1901.9	1915.1	1925.4	1913.6
160°	1940.0	1931.1	1940.0	1948.7	1938.5
162.5°	1963.3	1954.6	1961.9	1972.2	1959.0
165°	1983.9	1975.2	1979.5	1989.8	1979.5
167.5°	2000.0	1991.2	1995.7	2006.0	1992.7
170°	2013.3	2004.4	2007.4	2017.6	2004.4
172.5°	2022.0	2013.3	2016.2	2026.5	2013.3
175°	2029.3	2019.0	2022.0	2032.2	2017.6
177.5°	2032.2	2022.0	2023.5	2033.8	2020.6
180°	2024.9	2024.9	2024.9	2024.9	2024.9

TEST NUMBER: P905989

CATALOG NUMBER: DFN2DIP-PN4F0-070D060US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.02	10.91	10.94	11.86	13.07	9.58	10.47	10.50	11.42	12.63
	3H	11.68	12.49	12.62	13.44	14.68	11.20	12.00	12.13	12.95	14.19
	4H	12.27	13.04	13.22	13.99	15.24	11.79	12.55	12.74	13.50	14.75
	6H	12.68	13.38	13.64	14.34	15.60	12.19	12.89	13.15	13.85	15.11
	8H	12.79	13.45	13.75	14.43	15.69	12.29	12.96	13.26	13.94	15.20
	12H	12.84	13.47	13.81	14.44	15.73	12.34	12.97	13.31	13.94	15.23
4H	2H	10.48	11.25	11.44	12.20	13.45	10.13	10.89	11.09	11.85	13.10
	3H	12.36	12.99	13.32	13.98	15.24	11.95	12.59	12.92	13.57	14.84
	4H	13.07	13.65	14.05	14.63	15.92	12.66	13.24	13.63	14.22	15.50
	6H	13.59	14.09	14.58	15.10	16.38	13.17	13.67	14.16	14.67	15.96
	8H	13.75	14.21	14.73	15.21	16.51	13.32	13.78	14.31	14.78	16.08
	12H	13.82	14.24	14.83	15.26	16.56	13.38	13.80	14.39	14.82	16.12
8H	4H	13.27	13.74	14.26	14.74	16.04	12.90	13.37	13.89	14.37	15.67
	6H	13.91	14.30	14.92	15.33	16.63	13.53	13.92	14.55	14.96	16.26
	8H	14.13	14.47	15.15	15.50	16.81	13.75	14.09	14.77	15.11	16.43
	12H	14.27	14.57	15.29	15.59	16.95	13.87	14.17	14.89	15.19	16.55
12H	4H	13.26	13.68	14.27	14.70	16.00	12.90	13.32	13.91	14.33	15.64
	6H	13.94	14.28	14.96	15.31	16.62	13.58	13.92	14.60	14.94	16.26
	8H	14.19	14.49	15.21	15.51	16.87	13.81	14.11	14.84	15.13	16.49