

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906006

Luminaire Tested: DFN2DIP-PN4F0-070D100US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906006
REPORT IS A COMBINATION OF REPORTS P899724 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-070D100US835-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14800.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 141.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906006

CATALOG NUMBER: DFN2DIP-PN4F0-070D100US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906006

CATALOG NUMBER: DFN2DIP-PN4F0-070D100US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	43	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	20
7	58	46	38	33	53	42	35	31	35	30	27	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	45	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2112	2112	2112
5°	2115	2079	2092
10°	2094	2038	2024
15°	2065	1971	1919
20°	2027	1878	1791
25°	1988	1775	1666
30°	1936	1668	1508
35°	1884	1554	1370
40°	1832	1435	1210
45°	1771	1303	1066
50°	1708	1171	925
55°	1643	1029	790
60°	1567	880	650
65°	1480	729	586
70°	1374	588	531
75°	1241	519	484
80°	1048	437	421
85°	730	293	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2477 cd/sqm

TEST NUMBER: P906006

CATALOG NUMBER: DFN2DIP-PN4F0-070D100US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	1.8
10°-20°	744.3	5.0
20°-30°	1045.0	7.1
30°-40°	1139.2	7.7
40°-50°	1047.0	7.1
50°-60°	822.3	5.6
60°-70°	535.2	3.6
70°-80°	275.5	1.9
80°-90°	79.3	0.5
90°-100°	195.7	1.3
100°-110°	621.8	4.2
110°-120°	1064.1	7.2
120°-130°	1399.5	9.5
130°-140°	1570.9	10.6
140°-150°	1540.4	10.4
150°-160°	1292.2	8.7
160°-170°	856.9	5.8
170°-180°	299.5	2.0
0°-30°	2060.5	13.9
0°-40°	3199.7	21.6
0°-60°	5068.9	34.2
0°-90°	5958.9	40.3
90°-120°	1881.6	12.7
90°-150°	6392.4	43.2
90°-180°	8841.0	59.7
0°-180°	14800.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	3	34	93	88	91	15
95°	139	166	171	171	166	155
105°	574	582	587	592	592	606
115°	1068	1083	1078	1076	1068	1056
125°	1553	1577	1569	1561	1558	1388
135°	2009	2038	2044	2041	2034	1553
145°	2439	2458	2473	2476	2466	1524
155°	2789	2796	2805	2818	2810	1284
165°	3034	3031	3031	3050	3037	856
175°	3157	3149	3144	3163	3146	300
180°	3163	3163	3163	3163	3163	

TEST NUMBER: P906006

CATALOG NUMBER: DFN2DIP-PN4F0-070D100US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	2.9	34.3	93.4	87.7	90.6
92.5°	59.1	80.1	83.0	85.8	85.8
95°	139.2	165.9	170.7	170.7	165.9
97.5°	231.7	256.5	267.0	267.0	267.0
100°	338.5	360.4	368.0	368.0	365.2
102.5°	451.0	467.2	477.7	480.5	477.7
105°	574.0	581.6	587.3	592.1	592.1
107.5°	696.0	707.5	707.5	709.4	696.0
110°	814.3	829.5	829.5	829.5	821.9

TEST NUMBER: P906006

CATALOG NUMBER: DFN2DIP-PN4F0-070D100US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	942.0	958.2	955.4	947.7	942.0
115°	1067.9	1083.1	1078.4	1075.5	1067.9
117.5°	1192.8	1213.8	1200.4	1192.8	1185.1
120°	1318.6	1339.6	1318.6	1318.6	1310.1
122.5°	1433.0	1459.7	1446.4	1438.8	1433.0
125°	1553.2	1577.0	1569.4	1560.8	1558.0
127.5°	1670.5	1700.0	1689.5	1678.1	1670.5
130°	1780.1	1814.4	1809.7	1803.9	1793.5
132.5°	1903.1	1929.8	1931.7	1918.4	1910.7
135°	2008.9	2038.5	2044.2	2041.4	2033.7
137.5°	2127.2	2151.0	2155.8	2153.9	2142.4
140°	2231.1	2254.9	2268.3	2268.3	2257.8
142.5°	2337.9	2361.7	2369.3	2372.2	2361.7
145°	2438.9	2458.0	2473.3	2476.1	2465.6
147.5°	2529.5	2553.4	2564.8	2569.6	2559.1
150°	2623.0	2639.2	2649.7	2658.2	2649.7
152.5°	2705.9	2722.1	2735.5	2746.0	2735.5
155°	2788.9	2796.5	2805.1	2818.4	2809.8
157.5°	2860.4	2866.1	2870.9	2889.9	2876.6
160°	2924.3	2930.0	2932.8	2949.0	2937.6
162.5°	2983.4	2983.4	2986.2	3004.3	2991.0
165°	3033.9	3031.0	3031.0	3050.1	3036.8
167.5°	3079.7	3071.1	3071.1	3090.2	3076.8
170°	3114.0	3106.4	3103.5	3122.6	3106.4
172.5°	3137.8	3130.2	3127.3	3146.4	3130.2
175°	3156.9	3149.3	3143.6	3162.6	3146.4
177.5°	3167.4	3159.8	3154.0	3170.2	3154.0
180°	3162.6	3162.6	3162.6	3162.6	3162.6

TEST NUMBER: P906006

CATALOG NUMBER: DFN2DIP-PN4F0-070D100US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.77	9.52	9.81	10.57	11.97	4.73	5.49	5.77	6.53	7.94
	3H	10.44	11.12	11.49	12.17	13.60	5.92	6.59	6.97	7.64	9.07
	4H	11.05	11.69	12.11	12.74	14.18	6.36	7.00	7.43	8.06	9.49
	6H	11.47	12.06	12.54	13.12	14.56	6.68	7.27	7.75	8.33	9.77
	8H	11.59	12.16	12.67	13.23	14.67	6.77	7.33	7.85	8.41	9.84
	12H	11.66	12.19	12.74	13.26	14.72	6.81	7.34	7.89	8.41	9.87
4H	2H	8.78	9.42	9.85	10.47	11.90	5.32	5.96	6.39	7.02	8.45
	3H	10.60	11.13	11.68	12.22	13.66	6.66	7.20	7.74	8.28	9.72
	4H	11.29	11.78	12.38	12.85	14.32	7.21	7.70	8.29	8.77	10.24
	6H	11.81	12.23	12.90	13.32	14.78	7.63	8.04	8.72	9.14	10.60
	8H	11.98	12.37	13.07	13.46	14.94	7.75	8.15	8.85	9.23	10.71
	12H	12.08	12.43	13.18	13.53	15.01	7.82	8.17	8.93	9.27	10.75
8H	4H	11.26	11.65	12.35	12.74	14.21	7.49	7.88	8.58	8.97	10.44
	6H	11.82	12.14	12.94	13.28	14.75	8.00	8.33	9.12	9.46	10.93
	8H	12.04	12.32	13.16	13.44	14.93	8.20	8.48	9.32	9.59	11.08
	12H	12.18	12.43	13.30	13.53	15.07	8.31	8.56	9.43	9.67	11.20
12H	4H	11.20	11.56	12.31	12.66	14.14	7.49	7.84	8.60	8.94	10.42
	6H	11.80	12.08	12.92	13.19	14.69	8.05	8.34	9.17	9.45	10.94
	8H	12.02	12.27	13.14	13.37	14.90	8.26	8.51	9.38	9.62	11.15