

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913918

Luminaire Tested: DFN2DIP-PN3F0-050D030US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913918
REPORT IS A COMBINATION OF REPORTS P899516 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-050D030US927-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5470.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 68.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913918
CATALOG NUMBER: DFN2DIP-PN3F0-050D030US927-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P913918

CATALOG NUMBER: DFN2DIP-PN3F0-050D030US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	58	60	59	58	53
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	53	51	49	53	51	49	45
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	48	45	43	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	43	40	37	34
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33	39	36	33	30
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	36	32	29	27
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	30	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1914	1914	1914
5°	1916	1882	1895
10°	1895	1844	1832
15°	1868	1781	1736
20°	1833	1696	1618
25°	1796	1601	1505
30°	1747	1503	1361
35°	1700	1398	1235
40°	1651	1290	1090
45°	1595	1170	959
50°	1536	1049	831
55°	1475	920	709
60°	1404	785	582
65°	1323	648	524
70°	1224	521	473
75°	1099	456	428
80°	919	379	368
85°	625	246	272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1595 cd/sqm



TEST NUMBER: P913918

CATALOG NUMBER: DFN2DIP-PN3F0-050D030US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	2.8
10°-20°	421.2	7.7
20°-30°	591.3	10.8
30°-40°	644.6	11.8
40°-50°	592.4	10.8
50°-60°	465.3	8.5
60°-70°	302.9	5.5
70°-80°	155.9	2.8
80°-90°	41.9	0.8
90°-100°	46.5	0.9
100°-110°	147.8	2.7
110°-120°	252.9	4.6
120°-130°	332.6	6.1
130°-140°	373.3	6.8
140°-150°	366.1	6.7
150°-160°	307.1	5.6
160°-170°	203.7	3.7
170°-180°	71.2	1.3
0°-30°	1165.9	21.3
0°-40°	1810.5	33.1
0°-60°	2868.2	52.4
0°-90°	3368.9	61.6
90°-120°	447.2	8.2
90°-150°	1519.2	27.8
90°-180°	2101.0	38.4
0°-180°	5470.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	8	22	21	22	5
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	



TEST NUMBER: P913918

CATALOG NUMBER: DFN2DIP-PN3F0-050D030US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4



TEST NUMBER: P913918

CATALOG NUMBER: DFN2DIP-PN3F0-050D030US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6



TEST NUMBER: P913918
 CATALOG NUMBER: DFN2DIP-PN3F0-050D030US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.38	11.32	11.24	12.19	13.29	6.35	7.28	7.20	8.16	9.25
	3H	12.06	12.90	12.93	13.78	14.91	7.54	8.37	8.41	9.26	10.38
	4H	12.67	13.46	13.56	14.35	15.48	7.99	8.78	8.88	9.67	10.80
	6H	13.09	13.82	13.99	14.71	15.86	8.31	9.04	9.21	9.93	11.08
	8H	13.22	13.91	14.12	14.82	15.97	8.40	9.09	9.31	10.01	11.15
	12H	13.28	13.94	14.19	14.85	16.02	8.44	9.10	9.36	10.01	11.18
4H	2H	10.41	11.20	11.30	12.09	13.22	6.95	7.74	7.84	8.63	9.77
	3H	12.24	12.90	13.14	13.82	14.97	8.30	8.96	9.21	9.88	11.03
	4H	12.93	13.53	13.85	14.45	15.62	8.85	9.45	9.76	10.37	11.54
	6H	13.45	13.96	14.38	14.90	16.08	9.27	9.78	10.20	10.72	11.90
	8H	13.62	14.10	14.55	15.04	16.23	9.40	9.88	10.33	10.81	12.00
	12H	13.72	14.15	14.67	15.10	16.30	9.46	9.89	10.41	10.85	12.04
8H	4H	12.91	13.39	13.84	14.32	15.51	9.14	9.62	10.07	10.55	11.74
	6H	13.47	13.87	14.43	14.84	16.03	9.65	10.05	10.61	11.02	12.21
	8H	13.68	14.03	14.65	15.00	16.21	9.84	10.19	10.80	11.15	12.36
	12H	13.82	14.13	14.79	15.09	16.35	9.95	10.26	10.92	11.22	12.48
12H	4H	12.86	13.30	13.81	14.25	15.45	9.14	9.58	10.09	10.53	11.73
	6H	13.44	13.80	14.41	14.76	15.97	9.70	10.05	10.66	11.02	12.22
	8H	13.67	13.97	14.63	14.94	16.19	9.91	10.22	10.87	11.18	12.43