

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906019

Luminaire Tested: DFN2DIP-PN4F0-080D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906019
REPORT IS A COMBINATION OF REPORTS P901138 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D040US835-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10760.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 107.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906019

CATALOG NUMBER: DFN2DIP-PN4F0-080D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906019

CATALOG NUMBER: DFN2DIP-PN4F0-080D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2414	2414	2414
5°	2417	2376	2391
10°	2393	2329	2313
15°	2360	2253	2194
20°	2317	2147	2046
25°	2272	2028	1904
30°	2212	1906	1724
35°	2154	1775	1565
40°	2094	1640	1383
45°	2024	1490	1218
50°	1953	1338	1057
55°	1878	1176	903
60°	1791	1006	743
65°	1691	833	669
70°	1570	673	607
75°	1418	594	553
80°	1198	499	481
85°	835	335	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2024 cd/sqm

TEST NUMBER: P906019

CATALOG NUMBER: DFN2DIP-PN4F0-080D040US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.9	2.9
10°-20°	850.7	7.9
20°-30°	1194.3	11.1
30°-40°	1301.9	12.1
40°-50°	1196.6	11.1
50°-60°	939.7	8.7
60°-70°	611.7	5.7
70°-80°	314.9	2.9
80°-90°	82.8	0.8
90°-100°	44.5	0.4
100°-110°	165.9	1.5
110°-120°	440.1	4.1
120°-130°	729.9	6.8
130°-140°	775.4	7.2
140°-150°	720.6	6.7
150°-160°	579.4	5.4
160°-170°	373.3	3.5
170°-180°	128.5	1.2
0°-30°	2354.9	21.9
0°-40°	3656.8	34.0
0°-60°	5793.1	53.8
0°-90°	6802.4	63.2
90°-120°	650.5	6.0
90°-150°	2876.4	26.7
90°-180°	3958.0	36.8
0°-180°	10760.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3306	3306	3306	3306	3306	
5°	3306	3292	3252	3279	3270	314
15°	3145	3112	3010	2953	2924	886
25°	2855	2759	2561	2439	2394	1313
35°	2460	2307	2044	1855	1789	1540
45°	2011	1810	1496	1284	1212	1553
55°	1529	1296	972	793	736	1366
65°	1032	790	521	419	410	1024
75°	550	341	239	218	216	582
85°	129	66	57	57	57	148
90°	1	12	20	24	26	10
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P906019

CATALOG NUMBER: DFN2DIP-PN4F0-080D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3306.4	3306.4	3306.4	3306.4	3306.4
2.5°	3321.3	3306.4	3273.4	3303.5	3297.5
5°	3306.4	3291.5	3252.4	3279.4	3270.5
7.5°	3279.4	3261.6	3219.7	3231.5	3216.5
10°	3243.5	3222.6	3162.9	3153.7	3135.9
12.5°	3198.8	3171.8	3090.8	3073.0	3040.0
15°	3144.8	3111.8	3010.2	2953.4	2923.5
17.5°	3081.9	3034.0	2908.3	2842.6	2794.6
20°	3010.2	2950.2	2800.7	2726.1	2660.0
22.5°	2932.4	2863.5	2689.9	2588.3	2543.5
25°	2854.6	2758.8	2561.3	2438.8	2393.7
27.5°	2761.9	2660.0	2441.6	2301.0	2232.1
30°	2663.2	2549.2	2309.9	2157.5	2076.5
32.5°	2567.3	2429.6	2184.5	2004.8	1929.9
35°	2459.7	2307.0	2043.8	1855.3	1789.2
37.5°	2354.9	2190.2	1912.1	1705.4	1630.8
40°	2244.2	2064.8	1774.3	1561.9	1484.1
42.5°	2130.5	1939.1	1636.8	1415.3	1340.6
45°	2010.8	1810.2	1496.2	1283.5	1211.8
47.5°	1897.2	1684.8	1361.6	1148.9	1083.2
50°	1771.4	1559.1	1229.9	1023.2	960.6
52.5°	1648.6	1424.1	1104.1	906.7	849.9
55°	1528.9	1295.6	972.4	793.0	736.2
57.5°	1406.4	1167.0	855.9	688.3	640.3
60°	1280.6	1041.3	733.0	580.6	532.7
62.5°	1158.1	918.7	628.3	484.8	461.0
65°	1032.4	789.8	520.6	419.1	409.8
67.5°	912.7	670.2	419.1	367.9	359.1
70°	787.0	553.7	347.0	317.1	305.1
72.5°	667.3	445.7	290.2	266.4	260.3
75°	550.5	341.0	239.4	218.4	215.6
77.5°	434.0	242.2	188.6	176.5	170.5
80°	326.0	173.7	143.5	131.7	131.7
82.5°	227.3	116.8	98.7	92.7	92.7
85°	128.6	65.7	56.8	56.8	56.8
87.5°	47.9	23.8	23.8	21.0	21.0
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1



TEST NUMBER: P906019

CATALOG NUMBER: DFN2DIP-PN4F0-080D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P906019

CATALOG NUMBER: DFN2DIP-PN4F0-080D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.37	12.32	12.21	13.18	14.25	7.33	8.28	8.17	9.14	10.21
	3H	13.06	13.91	13.91	14.78	15.88	8.53	9.38	9.39	10.25	11.35
	4H	13.67	14.48	14.54	15.35	16.46	8.99	9.79	9.86	10.67	11.78
	6H	14.10	14.84	14.99	15.72	16.85	9.32	10.05	10.20	10.94	12.06
	8H	14.23	14.94	15.13	15.84	16.96	9.41	10.11	10.30	11.01	12.14
	12H	14.30	14.97	15.20	15.86	17.01	9.46	10.13	10.35	11.02	12.17
4H	2H	11.40	12.20	12.28	13.08	14.19	7.94	8.75	8.82	9.62	10.73
	3H	13.24	13.91	14.13	14.82	15.94	9.31	9.97	10.19	10.88	12.01
	4H	13.94	14.55	14.84	15.45	16.60	9.86	10.47	10.76	11.37	12.52
	6H	14.47	14.99	15.38	15.92	17.07	10.29	10.81	11.20	11.74	12.89
	8H	14.65	15.13	15.56	16.06	17.22	10.42	10.91	11.33	11.83	12.99
	12H	14.75	15.19	15.68	16.13	17.30	10.49	10.93	11.42	11.87	13.04
8H	4H	13.92	14.41	14.84	15.33	16.50	10.15	10.64	11.07	11.56	12.73
	6H	14.49	14.90	15.44	15.86	17.03	10.67	11.08	11.62	12.04	13.21
	8H	14.71	15.07	15.66	16.02	17.21	10.87	11.22	11.82	12.18	13.36
	12H	14.86	15.17	15.81	16.12	17.35	10.99	11.31	11.95	12.25	13.49
12H	4H	13.88	14.32	14.81	15.26	16.43	10.16	10.60	11.10	11.54	12.71
	6H	14.47	14.83	15.42	15.78	16.96	10.72	11.08	11.68	12.04	13.22
	8H	14.70	15.01	15.65	15.96	17.19	10.94	11.26	11.90	12.20	13.44