

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906028

Luminaire Tested: DFN2DIP-PN4F0-080D070US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906028
REPORT IS A COMBINATION OF REPORTS P899671 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D070US835-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14115.0 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 129.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906028
CATALOG NUMBER: DFN2DIP-PN4F0-080D070US835-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P906028
 CATALOG NUMBER: DFN2DIP-PN4F0-080D070US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	37	31	38	32	28	33	29	25	28	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	23	20	17
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2272	2272	2272
5°	2276	2241	2256
10°	2257	2211	2226
15°	2224	2175	2179
20°	2179	2125	2130
25°	2135	2065	2074
30°	2079	2009	2003
35°	2026	1942	1927
40°	1961	1876	1855
45°	1896	1809	1782
50°	1824	1739	1697
55°	1750	1658	1618
60°	1666	1561	1529
65°	1574	1461	1423
70°	1457	1340	1310
75°	1295	1195	1205
80°	1100	1009	1005
85°	796	689	672

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1896 cd/sqm



TEST NUMBER: P906028

CATALOG NUMBER: DFN2DIP-PN4F0-080D070US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	2.1
10°-20°	824.3	5.8
20°-30°	1211.5	8.6
30°-40°	1407.0	10.0
40°-50°	1405.3	10.0
50°-60°	1225.4	8.7
60°-70°	905.8	6.4
70°-80°	512.5	3.6
80°-90°	141.6	1.0
90°-100°	137.0	1.0
100°-110°	435.3	3.1
110°-120°	744.9	5.3
120°-130°	979.6	6.9
130°-140°	1099.6	7.8
140°-150°	1078.3	7.6
150°-160°	904.5	6.4
160°-170°	599.9	4.2
170°-180°	209.7	1.5
0°-30°	2328.8	16.5
0°-40°	3735.8	26.5
0°-60°	6366.4	45.1
0°-90°	7926.3	56.2
90°-120°	1317.2	9.3
90°-150°	4474.7	31.7
90°-180°	6189.0	43.8
0°-180°	14115.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	137
90°	2	24	65	61	63	14
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	



TEST NUMBER: P906028

CATALOG NUMBER: DFN2DIP-PN4F0-080D070US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3



TEST NUMBER: P906028

CATALOG NUMBER: DFN2DIP-PN4F0-080D070US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8



TEST NUMBER: P906028
 CATALOG NUMBER: DFN2DIP-PN4F0-080D070US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.68	11.60	11.58	12.52	13.70	10.24	11.16	11.14	12.08	13.26
	3H	12.35	13.17	13.26	14.10	15.31	11.86	12.69	12.78	13.62	14.82
	4H	12.94	13.72	13.87	14.66	15.87	12.45	13.23	13.38	14.17	15.38
	6H	13.34	14.06	14.29	15.01	16.23	12.85	13.57	13.79	14.51	15.74
	8H	13.45	14.14	14.40	15.10	16.32	12.96	13.64	13.91	14.60	15.83
	12H	13.50	14.16	14.46	15.11	16.36	13.00	13.66	13.96	14.61	15.86
4H	2H	11.15	11.93	12.08	12.86	14.08	10.80	11.58	11.73	12.51	13.73
	3H	13.02	13.67	13.97	14.64	15.87	12.62	13.27	13.56	14.24	15.47
	4H	13.74	14.34	14.70	15.30	16.55	13.32	13.92	14.28	14.88	16.13
	6H	14.26	14.78	15.23	15.76	17.01	13.84	14.35	14.81	15.34	16.59
	8H	14.42	14.89	15.38	15.87	17.14	13.99	14.47	14.96	15.44	16.71
	12H	14.49	14.93	15.48	15.92	17.19	14.05	14.48	15.04	15.48	16.75
8H	4H	13.94	14.42	14.91	15.40	16.67	13.57	14.05	14.54	15.03	16.30
	6H	14.58	14.98	15.58	16.00	17.26	14.20	14.60	15.20	15.62	16.89
	8H	14.80	15.15	15.81	16.16	17.45	14.42	14.77	15.42	15.78	17.06
	12H	14.94	15.25	15.95	16.25	17.58	14.54	14.85	15.55	15.85	17.18
12H	4H	13.93	14.36	14.92	15.36	16.63	13.57	14.00	14.56	15.00	16.27
	6H	14.61	14.96	15.61	15.97	17.25	14.25	14.60	15.25	15.60	16.89
	8H	14.86	15.17	15.87	16.17	17.50	14.49	14.79	15.49	15.80	17.13