

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906045

Luminaire Tested: DFN2DIP-PN4F0-080D110US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906045
REPORT IS A COMBINATION OF REPORTS P901263 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D110US835-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18810.0 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 168.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906045

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906045

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	65	58	53	53	49	45	43	40	37	34	31	30
4	73	62	54	49	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2272	2272	2272
5°	2276	2241	2256
10°	2257	2211	2226
15°	2224	2175	2179
20°	2179	2125	2130
25°	2135	2065	2074
30°	2079	2009	2003
35°	2026	1942	1927
40°	1961	1876	1855
45°	1896	1809	1782
50°	1824	1739	1697
55°	1750	1658	1618
60°	1666	1561	1529
65°	1574	1461	1423
70°	1457	1340	1310
75°	1295	1195	1205
80°	1100	1009	1005
85°	796	689	672

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1979 cd/sqm

TEST NUMBER: P906045

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	1.6
10°-20°	824.3	4.4
20°-30°	1211.5	6.4
30°-40°	1407.0	7.5
40°-50°	1405.3	7.5
50°-60°	1225.4	6.5
60°-70°	905.8	4.8
70°-80°	512.5	2.7
80°-90°	141.8	0.8
90°-100°	122.4	0.7
100°-110°	456.3	2.4
110°-120°	1210.3	6.4
120°-130°	2007.3	10.7
130°-140°	2132.2	11.3
140°-150°	1981.7	10.5
150°-160°	1593.2	8.5
160°-170°	1026.6	5.5
170°-180°	353.3	1.9
0°-30°	2328.8	12.4
0°-40°	3735.8	19.9
0°-60°	6366.4	33.8
0°-90°	7926.5	42.1
90°-120°	1789.0	9.5
90°-150°	7910.3	42.1
90°-180°	10883.0	57.9
0°-180°	18810.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	137
90°	3	32	54	67	72	17
95°	174	86	105	118	116	207
105°	817	897	164	193	204	873
115°	1544	1590	1658	414	220	1521
125°	2184	2219	2270	2289	2297	1948
135°	2702	2746	2769	2797	2791	2088
145°	3135	3132	3178	3197	3183	1961
155°	3452	3428	3460	3476	3455	1591
165°	3637	3621	3629	3648	3629	1028
175°	3720	3702	3707	3726	3699	354
180°	3712	3712	3712	3712	3712	

TEST NUMBER: P906045

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	2.6	32.2	53.6	67.3	72.4
92.5°	67.3	56.5	64.4	69.9	72.4
95°	174.5	85.8	104.6	118.3	115.5
97.5°	314.2	94.1	136.8	145.1	147.7
100°	475.6	107.5	153.1	174.5	179.9
102.5°	652.6	647.5	158.5	187.9	196.2
105°	816.6	897.3	164.0	193.3	204.2
107.5°	1007.4	1074.3	169.4	198.7	209.6
110°	1190.1	1246.3	470.2	201.6	212.1

TEST NUMBER: P906045

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1362.1	1410.2	1364.6	206.7	215.0
115°	1544.5	1590.1	1657.5	413.7	220.4
117.5°	1703.1	1756.7	1802.6	1418.2	714.5
120°	1880.4	1920.6	1969.1	2001.3	1638.6
122.5°	2030.7	2073.7	2127.6	2143.6	2146.5
125°	2183.8	2218.9	2269.9	2288.7	2296.7
127.5°	2323.5	2361.1	2401.6	2428.4	2431.0
130°	2455.2	2498.3	2527.6	2557.3	2554.8
132.5°	2589.5	2624.6	2654.0	2678.2	2675.7
135°	2702.5	2745.5	2769.4	2796.6	2791.1
137.5°	2820.5	2852.7	2879.8	2906.6	2898.6
140°	2936.0	2957.6	2987.0	3011.2	2997.8
142.5°	3032.9	3051.7	3086.5	3107.9	3094.5
145°	3135.0	3132.1	3177.7	3196.6	3183.2
147.5°	3223.4	3215.4	3261.0	3274.4	3263.9
150°	3309.5	3290.7	3333.7	3349.7	3336.3
152.5°	3381.9	3360.5	3400.7	3417.0	3398.2
155°	3451.8	3427.8	3460.0	3476.0	3454.6
157.5°	3508.2	3486.8	3511.1	3529.9	3508.2
160°	3556.7	3540.4	3556.7	3572.6	3553.8
162.5°	3599.4	3583.5	3596.9	3615.7	3591.5
165°	3637.1	3621.1	3629.1	3647.9	3629.1
167.5°	3666.7	3650.5	3658.8	3677.6	3653.4
170°	3691.0	3674.7	3680.1	3699.0	3674.7
172.5°	3706.9	3691.0	3696.4	3715.2	3691.0
175°	3720.3	3701.5	3706.9	3725.8	3699.0
177.5°	3725.8	3706.9	3709.8	3728.6	3704.4
180°	3712.4	3712.4	3712.4	3712.4	3712.4

TEST NUMBER: P906045

CATALOG NUMBER: DFN2DIP-PN4F0-080D110US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.36	10.15	10.38	11.18	12.56	8.92	9.71	9.94	10.74	12.12
	3H	11.02	11.73	12.05	12.77	14.17	10.53	11.24	11.56	12.28	13.68
	4H	11.60	12.28	12.65	13.32	14.73	11.12	11.79	12.16	12.83	14.24
	6H	12.00	12.62	13.06	13.67	15.09	11.51	12.13	12.56	13.18	14.59
	8H	12.11	12.70	13.16	13.76	15.17	11.61	12.20	12.67	13.27	14.68
	12H	12.15	12.71	13.22	13.77	15.21	11.65	12.21	12.72	13.27	14.71
4H	2H	9.81	10.49	10.86	11.53	12.93	9.46	10.14	10.51	11.18	12.58
	3H	11.67	12.24	12.73	13.31	14.73	11.27	11.84	12.33	12.90	14.32
	4H	12.39	12.90	13.45	13.96	15.41	11.97	12.49	13.04	13.55	14.99
	6H	12.90	13.35	13.98	14.43	15.87	12.48	12.92	13.55	14.01	15.44
	8H	13.05	13.47	14.13	14.54	15.99	12.62	13.04	13.70	14.11	15.57
	12H	13.12	13.50	14.22	14.59	16.04	12.68	13.06	13.78	14.15	15.60
8H	4H	12.58	12.99	13.65	14.07	15.52	12.21	12.62	13.28	13.70	15.15
	6H	13.21	13.55	14.31	14.67	16.12	12.83	13.18	13.93	14.30	15.74
	8H	13.43	13.73	14.54	14.83	16.30	13.05	13.35	14.15	14.45	15.92
	12H	13.56	13.83	14.67	14.92	16.43	13.16	13.43	14.27	14.52	16.03
12H	4H	12.56	12.94	13.65	14.03	15.48	12.20	12.57	13.29	13.66	15.12
	6H	13.24	13.54	14.35	14.64	16.11	12.88	13.18	13.98	14.28	15.75
	8H	13.48	13.75	14.59	14.84	16.35	13.11	13.37	14.22	14.47	15.98