

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913987

Luminaire Tested: DFN2DIP-PN3F0-070D060US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913987
REPORT IS A COMBINATION OF REPORTS P901082 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D060US927-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9419.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 115.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913987
CATALOG NUMBER: DFN2DIP-PN3F0-070D060US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913987
 CATALOG NUMBER: DFN2DIP-PN3F0-070D060US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	50	49	48	48	48	48	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	41	41	41	41	37
3	82	73	66	60	76	68	62	57	58	53	50	49	45	43	40	38	36	36	36	36	32
4	76	65	57	52	70	60	54	49	52	47	43	44	40	37	36	34	31	31	31	31	28
5	70	58	50	45	64	54	47	42	47	41	37	40	35	32	33	30	28	28	28	28	24
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	25	25	25	22
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	24	22	22	22	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	20	20	20	18
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	24	20	18	18	18	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2679	2679	2679
5°	2682	2635	2652
10°	2654	2581	2565
15°	2616	2494	2431
20°	2566	2375	2266
25°	2515	2241	2107
30°	2446	2105	1906
35°	2379	1958	1729
40°	2311	1806	1527
45°	2232	1638	1343
50°	2151	1469	1164
55°	2065	1288	992
60°	1966	1099	815
65°	1852	908	733
70°	1713	729	661
75°	1539	638	599
80°	1287	530	516
85°	874	345	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2232 cd/sqm



TEST NUMBER: P913987

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	2.3
10°-20°	589.7	6.3
20°-30°	827.9	8.8
30°-40°	902.4	9.6
40°-50°	829.4	8.8
50°-60°	651.4	6.9
60°-70°	424.0	4.5
70°-80°	218.2	2.3
80°-90°	58.5	0.6
90°-100°	52.9	0.6
100°-110°	197.2	2.1
110°-120°	523.0	5.6
120°-130°	867.4	9.2
130°-140°	921.3	9.8
140°-150°	856.3	9.1
150°-160°	688.4	7.3
160°-170°	443.6	4.7
170°-180°	152.7	1.6
0°-30°	1632.3	17.3
0°-40°	2534.7	26.9
0°-60°	4015.5	42.6
0°-90°	4716.3	50.1
90°-120°	773.0	8.2
90°-150°	3418.0	36.3
90°-180°	4703.0	49.9
0°-180°	9419.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2282	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	1	14	23	29	31	9
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	



TEST NUMBER: P913987

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US927-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.9	2291.9	2291.9	2291.9	2291.9
2.5°	2302.2	2291.9	2269.0	2289.9	2285.7
5°	2291.9	2281.5	2254.5	2273.2	2267.0
7.5°	2273.2	2260.8	2231.8	2239.9	2229.6
10°	2248.3	2233.8	2192.4	2186.0	2173.7
12.5°	2217.2	2198.5	2142.5	2130.1	2107.2
15°	2179.8	2157.0	2086.5	2047.2	2026.5
17.5°	2136.3	2103.1	2015.9	1970.3	1937.1
20°	2086.5	2044.9	1941.3	1889.6	1843.8
22.5°	2032.7	1984.9	1864.5	1794.1	1763.1
25°	1978.7	1912.2	1775.4	1690.4	1659.2
27.5°	1914.5	1843.8	1692.4	1595.0	1547.2
30°	1846.0	1767.0	1601.1	1495.5	1439.4
32.5°	1779.6	1684.1	1514.2	1389.6	1337.7
35°	1704.9	1599.1	1416.7	1286.0	1240.2
37.5°	1632.4	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.9	1082.7	1028.7
42.5°	1476.8	1344.1	1134.6	981.0	929.3
45°	1393.8	1254.7	1037.1	889.7	839.9
47.5°	1315.0	1167.8	943.8	796.4	750.8
50°	1227.9	1080.7	852.5	709.2	665.9
52.5°	1142.7	987.1	765.3	628.4	589.1
55°	1059.8	898.0	674.0	549.7	510.3
57.5°	974.9	808.9	593.3	477.1	443.9
60°	887.7	721.8	508.1	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.6	547.5	360.9	290.5	284.1
67.5°	632.6	464.5	290.5	255.0	248.9
70°	545.5	383.7	240.5	219.8	211.4
72.5°	462.6	309.0	201.1	184.7	180.5
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.1	45.6	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7



TEST NUMBER: P913987

CATALOG NUMBER: DFN2DIP-PN3F0-070D060US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1



TEST NUMBER: P913987
 CATALOG NUMBER: DFN2DIP-PN3F0-070D060US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.54	11.37	11.50	12.34	13.62	6.51	7.34	7.47	8.31	9.58
	3H	12.21	12.95	13.18	13.94	15.23	7.69	8.43	8.66	9.41	10.71
	4H	12.81	13.52	13.80	14.50	15.81	8.13	8.84	9.12	9.82	11.13
	6H	13.23	13.88	14.23	14.87	16.19	8.45	9.10	9.45	10.09	11.40
	8H	13.36	13.97	14.36	14.98	16.29	8.54	9.15	9.54	10.16	11.47
	12H	13.41	14.00	14.42	15.00	16.34	8.58	9.16	9.59	10.16	11.50
4H	2H	10.56	11.26	11.55	12.24	13.55	7.10	7.80	8.09	8.79	10.09
	3H	12.38	12.96	13.38	13.98	15.29	8.44	9.02	9.44	10.04	11.36
	4H	13.07	13.60	14.08	14.61	15.95	8.98	9.52	9.99	10.53	11.87
	6H	13.57	14.03	14.60	15.06	16.40	9.40	9.85	10.42	10.89	12.22
	8H	13.75	14.17	14.77	15.20	16.55	9.52	9.95	10.54	10.97	12.33
	12H	13.84	14.22	14.88	15.26	16.62	9.58	9.97	10.62	11.01	12.37
8H	4H	13.03	13.46	14.05	14.48	15.84	9.26	9.69	10.28	10.71	12.06
	6H	13.59	13.94	14.64	15.01	16.36	9.77	10.12	10.82	11.19	12.54
	8H	13.80	14.11	14.86	15.17	16.54	9.96	10.27	11.01	11.32	12.69
	12H	13.94	14.21	15.00	15.26	16.67	10.07	10.34	11.13	11.39	12.80
12H	4H	12.98	13.37	14.02	14.41	15.77	9.26	9.65	10.30	10.69	12.05
	6H	13.57	13.88	14.62	14.93	16.30	9.82	10.13	10.87	11.18	12.55
	8H	13.78	14.06	14.84	15.10	16.51	10.02	10.30	11.08	11.34	12.75