

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913999

Luminaire Tested: DFN2DIP-PN3F0-070D090US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913999
REPORT IS A COMBINATION OF REPORTS P901124 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D090US927-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11771.7 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913999

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913999

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	35	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	54	42	34	29	49	38	32	27	32	27	24	27	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2679	2679	2679
5°	2682	2635	2652
10°	2654	2581	2565
15°	2616	2494	2431
20°	2566	2375	2266
25°	2515	2241	2107
30°	2446	2105	1906
35°	2379	1958	1729
40°	2311	1806	1527
45°	2232	1638	1343
50°	2151	1469	1164
55°	2065	1288	992
60°	1966	1099	815
65°	1852	908	733
70°	1713	729	661
75°	1539	638	599
80°	1287	530	516
85°	874	345	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2232 cd/sqm

TEST NUMBER: P913999

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	1.8
10°-20°	589.7	5.0
20°-30°	827.9	7.0
30°-40°	902.4	7.7
40°-50°	829.4	7.0
50°-60°	651.4	5.5
60°-70°	424.0	3.6
70°-80°	218.2	1.9
80°-90°	59.9	0.5
90°-100°	79.3	0.7
100°-110°	295.8	2.5
110°-120°	784.4	6.7
120°-130°	1301.0	11.1
130°-140°	1382.0	11.7
140°-150°	1284.4	10.9
150°-160°	1032.6	8.8
160°-170°	665.4	5.7
170°-180°	229.0	1.9
0°-30°	1632.3	13.9
0°-40°	2534.7	21.5
0°-60°	4015.5	34.1
0°-90°	4717.7	40.1
90°-120°	1159.5	9.9
90°-150°	5127.0	43.6
90°-180°	7054.0	59.9
0°-180°	11771.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2282	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	2	21	35	44	47	11
95°	113	56	68	77	75	134
105°	529	582	106	125	132	566
115°	1001	1031	1074	268	143	986
125°	1415	1438	1471	1483	1489	1262
135°	1752	1780	1795	1813	1809	1353
145°	2032	2030	2060	2072	2063	1271
155°	2237	2222	2243	2253	2239	1031
165°	2357	2347	2352	2364	2352	666
175°	2411	2399	2403	2415	2398	229
180°	2406	2406	2406	2406	2406	

TEST NUMBER: P913999

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.9	2291.9	2291.9	2291.9	2291.9
2.5°	2302.2	2291.9	2269.0	2289.9	2285.7
5°	2291.9	2281.5	2254.5	2273.2	2267.0
7.5°	2273.2	2260.8	2231.8	2239.9	2229.6
10°	2248.3	2233.8	2192.4	2186.0	2173.7
12.5°	2217.2	2198.5	2142.5	2130.1	2107.2
15°	2179.8	2157.0	2086.5	2047.2	2026.5
17.5°	2136.3	2103.1	2015.9	1970.3	1937.1
20°	2086.5	2044.9	1941.3	1889.6	1843.8
22.5°	2032.7	1984.9	1864.5	1794.1	1763.1
25°	1978.7	1912.2	1775.4	1690.4	1659.2
27.5°	1914.5	1843.8	1692.4	1595.0	1547.2
30°	1846.0	1767.0	1601.1	1495.5	1439.4
32.5°	1779.6	1684.1	1514.2	1389.6	1337.7
35°	1704.9	1599.1	1416.7	1286.0	1240.2
37.5°	1632.4	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.9	1082.7	1028.7
42.5°	1476.8	1344.1	1134.6	981.0	929.3
45°	1393.8	1254.7	1037.1	889.7	839.9
47.5°	1315.0	1167.8	943.8	796.4	750.8
50°	1227.9	1080.7	852.5	709.2	665.9
52.5°	1142.7	987.1	765.3	628.4	589.1
55°	1059.8	898.0	674.0	549.7	510.3
57.5°	974.9	808.9	593.3	477.1	443.9
60°	887.7	721.8	508.1	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.6	547.5	360.9	290.5	284.1
67.5°	632.6	464.5	290.5	255.0	248.9
70°	545.5	383.7	240.5	219.8	211.4
72.5°	462.6	309.0	201.1	184.7	180.5
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.1	45.6	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.9
97.5°	203.7	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.3	113.1	116.6
102.5°	423.0	419.7	102.7	121.8	127.1
105°	529.3	581.6	106.2	125.3	132.3
107.5°	652.9	696.3	109.8	128.8	135.9
110°	771.3	807.8	304.8	130.6	137.5

TEST NUMBER: P913999

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	882.8	914.0	884.5	134.0	139.3
115°	1001.1	1030.6	1074.3	268.2	142.8
117.5°	1103.8	1138.6	1168.3	919.2	463.1
120°	1218.8	1244.8	1276.3	1297.1	1062.1
122.5°	1316.2	1344.1	1379.0	1389.3	1391.2
125°	1415.4	1438.1	1471.2	1483.4	1488.6
127.5°	1505.9	1530.3	1556.6	1574.0	1575.6
130°	1591.3	1619.3	1638.3	1657.5	1655.9
132.5°	1678.4	1701.1	1720.1	1735.9	1734.2
135°	1751.6	1779.5	1795.0	1812.6	1809.1
137.5°	1828.1	1849.0	1866.5	1883.9	1878.7
140°	1902.9	1917.0	1936.0	1951.7	1943.1
142.5°	1965.8	1978.0	2000.5	2014.4	2005.7
145°	2031.9	2030.0	2059.7	2071.9	2063.2
147.5°	2089.2	2084.1	2113.6	2122.3	2115.4
150°	2145.1	2132.9	2160.8	2171.1	2162.4
152.5°	2192.0	2178.1	2204.2	2214.7	2202.5
155°	2237.3	2221.8	2242.6	2253.0	2239.1
157.5°	2273.9	2260.0	2275.7	2287.9	2273.9
160°	2305.2	2294.7	2305.2	2315.6	2303.4
162.5°	2333.0	2322.6	2331.3	2343.5	2327.8
165°	2357.4	2347.0	2352.2	2364.4	2352.2
167.5°	2376.6	2366.1	2371.4	2383.6	2367.9
170°	2392.3	2381.8	2385.3	2397.5	2381.8
172.5°	2402.7	2392.3	2395.8	2408.0	2392.3
175°	2411.3	2399.1	2402.7	2414.8	2397.5
177.5°	2414.8	2402.7	2404.5	2416.7	2401.0
180°	2406.2	2406.2	2406.2	2406.2	2406.2

TEST NUMBER: P913999

CATALOG NUMBER: DFN2DIP-PN3F0-070D090US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.53	10.29	10.57	11.33	12.74	5.50	6.25	6.54	7.30	8.71
	3H	11.20	11.87	12.25	12.92	14.35	6.67	7.35	7.73	8.40	9.83
	4H	11.80	12.44	12.86	13.49	14.93	7.12	7.75	8.18	8.81	10.25
	6H	12.21	12.80	13.28	13.86	15.30	7.43	8.02	8.50	9.08	10.52
	8H	12.33	12.89	13.41	13.97	15.41	7.51	8.07	8.59	9.15	10.59
	12H	12.39	12.92	13.47	13.99	15.45	7.55	8.08	8.63	9.15	10.62
4H	2H	9.54	10.18	10.61	11.23	12.67	6.08	6.72	7.15	7.77	9.21
	3H	11.35	11.88	12.43	12.97	14.42	7.42	7.95	8.49	9.03	10.48
	4H	12.04	12.52	13.12	13.60	15.07	7.96	8.44	9.04	9.52	10.99
	6H	12.54	12.96	13.63	14.06	15.52	8.36	8.78	9.46	9.88	11.34
	8H	12.71	13.10	13.81	14.19	15.67	8.49	8.88	9.58	9.97	11.45
	12H	12.80	13.15	13.91	14.26	15.74	8.55	8.90	9.66	10.00	11.48
8H	4H	12.00	12.39	13.09	13.48	14.96	8.23	8.62	9.32	9.71	11.18
	6H	12.55	12.88	13.67	14.01	15.48	8.73	9.06	9.85	10.19	11.66
	8H	12.77	13.05	13.89	14.16	15.66	8.92	9.20	10.04	10.31	11.81
	12H	12.90	13.14	14.02	14.25	15.79	9.03	9.28	10.15	10.39	11.92
12H	4H	11.95	12.30	13.06	13.40	14.88	8.23	8.58	9.34	9.68	11.17
	6H	12.53	12.81	13.65	13.92	15.42	8.78	9.06	9.90	10.18	11.67
	8H	12.74	12.99	13.87	14.10	15.63	8.98	9.23	10.11	10.34	11.87

END OF REPORT