

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906093

Luminaire Tested: DFN2DIP-PN4F0-100D050US835-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P906093  
REPORT IS A COMBINATION OF REPORTS P901159 AND P898053  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-100D050US835-FLLONL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14850.0 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 138.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9952  
Total Harmonic Distortion (THDi): 0.069  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P906093  
CATALOG NUMBER: DFN2DIP-PN4F0-100D050US835-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P906093

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US835-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67	67	67	67
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56	56	56	56
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47	47	47	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40	40	40	40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34	34	34	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30	30	30	30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26	26	26	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23	23	23	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21	21	21	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19	19	19	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17	17	17	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2840	2840	2840
5°	2845	2801	2820
10°	2822	2764	2782
15°	2780	2719	2723
20°	2724	2656	2663
25°	2668	2581	2593
30°	2599	2511	2503
35°	2532	2428	2409
40°	2451	2345	2319
45°	2369	2261	2227
50°	2281	2173	2121
55°	2187	2072	2023
60°	2082	1951	1911
65°	1968	1827	1779
70°	1821	1675	1637
75°	1619	1493	1507
80°	1375	1262	1257
85°	994	861	841

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2369 cd/sqm



TEST NUMBER: P906093

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US835-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	366.2	2.5
10°-20°	1030.4	6.9
20°-30°	1514.3	10.2
30°-40°	1758.8	11.8
40°-50°	1756.6	11.8
50°-60°	1531.7	10.3
60°-70°	1132.3	7.6
70°-80°	640.6	4.3
80°-90°	172.1	1.2
90°-100°	55.7	0.4
100°-110°	207.4	1.4
110°-120°	550.1	3.7
120°-130°	912.4	6.1
130°-140°	969.2	6.5
140°-150°	900.8	6.1
150°-160°	724.2	4.9
160°-170°	466.6	3.1
170°-180°	160.6	1.1
0°-30°	2911.0	19.6
0°-40°	4669.7	31.4
0°-60°	7958.0	53.6
0°-90°	9903.0	66.7
90°-120°	813.2	5.5
90°-150°	3595.6	24.2
90°-180°	4947.0	33.3
0°-180°	14850.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	1	15	24	31	33	14
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P906093

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US835-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P906093

CATALOG NUMBER: DFN2DIP-PN4F0-100D050US835-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P906093  
 CATALOG NUMBER: DFN2DIP-PN4F0-100D050US835-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.32	13.35	13.12	14.17	15.19	11.88	12.91	12.68	13.74	14.75
	3H	13.99	14.92	14.81	15.76	16.80	13.51	14.44	14.32	15.27	16.31
	4H	14.59	15.47	15.42	16.31	17.36	14.11	14.98	14.93	15.82	16.87
	6H	15.00	15.81	15.84	16.66	17.72	14.51	15.32	15.35	16.17	17.23
	8H	15.11	15.89	15.96	16.75	17.82	14.62	15.39	15.47	16.26	17.32
	12H	15.17	15.90	16.03	16.76	17.85	14.67	15.40	15.53	16.26	17.35
4H	2H	12.80	13.68	13.63	14.52	15.57	12.45	13.33	13.28	14.17	15.22
	3H	14.69	15.42	15.53	16.29	17.36	14.28	15.02	15.13	15.89	16.95
	4H	15.41	16.08	16.27	16.95	18.04	14.99	15.66	15.85	16.53	17.62
	6H	15.94	16.51	16.81	17.41	18.51	15.51	16.09	16.39	16.98	18.08
	8H	16.09	16.63	16.97	17.52	18.63	15.66	16.20	16.54	17.09	18.20
	12H	16.18	16.66	17.07	17.57	18.69	15.73	16.22	16.63	17.13	18.25
8H	4H	15.62	16.16	16.50	17.05	18.16	15.25	15.79	16.13	16.68	17.79
	6H	16.26	16.71	17.17	17.64	18.75	15.89	16.33	16.79	17.26	18.37
	8H	16.49	16.88	17.40	17.81	18.93	16.10	16.50	17.02	17.42	18.55
	12H	16.63	16.98	17.55	17.89	19.07	16.23	16.57	17.14	17.49	18.67
12H	4H	15.61	16.10	16.51	17.01	18.12	15.25	15.74	16.15	16.65	17.76
	6H	16.29	16.69	17.21	17.61	18.74	15.93	16.33	16.84	17.25	18.38
	8H	16.55	16.89	17.46	17.81	18.99	16.17	16.52	17.09	17.44	18.62