

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906101

Luminaire Tested: DFN2DIP-PN4F0-100D070US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906101
REPORT IS A COMBINATION OF REPORTS P901195 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D070US835-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16830.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 153.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906101

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906101

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		102	102	102	102		88	88	88		76	76	76		64	64	64
1	100	95	91	88		93	89	86	83		77	75	73		67	65	63		57	56	54
2	91	83	77	72		85	78	72	68		68	64	60		59	55	53		50	48	46
3	83	73	66	60		77	69	62	57		60	55	51		52	48	45		44	41	39
4	76	65	57	51		71	61	54	48		53	48	43		46	42	38		40	36	34
5	70	58	50	44		65	54	47	41		48	42	37		42	37	33		36	32	29
6	64	52	44	38		60	49	41	36		43	37	33		38	33	29		32	29	26
7	59	47	39	33		55	44	37	32		39	33	29		34	29	26		30	26	23
8	55	43	35	29		51	40	33	28		36	30	26		31	27	23		27	23	21
9	51	39	31	26		48	37	30	25		33	27	23		29	24	21		25	21	19
10	48	36	29	24		45	34	27	23		30	25	21		27	22	19		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2840	2840	2840
5°	2845	2801	2820
10°	2822	2764	2782
15°	2780	2719	2723
20°	2724	2656	2663
25°	2668	2581	2593
30°	2599	2511	2503
35°	2532	2428	2409
40°	2451	2345	2319
45°	2369	2261	2227
50°	2281	2173	2121
55°	2187	2072	2023
60°	2082	1951	1911
65°	1968	1827	1779
70°	1821	1675	1637
75°	1619	1493	1507
80°	1375	1262	1257
85°	994	861	841

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2369 cd/sqm

TEST NUMBER: P906101

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	2.2
10°-20°	1030.4	6.1
20°-30°	1514.3	9.0
30°-40°	1758.8	10.5
40°-50°	1756.6	10.4
50°-60°	1531.7	9.1
60°-70°	1132.3	6.7
70°-80°	640.6	3.8
80°-90°	173.2	1.0
90°-100°	77.9	0.5
100°-110°	290.4	1.7
110°-120°	770.2	4.6
120°-130°	1277.4	7.6
130°-140°	1356.9	8.1
140°-150°	1261.1	7.5
150°-160°	1013.9	6.0
160°-170°	653.3	3.9
170°-180°	224.9	1.3
0°-30°	2911.0	17.3
0°-40°	4669.7	27.7
0°-60°	7958.0	47.3
0°-90°	9904.2	58.8
90°-120°	1138.5	6.8
90°-150°	5033.8	29.9
90°-180°	6926.0	41.2
0°-180°	16830.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	2	20	34	43	46	16
95°	111	55	67	75	74	131
105°	520	571	104	123	130	555
115°	983	1012	1055	263	140	968
125°	1390	1412	1444	1456	1462	1239
135°	1720	1747	1762	1780	1776	1328
145°	1995	1993	2022	2034	2026	1248
155°	2197	2181	2202	2212	2198	1012
165°	2314	2304	2309	2321	2309	654
175°	2368	2356	2359	2371	2354	225
180°	2362	2362	2362	2362	2362	



TEST NUMBER: P906101

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	1.6	20.5	34.1	42.8	46.1
92.5°	42.8	35.9	41.0	44.5	46.1
95°	111.0	54.6	66.6	75.3	73.5
97.5°	199.9	59.9	87.1	92.4	94.0
100°	302.7	68.4	97.4	111.0	114.5
102.5°	415.3	412.1	100.9	119.6	124.8
105°	519.7	571.0	104.3	123.0	129.9
107.5°	641.0	683.7	107.8	126.5	133.4
110°	757.4	793.1	299.2	128.3	135.0

TEST NUMBER: P906101

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	866.8	897.4	868.4	131.5	136.8
115°	982.9	1011.9	1054.7	263.3	140.3
117.5°	1083.8	1117.9	1147.1	902.5	454.7
120°	1196.6	1222.2	1253.1	1273.6	1042.8
122.5°	1292.2	1319.6	1354.0	1364.1	1365.9
125°	1389.7	1412.0	1444.5	1456.5	1461.5
127.5°	1478.6	1502.5	1528.3	1545.4	1547.0
130°	1562.4	1589.8	1608.5	1627.4	1625.8
132.5°	1647.9	1670.2	1688.9	1704.3	1702.7
135°	1719.7	1747.1	1762.4	1779.6	1776.2
137.5°	1794.8	1815.4	1832.6	1849.7	1844.6
140°	1868.3	1882.1	1900.8	1916.2	1907.7
142.5°	1930.0	1942.0	1964.1	1977.7	1969.2
145°	1995.0	1993.2	2022.2	2034.2	2025.7
147.5°	2051.2	2046.2	2075.2	2083.7	2077.0
150°	2106.0	2094.1	2121.5	2131.6	2123.1
152.5°	2152.1	2138.5	2164.1	2174.4	2162.5
155°	2196.6	2181.3	2201.8	2212.0	2198.4
157.5°	2232.5	2218.9	2234.3	2246.3	2232.5
160°	2263.4	2253.0	2263.4	2273.5	2261.5
162.5°	2290.6	2280.4	2288.9	2300.9	2285.5
165°	2314.5	2304.4	2309.4	2321.4	2309.4
167.5°	2333.4	2323.0	2328.3	2340.3	2324.9
170°	2348.8	2338.5	2341.9	2353.9	2338.5
172.5°	2359.0	2348.8	2352.3	2364.2	2348.8
175°	2367.5	2355.5	2359.0	2370.9	2353.9
177.5°	2370.9	2359.0	2360.8	2372.8	2357.3
180°	2362.4	2362.4	2362.4	2362.4	2362.4

TEST NUMBER: P906101

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US835-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.68	12.63	12.56	13.53	14.67	11.24	12.19	12.12	13.09	14.23
	3H	13.35	14.20	14.24	15.11	16.28	12.87	13.72	13.76	14.63	15.79
	4H	13.95	14.75	14.85	15.66	16.84	13.46	14.26	14.37	15.18	16.35
	6H	14.35	15.10	15.27	16.01	17.20	13.86	14.60	14.78	15.52	16.71
	8H	14.46	15.17	15.39	16.11	17.29	13.97	14.68	14.89	15.61	16.80
	12H	14.52	15.19	15.45	16.12	17.33	14.02	14.69	14.95	15.62	16.83
4H	2H	12.16	12.96	13.07	13.87	15.05	11.81	12.61	12.72	13.52	14.70
	3H	14.03	14.70	14.95	15.65	16.84	13.63	14.30	14.55	15.25	16.44
	4H	14.75	15.37	15.69	16.31	17.52	14.34	14.95	15.27	15.89	17.10
	6H	15.28	15.80	16.22	16.77	17.98	14.85	15.38	15.80	16.34	17.56
	8H	15.43	15.92	16.38	16.88	18.11	15.00	15.49	15.95	16.45	17.68
	12H	15.51	15.95	16.48	16.93	18.16	15.07	15.51	16.04	16.49	17.72
8H	4H	14.96	15.45	15.90	16.41	17.64	14.59	15.08	15.53	16.04	17.27
	6H	15.60	16.00	16.57	17.00	18.23	15.22	15.63	16.19	16.63	17.85
	8H	15.82	16.18	16.80	17.17	18.41	15.43	15.80	16.42	16.78	18.03
	12H	15.96	16.27	16.94	17.26	18.55	15.55	15.87	16.54	16.85	18.15
12H	4H	14.95	15.39	15.91	16.37	17.60	14.58	15.03	15.55	16.00	17.24
	6H	15.63	15.99	16.61	16.98	18.22	15.26	15.62	16.24	16.61	17.86
	8H	15.87	16.19	16.86	17.17	18.47	15.50	15.82	16.49	16.80	18.09