

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914046

Luminaire Tested: DFN2DIP-PN3F0-090D070US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P914046
REPORT IS A COMBINATION OF REPORTS P899580 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D070US927-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10967.8 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 147.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P914046

CATALOG NUMBER: DFN2DIP-PN3F0-090D070US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P914046

CATALOG NUMBER: DFN2DIP-PN3F0-090D070US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	95	92	88		92	89	86	83		76	74	72		65	63	62		55	54	53
2	91	84	78	73		84	78	73	69		68	64	60		58	55	53		49	47	45
3	83	74	67	61		77	69	63	58		60	55	51		52	48	45		44	41	39
4	77	66	58	52		71	62	55	50		54	49	44		46	42	39		39	36	34
5	71	59	51	45		65	55	48	43		48	43	39		42	38	34		36	33	30
6	65	53	45	40		60	50	43	38		44	38	34		38	34	30		33	29	27
7	60	48	41	35		56	45	38	33		40	34	30		35	30	27		30	27	24
8	56	44	36	31		52	41	35	30		37	31	27		32	28	24		28	24	22
9	52	40	33	28		49	38	31	27		34	28	24		30	25	22		26	22	20
10	49	37	30	25		46	35	29	24		31	26	22		27	23	20		24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3445	3445	3445
5°	3448	3388	3410
10°	3412	3319	3298
15°	3363	3207	3125
20°	3299	3053	2913
25°	3233	2882	2709
30°	3145	2706	2450
35°	3059	2517	2223
40°	2972	2322	1963
45°	2870	2106	1727
50°	2765	1888	1497
55°	2655	1656	1276
60°	2528	1413	1049
65°	2381	1167	942
70°	2203	937	850
75°	1979	821	770
80°	1655	681	663
85°	1123	443	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2870 cd/sqm

TEST NUMBER: P914046

CATALOG NUMBER: DFN2DIP-PN3F0-090D070US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.2	2.5
10°-20°	758.1	6.9
20°-30°	1064.4	9.7
30°-40°	1160.3	10.6
40°-50°	1066.4	9.7
50°-60°	837.5	7.6
60°-70°	545.1	5.0
70°-80°	280.6	2.6
80°-90°	76.6	0.7
90°-100°	108.5	1.0
100°-110°	344.8	3.1
110°-120°	590.1	5.4
120°-130°	776.1	7.1
130°-140°	871.1	7.9
140°-150°	854.2	7.8
150°-160°	716.6	6.5
160°-170°	475.2	4.3
170°-180°	166.1	1.5
0°-30°	2098.7	19.1
0°-40°	3258.9	29.7
0°-60°	5162.8	47.1
0°-90°	6065.2	55.3
90°-120°	1043.4	9.5
90°-150°	3544.8	32.3
90°-180°	4903.0	44.7
0°-180°	10967.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2947	2947	2947	2947	2947	
5°	2947	2933	2899	2923	2915	279
15°	2803	2773	2683	2632	2606	790
25°	2544	2459	2283	2173	2133	1170
35°	2192	2056	1822	1653	1595	1372
45°	1792	1613	1333	1144	1080	1384
55°	1363	1155	867	707	656	1218
65°	920	704	464	373	365	912
75°	491	304	213	195	192	519
85°	114	58	51	51	51	132
90°	2	19	52	49	50	11
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1372	1373	1367	845
155°	1546	1551	1556	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	

TEST NUMBER: P914046

CATALOG NUMBER: DFN2DIP-PN3F0-090D070US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2946.7	2946.7	2946.7	2946.7	2946.7
2.5°	2960.0	2946.7	2917.2	2944.1	2938.8
5°	2946.7	2933.4	2898.6	2922.6	2914.7
7.5°	2922.6	2906.8	2869.4	2879.9	2866.6
10°	2890.7	2872.0	2818.8	2810.6	2794.7
12.5°	2850.7	2826.7	2754.6	2738.7	2709.3
15°	2802.7	2773.3	2682.7	2632.0	2605.5
17.5°	2746.7	2704.0	2591.9	2533.3	2490.6
20°	2682.7	2629.2	2495.9	2429.5	2370.6
22.5°	2613.4	2552.0	2397.2	2306.7	2266.8
25°	2544.1	2458.6	2282.7	2173.4	2133.3
27.5°	2461.5	2370.6	2176.0	2050.6	1989.2
30°	2373.5	2271.9	2058.6	1922.8	1850.6
32.5°	2288.0	2165.2	1946.8	1786.7	1719.9
35°	2192.1	2056.0	1821.5	1653.4	1594.6
37.5°	2098.7	1951.9	1704.1	1519.9	1453.4
40°	2000.0	1840.2	1581.3	1392.0	1322.7
42.5°	1898.7	1728.1	1458.7	1261.3	1194.8
45°	1792.1	1613.3	1333.4	1143.8	1079.9
47.5°	1690.8	1501.5	1213.5	1023.9	965.4
50°	1578.7	1389.4	1096.1	911.9	856.1
52.5°	1469.3	1269.2	984.0	808.0	757.4
55°	1362.6	1154.6	866.6	706.8	656.1
57.5°	1253.4	1040.1	762.8	613.4	570.7
60°	1141.3	928.0	653.3	517.5	474.8
62.5°	1032.1	818.8	559.9	432.1	410.8
65°	920.0	703.9	464.0	373.4	365.3
67.5°	813.4	597.2	373.4	327.9	320.0
70°	701.4	493.4	309.3	282.7	271.9
72.5°	594.7	397.2	258.6	237.3	232.0
75°	490.6	303.9	213.3	194.6	192.1
77.5°	386.7	215.9	168.0	157.3	151.9
80°	290.6	154.8	127.9	117.4	117.4
82.5°	202.6	104.1	88.0	82.6	82.6
85°	114.5	58.5	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.6	19.0	51.8	48.6	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.7	94.7	92.0
97.5°	128.5	142.2	148.1	148.1	148.1
100°	187.7	199.9	204.1	204.1	202.5
102.5°	250.1	259.0	264.9	266.5	264.9
105°	318.3	322.5	325.7	328.4	328.4
107.5°	386.0	392.3	392.3	393.4	386.0
110°	451.5	460.0	460.0	460.0	455.7

TEST NUMBER: P914046

CATALOG NUMBER: DFN2DIP-PN3F0-090D070US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.4	531.4	529.8	525.5	522.4
115°	592.2	600.6	598.0	596.4	592.2
117.5°	661.4	673.0	665.7	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.1	797.8	794.6
125°	861.3	874.5	870.3	865.5	864.0
127.5°	926.3	942.7	936.9	930.6	926.3
130°	987.1	1006.1	1003.5	1000.4	994.5
132.5°	1055.3	1070.2	1071.2	1063.8	1059.5
135°	1114.0	1130.4	1133.6	1131.9	1127.7
137.5°	1179.6	1192.8	1195.4	1194.4	1188.0
140°	1237.2	1250.5	1257.8	1257.8	1252.0
142.5°	1296.4	1309.6	1313.8	1315.4	1309.6
145°	1352.5	1363.0	1371.5	1373.1	1367.3
147.5°	1402.7	1415.9	1422.3	1424.9	1419.1
150°	1454.5	1463.5	1469.3	1474.1	1469.3
152.5°	1500.5	1509.5	1516.9	1522.7	1516.9
155°	1546.5	1550.7	1555.5	1562.9	1558.1
157.5°	1586.2	1589.4	1592.0	1602.6	1595.1
160°	1621.6	1624.8	1626.3	1635.3	1629.0
162.5°	1654.4	1654.4	1656.0	1666.0	1658.6
165°	1682.4	1680.8	1680.8	1691.4	1683.9
167.5°	1707.8	1703.0	1703.0	1713.6	1706.2
170°	1726.8	1722.6	1721.0	1731.5	1722.6
172.5°	1740.0	1735.7	1734.2	1744.8	1735.7
175°	1750.6	1746.4	1743.2	1753.7	1744.8
177.5°	1756.4	1752.1	1749.0	1758.0	1749.0
180°	1753.7	1753.7	1753.7	1753.7	1753.7

TEST NUMBER: P914046

CATALOG NUMBER: DFN2DIP-PN3F0-090D070US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.89	12.76	12.80	13.69	14.89	7.85	8.73	8.77	9.66	10.85
	3H	13.56	14.34	14.49	15.28	16.50	9.04	9.82	9.97	10.76	11.98
	4H	14.17	14.91	15.11	15.85	17.08	9.49	10.23	10.43	11.17	12.40
	6H	14.59	15.27	15.54	16.22	17.46	9.80	10.48	10.76	11.44	12.68
	8H	14.71	15.36	15.67	16.33	17.57	9.89	10.54	10.85	11.51	12.75
	12H	14.77	15.39	15.74	16.35	17.61	9.93	10.55	10.90	11.51	12.78
4H	2H	11.91	12.65	12.86	13.59	14.82	8.45	9.19	9.40	10.13	11.36
	3H	13.73	14.35	14.69	15.32	16.57	9.80	10.41	10.76	11.39	12.63
	4H	14.42	14.98	15.39	15.95	17.22	10.34	10.90	11.31	11.87	13.14
	6H	14.94	15.42	15.92	16.41	17.68	10.76	11.24	11.74	12.23	13.50
	8H	15.11	15.56	16.09	16.54	17.83	10.88	11.33	11.87	12.32	13.60
	12H	15.20	15.61	16.20	16.61	17.90	10.95	11.35	11.95	12.35	13.64
8H	4H	14.39	14.84	15.38	15.83	17.11	10.62	11.07	11.60	12.06	13.34
	6H	14.95	15.33	15.96	16.35	17.63	11.13	11.50	12.14	12.53	13.81
	8H	15.17	15.49	16.18	16.51	17.81	11.32	11.65	12.34	12.66	13.96
	12H	15.30	15.59	16.32	16.60	17.94	11.44	11.72	12.45	12.73	14.08
12H	4H	14.35	14.75	15.35	15.76	17.04	10.63	11.03	11.63	12.04	13.32
	6H	14.93	15.26	15.94	16.27	17.57	11.18	11.51	12.20	12.52	13.82
	8H	15.15	15.44	16.17	16.44	17.79	11.39	11.68	12.41	12.69	14.03

END OF REPORT