

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916588

Luminaire Tested: DFN2DIP-PN3F0-030D030US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916588
REPORT IS A COMBINATION OF REPORTS P899511 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D030US930-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4586.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916588
CATALOG NUMBER: DFN2DIP-PN3F0-030D030US930-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P916588

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59	53
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	46	44	42	37
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	33	29	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	30	26	24	21
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	27	24	21	18
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1113	1113	1113
5°	1114	1096	1104
10°	1104	1081	1089
15°	1087	1062	1065
20°	1064	1037	1040
25°	1042	1006	1012
30°	1014	978	977
35°	987	945	939
40°	955	911	903
45°	922	877	866
50°	886	842	824
55°	849	801	785
60°	807	752	740
65°	760	702	687
70°	701	640	630
75°	620	567	576
80°	522	472	476
85°	368	312	310

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 922 cd/sqm



TEST NUMBER: P916588

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.0
10°-20°	252.0	5.5
20°-30°	370.4	8.1
30°-40°	430.2	9.4
40°-50°	429.7	9.4
50°-60°	374.6	8.2
60°-70°	277.0	6.0
70°-80°	156.7	3.4
80°-90°	43.5	0.9
90°-100°	47.9	1.0
100°-110°	152.1	3.3
110°-120°	260.3	5.7
120°-130°	342.3	7.5
130°-140°	384.2	8.4
140°-150°	376.8	8.2
150°-160°	316.1	6.9
160°-170°	209.6	4.6
170°-180°	73.3	1.6
0°-30°	712.0	15.5
0°-40°	1142.2	24.9
0°-60°	1946.5	42.4
0°-90°	2423.6	52.8
90°-120°	460.2	10.0
90°-150°	1563.5	34.1
90°-180°	2162.0	47.1
0°-180°	4586.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	1	8	23	21	22	4
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	



TEST NUMBER: P916588

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P916588

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6



TEST NUMBER: P916588
 CATALOG NUMBER: DFN2DIP-PN3F0-030D030US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.86	8.75	8.79	9.70	10.93	7.42	8.31	8.35	9.26	10.49
	3H	9.52	10.31	10.46	11.27	12.53	9.04	9.83	9.98	10.79	12.04
	4H	10.10	10.86	11.06	11.82	13.08	9.62	10.37	10.58	11.33	12.60
	6H	10.50	11.19	11.47	12.16	13.44	10.01	10.70	10.98	11.67	12.95
	8H	10.60	11.26	11.58	12.25	13.52	10.11	10.77	11.09	11.76	13.03
	12H	10.65	11.28	11.63	12.26	13.56	10.15	10.78	11.13	11.76	13.06
4H	2H	8.32	9.08	9.29	10.04	11.30	7.97	8.73	8.94	9.69	10.95
	3H	10.18	10.81	11.16	11.81	13.08	9.78	10.41	10.76	11.40	12.68
	4H	10.89	11.47	11.88	12.46	13.76	10.48	11.05	11.46	12.04	13.34
	6H	11.41	11.90	12.40	12.91	14.21	10.98	11.48	11.98	12.49	13.79
	8H	11.55	12.02	12.55	13.02	14.33	11.13	11.59	12.12	12.59	13.91
	12H	11.62	12.04	12.64	13.06	14.38	11.19	11.60	12.20	12.62	13.94
8H	4H	11.09	11.55	12.09	12.56	13.87	10.72	11.18	11.72	12.19	13.50
	6H	11.71	12.10	12.74	13.14	14.45	11.34	11.72	12.36	12.77	14.08
	8H	11.93	12.27	12.96	13.30	14.63	11.55	11.89	12.58	12.92	14.25
	12H	12.06	12.36	13.09	13.38	14.76	11.66	11.96	12.69	12.98	14.36
12H	4H	11.08	11.49	12.09	12.51	13.83	10.71	11.13	11.73	12.15	13.47
	6H	11.74	12.08	12.77	13.11	14.44	11.38	11.72	12.41	12.75	14.08
	8H	11.98	12.28	13.01	13.30	14.68	11.61	11.91	12.64	12.93	14.31