

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906159

Luminaire Tested: DFN2DIP-PN4F0-110D120US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906159
REPORT IS A COMBINATION OF REPORTS P901288 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D120US835-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21230.0 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 217.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906159

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906159

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44
2	89	81	76	71	81	75	70	66	62	59	56	51	49	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3319	3319	3319
5°	3324	3266	3287
10°	3291	3203	3181
15°	3246	3097	3016
20°	3186	2952	2814
25°	3124	2789	2618
30°	3042	2621	2370
35°	2961	2441	2152
40°	2879	2255	1902
45°	2784	2048	1675
50°	2685	1840	1454
55°	2582	1616	1241
60°	2462	1383	1022
65°	2325	1146	921
70°	2159	925	834
75°	1950	816	760
80°	1647	686	662
85°	1148	460	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2784 cd/sqm

TEST NUMBER: P906159

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	2.0
10°-20°	1169.7	5.5
20°-30°	1642.2	7.7
30°-40°	1790.1	8.4
40°-50°	1645.3	7.7
50°-60°	1292.1	6.1
60°-70°	841.1	4.0
70°-80°	432.9	2.0
80°-90°	117.7	0.6
90°-100°	133.5	0.6
100°-110°	497.8	2.3
110°-120°	1320.3	6.2
120°-130°	2189.8	10.3
130°-140°	2326.1	11.0
140°-150°	2161.8	10.2
150°-160°	1738.1	8.2
160°-170°	1119.9	5.3
170°-180°	385.5	1.8
0°-30°	3238.0	15.3
0°-40°	5028.1	23.7
0°-60°	7965.5	37.5
0°-90°	9357.1	44.1
90°-120°	1951.7	9.2
90°-150°	8629.4	40.6
90°-180°	11873.0	55.9
0°-180°	21230.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	3	35	58	73	79	20
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	

TEST NUMBER: P906159

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4

TEST NUMBER: P906159

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9

TEST NUMBER: P906159

CATALOG NUMBER: DFN2DIP-PN4F0-110D120US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.74	11.53	11.75	12.54	13.90	6.71	7.49	7.72	8.51	9.87
	3H	12.42	13.12	13.44	14.15	15.52	7.89	8.59	8.92	9.62	11.00
	4H	13.03	13.69	14.06	14.72	16.10	8.34	9.01	9.38	10.03	11.42
	6H	13.45	14.06	14.49	15.09	16.49	8.66	9.27	9.71	10.31	11.70
	8H	13.58	14.16	14.63	15.21	16.60	8.75	9.33	9.80	10.38	11.77
	12H	13.64	14.19	14.69	15.23	16.65	8.79	9.34	9.85	10.39	11.80
4H	2H	10.75	11.42	11.80	12.45	13.83	7.30	7.96	8.34	8.99	10.38
	3H	12.58	13.13	13.63	14.19	15.59	8.65	9.20	9.70	10.25	11.65
	4H	13.28	13.78	14.33	14.83	16.25	9.19	9.70	10.25	10.75	12.17
	6H	13.79	14.22	14.86	15.30	16.71	9.61	10.04	10.68	11.12	12.53
	8H	13.97	14.37	15.03	15.44	16.87	9.74	10.14	10.80	11.21	12.64
	12H	14.06	14.43	15.14	15.51	16.94	9.80	10.17	10.89	11.25	12.68
8H	4H	13.24	13.64	14.31	14.71	16.14	9.47	9.88	10.54	10.94	12.37
	6H	13.81	14.14	14.90	15.25	16.67	9.99	10.32	11.08	11.43	12.86
	8H	14.03	14.32	15.12	15.41	16.86	10.18	10.47	11.28	11.56	13.01
	12H	14.16	14.42	15.26	15.51	16.99	10.30	10.56	11.40	11.64	13.13
12H	4H	13.19	13.56	14.27	14.63	16.07	9.47	9.84	10.56	10.92	12.35
	6H	13.78	14.08	14.88	15.17	16.61	10.04	10.33	11.13	11.42	12.87
	8H	14.00	14.26	15.10	15.35	16.83	10.25	10.51	11.35	11.59	13.08

END OF REPORT