

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908621

Luminaire Tested: DFN2DIP-PN4F0-040D090US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908621
REPORT IS A COMBINATION OF REPORTS P901219 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-040D090US840-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12996.9 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 100
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908621

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908621

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	93	89	86	82	84	80	77	74	64	61	59	48	47	46	34	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	26	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	27	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	18	15	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	24	43	32	26	22	26	21	18	20	17	14	15	13	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1147	1147	1147
5°	1149	1131	1139
10°	1140	1116	1124
15°	1123	1098	1100
20°	1100	1073	1076
25°	1078	1042	1047
30°	1050	1014	1011
35°	1023	981	973
40°	990	947	937
45°	957	913	900
50°	921	878	857
55°	884	837	817
60°	841	788	772
65°	795	738	719
70°	736	677	661
75°	654	603	609
80°	556	509	508
85°	402	348	339

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1635 cd/sqm

TEST NUMBER: P908621

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	1.1
10°-20°	416.2	3.2
20°-30°	611.7	4.7
30°-40°	710.5	5.5
40°-50°	709.6	5.5
50°-60°	618.7	4.8
60°-70°	457.4	3.5
70°-80°	258.8	2.0
80°-90°	73.7	0.6
90°-100°	101.2	0.8
100°-110°	377.0	2.9
110°-120°	1000.0	7.7
120°-130°	1658.6	12.8
130°-140°	1761.8	13.6
140°-150°	1637.4	12.6
150°-160°	1316.4	10.1
160°-170°	848.2	6.5
170°-180°	292.0	2.2
0°-30°	1175.9	9.0
0°-40°	1886.3	14.5
0°-60°	3214.6	24.7
0°-90°	4004.4	30.8
90°-120°	1478.2	11.4
90°-150°	6535.9	50.3
90°-180°	8992.0	69.2
0°-180°	12996.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1468	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	2	27	44	56	60	12
95°	144	71	86	98	95	171
105°	675	741	135	160	169	721
115°	1276	1314	1370	342	182	1256
125°	1804	1833	1876	1891	1898	1609
135°	2233	2268	2288	2311	2306	1725
145°	2590	2588	2626	2641	2630	1620
155°	2852	2832	2859	2872	2854	1314
165°	3005	2992	2999	3014	2999	849
175°	3074	3058	3063	3078	3056	293
180°	3067	3067	3067	3067	3067	

TEST NUMBER: P908621

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.8	1571.8	1571.8	1571.8	1571.8
2.5°	1580.9	1573.4	1556.7	1571.8	1568.9
5°	1571.8	1565.8	1549.1	1561.2	1558.3
7.5°	1561.2	1552.2	1535.5	1547.7	1544.7
10°	1544.7	1534.1	1516.0	1528.0	1523.5
12.5°	1521.9	1512.9	1494.8	1502.4	1499.2
15°	1496.2	1487.2	1467.5	1473.6	1466.1
17.5°	1464.5	1455.5	1435.8	1443.3	1435.8
20°	1429.7	1420.7	1399.6	1404.0	1398.2
22.5°	1395.0	1381.4	1361.7	1361.7	1358.7
25°	1354.1	1342.1	1316.5	1319.4	1316.5
27.5°	1308.8	1298.2	1278.7	1274.1	1266.7
30°	1263.5	1251.4	1228.8	1224.3	1218.2
32.5°	1215.2	1206.2	1181.9	1172.9	1166.7
35°	1168.3	1153.3	1129.0	1119.9	1112.4
37.5°	1115.4	1101.8	1077.5	1067.0	1059.4
40°	1061.1	1048.8	1024.6	1011.2	1005.1
42.5°	1008.1	995.9	971.9	956.6	947.7
45°	950.7	940.2	917.4	900.9	894.7
47.5°	894.7	884.1	860.0	843.3	834.4
50°	835.8	828.2	807.1	785.9	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.3	674.1	666.6
57.5°	660.5	653.0	633.2	615.1	609.0
60°	601.5	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.5	503.3	497.3
65°	485.2	476.1	461.0	447.4	439.9
67.5°	424.7	417.1	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.7
75°	253.9	251.0	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.1
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	2.1	26.7	44.2	55.6	59.8
92.5°	55.6	46.7	53.2	57.8	59.8
95°	144.2	70.9	86.4	97.8	95.4
97.5°	259.6	77.8	113.1	119.9	122.0
100°	392.9	88.9	126.5	144.2	148.7
102.5°	539.3	535.0	131.0	155.2	162.1
105°	674.7	741.4	135.4	159.8	168.6
107.5°	832.3	887.7	140.0	164.2	173.2
110°	983.3	1029.8	388.5	166.5	175.3

TEST NUMBER: P908621

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1125.4	1165.2	1127.5	170.8	177.6
115°	1276.2	1313.8	1369.5	341.8	182.1
117.5°	1407.1	1451.5	1489.3	1171.8	590.4
120°	1553.7	1586.9	1627.0	1653.6	1353.9
122.5°	1677.9	1713.4	1758.0	1771.1	1773.5
125°	1804.3	1833.3	1875.5	1891.1	1897.6
127.5°	1919.8	1950.9	1984.4	2006.5	2008.6
130°	2028.6	2064.3	2088.5	2112.9	2110.9
132.5°	2139.6	2168.6	2192.8	2212.9	2210.8
135°	2232.9	2268.5	2288.3	2310.7	2306.2
137.5°	2330.5	2357.0	2379.4	2401.6	2395.0
140°	2425.8	2443.8	2468.0	2488.0	2477.0
142.5°	2506.0	2521.5	2550.2	2567.9	2556.9
145°	2590.3	2587.9	2625.7	2641.2	2630.1
147.5°	2663.3	2656.8	2694.4	2705.5	2696.7
150°	2734.5	2719.0	2754.5	2767.6	2756.6
152.5°	2794.3	2776.6	2809.8	2823.3	2807.7
155°	2852.1	2832.3	2858.8	2872.1	2854.4
157.5°	2898.7	2881.0	2901.0	2916.6	2898.7
160°	2938.7	2925.3	2938.7	2951.9	2936.4
162.5°	2974.1	2960.8	2971.9	2987.5	2967.5
165°	3005.2	2991.9	2998.6	3014.1	2998.6
167.5°	3029.7	3016.3	3023.0	3038.6	3018.6
170°	3049.7	3036.3	3040.7	3056.3	3036.3
172.5°	3062.9	3049.7	3054.1	3069.7	3049.7
175°	3073.9	3058.4	3062.9	3078.4	3056.3
177.5°	3078.4	3062.9	3065.2	3080.8	3060.8
180°	3067.4	3067.4	3067.4	3067.4	3067.4

TEST NUMBER: P908621

CATALOG NUMBER: DFN2DIP-PN4F0-040D090US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.65	6.36	6.76	7.47	8.99	5.21	5.92	6.32	7.03	8.55
	3H	7.30	7.94	8.42	9.05	10.59	6.82	7.46	7.93	8.57	10.11
	4H	7.89	8.49	9.01	9.60	11.15	7.40	8.00	8.52	9.12	10.66
	6H	8.28	8.84	9.41	9.95	11.51	7.79	8.35	8.92	9.46	11.02
	8H	8.38	8.91	9.52	10.04	11.59	7.89	8.42	9.03	9.55	11.10
	12H	8.43	8.93	9.57	10.05	11.62	7.93	8.43	9.07	9.55	11.12
4H	2H	6.10	6.70	7.23	7.81	9.36	5.74	6.35	6.88	7.46	9.00
	3H	7.95	8.46	9.09	9.59	11.15	7.55	8.05	8.69	9.19	10.75
	4H	8.66	9.13	9.80	10.25	11.83	8.24	8.71	9.38	9.83	11.41
	6H	9.17	9.57	10.32	10.72	12.28	8.75	9.14	9.89	10.29	11.86
	8H	9.32	9.69	10.46	10.83	12.41	8.89	9.26	10.04	10.40	11.99
	12H	9.39	9.72	10.55	10.88	12.46	8.94	9.28	10.11	10.43	12.02
8H	4H	8.85	9.22	9.99	10.36	11.94	8.47	8.85	9.62	9.99	11.57
	6H	9.47	9.78	10.64	10.96	12.54	9.10	9.40	10.26	10.59	12.17
	8H	9.70	9.96	10.87	11.13	12.73	9.31	9.58	10.48	10.74	12.34
	12H	9.82	10.06	11.00	11.22	12.85	9.42	9.65	10.60	10.81	12.45
12H	4H	8.82	9.16	9.99	10.31	11.90	8.46	8.80	9.63	9.95	11.54
	6H	9.50	9.77	10.68	10.93	12.53	9.14	9.41	10.31	10.57	12.17
	8H	9.74	9.98	10.92	11.13	12.77	9.37	9.60	10.54	10.76	12.40

END OF REPORT