

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919337

Luminaire Tested: DFN2DIP-PN3F0-030D080US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919337
REPORT IS A COMBINATION OF REPORTS P901101 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D080US935-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9376.3 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919337

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919337

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35			27
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30			23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25			19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21			16
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18			14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16			12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14			11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12			9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11			8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10			8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1175	1175	1175
5°	1176	1158	1166
10°	1166	1141	1150
15°	1148	1122	1124
20°	1124	1095	1099
25°	1100	1063	1069
30°	1071	1033	1031
35°	1043	998	992
40°	1008	962	954
45°	974	927	915
50°	936	889	870
55°	897	846	829
60°	852	795	781
65°	803	741	726
70°	741	677	665
75°	655	599	609
80°	551	499	502
85°	388	330	327

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1570 cd/sqm

TEST NUMBER: P919337

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.0
10°-20°	266.2	2.8
20°-30°	391.1	4.2
30°-40°	454.3	4.8
40°-50°	453.7	4.8
50°-60°	395.6	4.2
60°-70°	292.5	3.1
70°-80°	165.5	1.8
80°-90°	47.8	0.5
90°-100°	76.7	0.8
100°-110°	285.7	3.0
110°-120°	757.9	8.1
120°-130°	1256.9	13.4
130°-140°	1335.2	14.2
140°-150°	1240.9	13.2
150°-160°	997.6	10.6
160°-170°	642.8	6.9
170°-180°	221.3	2.4
0°-30°	751.9	8.0
0°-40°	1206.2	12.9
0°-60°	2055.6	21.9
0°-90°	2561.3	27.3
90°-120°	1120.2	11.9
90°-150°	4953.3	52.8
90°-180°	6815.0	72.7
0°-180°	9376.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	1005	1001	991	998	996	95
15°	957	951	938	942	938	269
25°	866	858	842	844	842	398
35°	747	737	722	716	711	467
45°	608	601	587	576	572	469
55°	460	454	443	431	426	411
65°	310	304	295	286	281	307
75°	162	160	156	150	152	173
85°	40	39	38	35	34	44
90°	2	20	34	42	45	9
95°	109	54	66	74	72	129
105°	511	562	103	121	128	546
115°	967	996	1038	259	138	952
125°	1367	1389	1421	1433	1438	1220
135°	1692	1719	1734	1751	1748	1307
145°	1963	1961	1990	2002	1993	1228
155°	2161	2146	2167	2177	2163	996
165°	2278	2268	2272	2284	2272	643
175°	2330	2318	2321	2333	2316	222
180°	2325	2325	2325	2325	2325	

TEST NUMBER: P919337

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1005.0	1005.0	1005.0	1005.0	1005.0
2.5°	1010.9	1006.1	995.4	1005.0	1003.2
5°	1005.0	1001.3	990.6	998.3	996.4
7.5°	998.3	992.6	981.9	989.7	987.7
10°	987.7	980.9	969.4	977.1	974.2
12.5°	973.2	967.4	955.9	960.6	958.7
15°	956.7	951.1	938.4	942.3	937.5
17.5°	936.4	930.7	918.1	922.9	918.1
20°	914.2	908.4	894.9	897.8	894.0
22.5°	892.1	883.4	870.7	870.7	868.7
25°	865.9	858.2	841.8	843.7	841.8
27.5°	836.9	830.1	817.6	814.8	809.9
30°	808.0	800.2	785.7	782.8	778.9
32.5°	777.1	771.3	755.8	749.9	746.1
35°	747.1	737.4	721.9	716.1	711.3
37.5°	713.3	704.6	689.1	682.3	677.4
40°	678.5	670.7	655.2	646.6	642.7
42.5°	644.6	636.9	621.5	611.7	606.0
45°	608.0	601.1	586.6	576.0	572.1
47.5°	572.1	565.4	549.9	539.2	533.5
50°	534.4	529.6	516.1	502.6	497.7
52.5°	497.7	490.9	478.5	467.8	461.0
55°	460.1	454.3	442.6	431.1	426.3
57.5°	422.3	417.5	404.9	393.3	389.4
60°	384.6	380.8	367.3	356.6	353.8
62.5°	347.9	341.1	331.5	321.8	318.0
65°	310.3	304.4	294.8	286.1	281.3
67.5°	271.6	266.7	258.0	251.3	247.5
70°	235.8	232.0	223.3	216.5	212.7
72.5°	199.1	195.2	190.4	183.7	180.8
75°	162.3	160.5	155.6	149.8	151.8
77.5°	129.5	125.6	123.6	120.8	118.0
80°	96.7	95.7	93.7	90.8	88.9
82.5°	65.7	65.7	64.8	60.9	60.9
85°	39.6	38.7	37.7	34.8	33.8
87.5°	17.4	15.5	13.5	10.7	9.6
90°	1.6	20.1	33.6	42.1	45.4
92.5°	42.1	35.4	40.4	43.7	45.4
95°	109.3	53.7	65.5	74.1	72.3
97.5°	196.7	58.9	85.7	90.9	92.5
100°	297.8	67.3	95.9	109.3	112.6
102.5°	408.7	405.4	99.3	117.6	122.9
105°	511.3	561.9	102.6	121.1	127.9
107.5°	630.8	672.7	106.1	124.4	131.2
110°	745.3	780.4	294.5	126.2	132.9

TEST NUMBER: P919337

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	852.9	883.0	854.5	129.4	134.7
115°	967.2	995.7	1037.8	259.1	138.0
117.5°	1066.4	1100.0	1128.8	888.0	447.5
120°	1177.5	1202.6	1233.0	1253.2	1026.1
122.5°	1271.5	1298.6	1332.3	1342.3	1344.1
125°	1367.4	1389.4	1421.3	1433.1	1438.1
127.5°	1454.9	1478.5	1503.9	1520.6	1522.2
130°	1537.4	1564.3	1582.8	1601.4	1599.7
132.5°	1621.5	1643.5	1661.9	1677.1	1675.4
135°	1692.2	1719.2	1734.1	1751.2	1747.7
137.5°	1766.2	1786.3	1803.3	1820.1	1815.1
140°	1838.4	1852.0	1870.4	1885.6	1877.1
142.5°	1899.2	1910.9	1932.7	1946.1	1937.7
145°	1963.1	1961.3	1989.9	2001.6	1993.2
147.5°	2018.4	2013.4	2041.9	2050.4	2043.8
150°	2072.3	2060.5	2087.5	2097.5	2089.1
152.5°	2117.7	2104.3	2129.4	2139.7	2127.9
155°	2161.4	2146.5	2166.6	2176.6	2163.3
157.5°	2196.7	2183.4	2198.6	2210.4	2196.7
160°	2227.1	2217.0	2227.1	2237.1	2225.3
162.5°	2253.9	2243.9	2252.3	2264.1	2248.9
165°	2277.5	2267.5	2272.5	2284.2	2272.5
167.5°	2296.0	2285.9	2291.0	2302.8	2287.7
170°	2311.3	2301.0	2304.5	2316.3	2301.0
172.5°	2321.3	2311.3	2314.6	2326.4	2311.3
175°	2329.6	2317.8	2321.3	2333.0	2316.3
177.5°	2333.0	2321.3	2323.0	2334.8	2319.6
180°	2324.6	2324.6	2324.6	2324.6	2324.6

TEST NUMBER: P919337

CATALOG NUMBER: DFN2DIP-PN3F0-030D080US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.20	5.89	6.33	7.01	8.57	4.76	5.45	5.89	6.57	8.13
	3H	6.84	7.46	7.98	8.59	10.16	6.36	6.97	7.50	8.10	9.68
	4H	7.41	8.00	8.56	9.13	10.71	6.93	7.52	8.08	8.65	10.23
	6H	7.80	8.34	8.96	9.47	11.07	7.31	7.85	8.47	8.98	10.58
	8H	7.90	8.41	9.06	9.56	11.15	7.41	7.92	8.57	9.07	10.66
	12H	7.94	8.43	9.10	9.57	11.18	7.44	7.93	8.60	9.07	10.68
4H	2H	5.63	6.22	6.79	7.35	8.93	5.28	5.87	6.44	7.00	8.58
	3H	7.48	7.97	8.64	9.12	10.72	7.08	7.57	8.24	8.72	10.32
	4H	8.18	8.63	9.34	9.77	11.39	7.76	8.21	8.93	9.36	10.97
	6H	8.68	9.06	9.85	10.23	11.84	8.26	8.64	9.43	9.81	11.41
	8H	8.82	9.18	9.99	10.34	11.96	8.40	8.76	9.56	9.91	11.54
	12H	8.88	9.21	10.07	10.38	12.01	8.45	8.77	9.63	9.94	11.57
8H	4H	8.36	8.72	9.53	9.88	11.50	7.99	8.35	9.16	9.51	11.13
	6H	8.97	9.27	10.16	10.47	12.09	8.60	8.90	9.79	10.10	11.72
	8H	9.19	9.45	10.38	10.63	12.27	8.81	9.07	10.00	10.24	11.88
	12H	9.31	9.54	10.51	10.71	12.38	8.91	9.14	10.11	10.31	11.98
12H	4H	8.33	8.66	9.52	9.83	11.46	7.97	8.30	9.16	9.47	11.10
	6H	9.00	9.26	10.19	10.44	12.08	8.64	8.90	9.83	10.08	11.71
	8H	9.23	9.46	10.43	10.63	12.31	8.86	9.09	10.06	10.26	11.93