

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908699

Luminaire Tested: DFN2DIP-PN4F0-060D100US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908699
REPORT IS A COMBINATION OF REPORTS P901242 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-060D100US840-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15148.0 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 129.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908699

CATALOG NUMBER: DFN2DIP-PN4F0-060D100US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908699

CATALOG NUMBER: DFN2DIP-PN4F0-060D100US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	30	28	26
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1828	1828	1828
5°	1831	1799	1811
10°	1813	1764	1752
15°	1788	1706	1661
20°	1755	1626	1550
25°	1721	1536	1442
30°	1676	1444	1306
35°	1631	1345	1185
40°	1586	1242	1048
45°	1533	1128	923
50°	1479	1013	801
55°	1422	890	683
60°	1356	762	563
65°	1281	631	507
70°	1189	509	460
75°	1074	450	419
80°	907	378	364
85°	632	253	276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1815 cd/sqm

TEST NUMBER: P908699

CATALOG NUMBER: DFN2DIP-PN4F0-060D100US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	1.5
10°-20°	644.3	4.3
20°-30°	904.6	6.0
30°-40°	986.1	6.5
40°-50°	906.3	6.0
50°-60°	711.7	4.7
60°-70°	463.3	3.1
70°-80°	238.5	1.6
80°-90°	66.9	0.4
90°-100°	112.4	0.7
100°-110°	418.9	2.8
110°-120°	1111.1	7.3
120°-130°	1842.9	12.2
130°-140°	1957.5	12.9
140°-150°	1819.3	12.0
150°-160°	1462.7	9.7
160°-170°	942.5	6.2
170°-180°	324.4	2.1
0°-30°	1783.6	11.8
0°-40°	2769.6	18.3
0°-60°	4387.7	29.0
0°-90°	5156.3	34.0
90°-120°	1642.4	10.8
90°-150°	7262.1	47.9
90°-180°	9992.0	66.0
0°-180°	15148.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2090	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	2	30	49	62	66	14
95°	160	79	96	109	106	190
105°	750	824	151	177	187	801
115°	1418	1460	1522	380	202	1396
125°	2005	2037	2084	2101	2108	1788
135°	2481	2520	2542	2567	2562	1916
145°	2878	2876	2917	2935	2922	1800
155°	3169	3147	3176	3191	3172	1460
165°	3339	3324	3332	3349	3332	943
175°	3416	3398	3403	3420	3396	325
180°	3408	3408	3408	3408	3408	

TEST NUMBER: P908699

CATALOG NUMBER: DFN2DIP-PN4F0-060D100US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.3	2504.3	2504.3	2504.3	2504.3
2.5°	2515.6	2504.3	2479.2	2502.0	2497.5
5°	2504.3	2493.0	2463.4	2483.9	2477.1
7.5°	2483.9	2470.3	2438.6	2447.5	2436.2
10°	2456.6	2440.7	2395.6	2388.6	2375.1
12.5°	2422.8	2402.3	2341.0	2327.5	2302.5
15°	2381.9	2356.8	2279.9	2236.9	2214.2
17.5°	2334.3	2297.9	2202.7	2152.9	2116.7
20°	2279.9	2234.4	2121.2	2064.7	2014.7
22.5°	2221.0	2168.8	2037.3	1960.4	1926.4
25°	2162.1	2089.5	1940.0	1847.1	1813.0
27.5°	2091.9	2014.7	1849.3	1742.7	1690.6
30°	2017.1	1930.8	1749.5	1634.1	1572.8
32.5°	1944.5	1840.2	1654.6	1518.4	1461.7
35°	1863.0	1747.4	1548.0	1405.1	1355.1
37.5°	1783.6	1658.8	1448.2	1291.7	1235.2
40°	1699.7	1563.9	1343.8	1183.0	1124.1
42.5°	1613.7	1468.6	1239.7	1071.9	1015.4
45°	1523.0	1371.0	1133.3	972.1	917.8
47.5°	1436.9	1276.1	1031.3	870.2	820.4
50°	1341.7	1180.8	931.5	775.0	727.6
52.5°	1248.6	1078.6	836.3	686.7	643.7
55°	1158.0	981.3	736.5	600.7	557.5
57.5°	1065.2	883.8	648.2	521.3	484.9
60°	970.0	788.7	555.2	439.8	403.4
62.5°	877.2	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.4	317.4	310.4
67.5°	691.3	507.6	317.4	278.7	272.0
70°	596.0	419.3	262.8	240.2	231.1
72.5°	505.4	337.6	219.7	201.8	197.1
75°	417.0	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.4	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	2.3	29.6	49.2	61.8	66.4
92.5°	61.8	51.8	59.2	64.1	66.4
95°	160.2	78.8	96.0	108.7	106.0
97.5°	288.4	86.3	125.6	133.2	135.6
100°	436.7	98.7	140.6	160.2	165.2
102.5°	599.2	594.5	145.5	172.5	180.1
105°	749.7	823.7	150.6	177.4	187.4
107.5°	924.8	986.3	155.5	182.5	192.4
110°	1092.6	1144.2	431.6	185.1	194.7

TEST NUMBER: P908699

CATALOG NUMBER: DFN2DIP-PN4F0-060D100US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1250.4	1294.6	1252.8	189.8	197.4
115°	1418.0	1459.9	1521.7	379.8	202.4
117.5°	1563.5	1612.8	1654.9	1302.0	656.0
120°	1726.4	1763.2	1807.8	1837.3	1504.4
122.5°	1864.3	1903.8	1953.3	1967.9	1970.6
125°	2004.9	2037.1	2084.0	2101.2	2108.5
127.5°	2133.1	2167.7	2204.8	2229.5	2231.8
130°	2254.0	2293.6	2320.6	2347.7	2345.4
132.5°	2377.3	2409.5	2436.5	2458.7	2456.4
135°	2481.0	2520.5	2542.5	2567.4	2562.4
137.5°	2589.4	2619.0	2643.8	2668.5	2661.1
140°	2695.3	2715.3	2742.2	2764.5	2752.2
142.5°	2784.4	2801.7	2833.6	2853.2	2841.0
145°	2878.1	2875.5	2917.4	2934.7	2922.3
147.5°	2959.2	2951.9	2993.7	3006.1	2996.5
150°	3038.3	3021.0	3060.6	3075.2	3062.9
152.5°	3104.7	3085.1	3122.1	3136.9	3119.7
155°	3169.0	3146.9	3176.5	3191.2	3171.6
157.5°	3220.8	3201.2	3223.4	3240.7	3220.8
160°	3265.3	3250.4	3265.3	3279.9	3262.7
162.5°	3304.5	3289.8	3302.2	3319.4	3297.2
165°	3339.0	3324.4	3331.7	3349.0	3331.7
167.5°	3366.3	3351.3	3359.0	3376.3	3354.0
170°	3388.5	3373.7	3378.6	3395.9	3373.7
172.5°	3403.1	3388.5	3393.6	3410.8	3388.5
175°	3415.5	3398.2	3403.1	3420.5	3395.9
177.5°	3420.5	3403.1	3405.9	3423.1	3400.8
180°	3408.2	3408.2	3408.2	3408.2	3408.2

TEST NUMBER: P908699

CATALOG NUMBER: DFN2DIP-PN4F0-060D100US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.54	8.26	8.63	9.34	10.83	3.51	4.22	4.60	5.31	6.79
	3H	9.22	9.86	10.31	10.95	12.45	4.69	5.33	5.79	6.42	7.92
	4H	9.82	10.43	10.93	11.52	13.03	5.14	5.74	6.24	6.84	8.34
	6H	10.24	10.80	11.36	11.89	13.41	5.45	6.01	6.57	7.11	8.63
	8H	10.36	10.89	11.48	12.01	13.52	5.54	6.07	6.66	7.18	8.69
	12H	10.42	10.93	11.55	12.03	13.57	5.58	6.08	6.70	7.19	8.72
4H	2H	7.55	8.15	8.66	9.25	10.76	4.09	4.70	5.21	5.79	7.30
	3H	9.37	9.87	10.49	10.99	12.51	5.43	5.94	6.55	7.06	8.58
	4H	10.06	10.52	11.18	11.63	13.17	5.98	6.44	7.10	7.55	9.09
	6H	10.57	10.97	11.70	12.10	13.63	6.39	6.79	7.52	7.92	9.45
	8H	10.75	11.12	11.88	12.24	13.79	6.52	6.89	7.65	8.01	9.56
	12H	10.84	11.17	11.99	12.31	13.86	6.58	6.91	7.73	8.05	9.60
8H	4H	10.02	10.39	11.15	11.51	13.06	6.25	6.62	7.38	7.75	9.29
	6H	10.58	10.89	11.74	12.06	13.60	6.77	7.07	7.92	8.24	9.78
	8H	10.80	11.07	11.96	12.22	13.78	6.96	7.22	8.12	8.37	9.94
	12H	10.94	11.17	12.10	12.32	13.92	7.07	7.31	8.23	8.45	10.05
12H	4H	9.97	10.30	11.11	11.44	12.99	6.25	6.59	7.40	7.72	9.28
	6H	10.56	10.83	11.72	11.97	13.54	6.82	7.08	7.97	8.23	9.79
	8H	10.78	11.01	11.94	12.15	13.76	7.02	7.26	8.18	8.40	10.00