

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908752

Luminaire Tested: DFN2DIP-PN4F0-080D060US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908752
REPORT IS A COMBINATION OF REPORTS P899653 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-080D060US840-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13360.6 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 122.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908752
CATALOG NUMBER: DFN2DIP-PN4F0-080D060US840-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P908752

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	55	55	55	50
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	46	46	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	40	40	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	34	34	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	30	30	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	26	26	26	23
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	23	23	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2295	2295	2295
5°	2298	2263	2278
10°	2280	2233	2248
15°	2246	2196	2200
20°	2201	2146	2151
25°	2156	2085	2095
30°	2099	2028	2022
35°	2046	1962	1946
40°	1980	1894	1873
45°	1914	1827	1799
50°	1842	1756	1713
55°	1767	1674	1634
60°	1682	1576	1544
65°	1590	1476	1437
70°	1472	1353	1322
75°	1308	1206	1217
80°	1112	1020	1015
85°	804	696	679

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1914 cd/sqm



TEST NUMBER: P908752

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.9	2.2
10°-20°	832.5	6.2
20°-30°	1223.4	9.2
30°-40°	1420.9	10.6
40°-50°	1419.1	10.6
50°-60°	1237.5	9.3
60°-70°	914.7	6.8
70°-80°	517.6	3.9
80°-90°	142.1	1.1
90°-100°	118.6	0.9
100°-110°	376.8	2.8
110°-120°	644.8	4.8
120°-130°	848.0	6.3
130°-140°	951.8	7.1
140°-150°	933.4	7.0
150°-160°	783.0	5.9
160°-170°	519.2	3.9
170°-180°	181.5	1.4
0°-30°	2351.8	17.6
0°-40°	3772.7	28.2
0°-60°	6429.3	48.1
0°-90°	8003.6	59.9
90°-120°	1140.1	8.5
90°-150°	3873.3	29.0
90°-180°	5357.0	40.1
0°-180°	13360.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3144	3144	3144	3144	3144	
5°	3144	3132	3098	3122	3117	298
15°	2992	2975	2935	2947	2932	843
25°	2708	2684	2633	2639	2633	1246
35°	2337	2306	2258	2240	2225	1459
45°	1902	1880	1835	1802	1790	1467
55°	1439	1421	1384	1348	1333	1287
65°	970	952	922	895	880	959
75°	508	502	487	469	475	542
85°	124	121	118	109	106	138
90°	2	21	57	53	55	13
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	



TEST NUMBER: P908752

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US840-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3143.5	3143.5	3143.5	3143.5	3143.5
2.5°	3161.8	3146.7	3113.4	3143.5	3137.8
5°	3143.5	3131.7	3098.4	3122.4	3116.6
7.5°	3122.4	3104.4	3071.1	3095.4	3089.4
10°	3089.4	3068.2	3031.9	3056.0	3047.1
12.5°	3043.8	3025.9	2989.6	3004.7	2998.6
15°	2992.5	2974.6	2935.1	2947.3	2932.2
17.5°	2929.0	2911.0	2871.6	2886.7	2871.6
20°	2859.4	2841.5	2799.1	2808.1	2796.2
22.5°	2790.2	2762.9	2723.4	2723.4	2717.3
25°	2708.4	2684.3	2633.0	2638.8	2633.0
27.5°	2617.6	2596.5	2557.3	2548.3	2533.2
30°	2527.2	2502.7	2457.6	2448.6	2436.4
32.5°	2430.3	2412.4	2363.9	2345.6	2333.5
35°	2336.6	2306.5	2258.1	2239.8	2224.7
37.5°	2230.8	2203.5	2155.2	2133.9	2118.9
40°	2122.1	2097.7	2049.3	2022.4	2010.1
42.5°	2016.3	1991.9	1943.8	1913.3	1895.4
45°	1901.5	1880.3	1834.7	1801.7	1789.6
47.5°	1789.6	1768.4	1719.9	1686.6	1668.6
50°	1671.5	1656.5	1614.1	1571.8	1556.7
52.5°	1556.7	1535.5	1496.4	1463.1	1441.9
55°	1439.0	1420.7	1384.5	1348.3	1333.1
57.5°	1321.0	1306.0	1266.5	1230.2	1218.0
60°	1203.0	1191.1	1148.7	1115.4	1106.4
62.5°	1088.1	1067.0	1036.8	1006.7	994.5
65°	970.5	952.2	922.0	894.7	879.7
67.5°	849.5	834.1	807.2	786.1	773.9
70°	737.6	725.4	698.2	677.0	665.1
72.5°	622.8	610.7	595.5	574.4	565.4
75°	507.7	501.9	486.6	468.6	474.6
77.5°	405.1	392.8	386.8	377.8	368.8
80°	302.5	299.2	293.2	284.2	278.0
82.5°	205.6	205.6	202.7	190.5	190.5
85°	123.8	120.9	118.1	108.8	105.8
87.5°	54.5	48.5	42.3	33.3	30.2
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0



TEST NUMBER: P908752

CATALOG NUMBER: DFN2DIP-PN4F0-080D060US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3



TEST NUMBER: P908752
 CATALOG NUMBER: DFN2DIP-PN4F0-080D060US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.03	11.99	11.90	12.88	14.00	10.59	11.55	11.46	12.44	13.56
	3H	12.70	13.56	13.58	14.46	15.61	12.22	13.08	13.10	13.97	15.12
	4H	13.29	14.11	14.19	15.01	16.17	12.81	13.62	13.70	14.52	15.68
	6H	13.70	14.45	14.61	15.36	16.53	13.21	13.96	14.12	14.87	16.04
	8H	13.81	14.52	14.73	15.45	16.62	13.32	14.03	14.23	14.96	16.13
	12H	13.86	14.54	14.78	15.47	16.66	13.36	14.04	14.28	14.97	16.16
4H	2H	11.50	12.32	12.40	13.22	14.38	11.15	11.97	12.05	12.87	14.03
	3H	13.38	14.06	14.29	15.00	16.17	12.98	13.66	13.89	14.59	15.77
	4H	14.10	14.72	15.02	15.65	16.85	13.68	14.30	14.61	15.23	16.43
	6H	14.63	15.16	15.56	16.11	17.31	14.20	14.74	15.14	15.69	16.89
	8H	14.78	15.28	15.72	16.23	17.44	14.35	14.85	15.29	15.80	17.01
	12H	14.86	15.31	15.82	16.28	17.49	14.42	14.87	15.38	15.83	17.05
8H	4H	14.31	14.81	15.25	15.75	16.97	13.94	14.44	14.87	15.38	16.60
	6H	14.95	15.36	15.91	16.35	17.56	14.57	14.98	15.53	15.97	17.18
	8H	15.17	15.53	16.14	16.51	17.74	14.78	15.15	15.76	16.13	17.36
	12H	15.31	15.63	16.28	16.60	17.88	14.91	15.23	15.88	16.20	17.48
12H	4H	14.30	14.75	15.26	15.71	16.93	13.93	14.39	14.89	15.35	16.57
	6H	14.98	15.34	15.95	16.32	17.55	14.61	14.98	15.59	15.96	17.19
	8H	15.23	15.55	16.20	16.52	17.80	14.85	15.17	15.83	16.15	17.43