

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919482

Luminaire Tested: DFN2DIP-PN3F0-080D090US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919482
REPORT IS A COMBINATION OF REPORTS P899606 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D090US935-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12712.6 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 151.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919482

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919482

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3328	3328	3328
5°	3331	3273	3295
10°	3296	3206	3186
15°	3249	3098	3019
20°	3187	2950	2815
25°	3123	2784	2617
30°	3039	2614	2367
35°	2956	2432	2148
40°	2871	2244	1896
45°	2773	2035	1669
50°	2671	1824	1446
55°	2565	1600	1232
60°	2442	1365	1013
65°	2300	1127	910
70°	2128	905	822
75°	1912	793	744
80°	1598	658	641
85°	1086	428	473

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2773 cd/sqm

TEST NUMBER: P919482

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.8	2.1
10°-20°	732.4	5.8
20°-30°	1028.3	8.1
30°-40°	1120.9	8.8
40°-50°	1030.3	8.1
50°-60°	809.1	6.4
60°-70°	526.6	4.1
70°-80°	271.1	2.1
80°-90°	76.2	0.6
90°-100°	151.6	1.2
100°-110°	481.8	3.8
110°-120°	824.6	6.5
120°-130°	1084.4	8.5
130°-140°	1217.2	9.6
140°-150°	1193.6	9.4
150°-160°	1001.3	7.9
160°-170°	664.0	5.2
170°-180°	232.1	1.8
0°-30°	2027.6	15.9
0°-40°	3148.5	24.8
0°-60°	4987.8	39.2
0°-90°	5861.8	46.1
90°-120°	1458.0	11.5
90°-150°	4953.4	39.0
90°-180°	6851.0	53.9
0°-180°	12712.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2847	2847	2847	2847	2847	
5°	2847	2834	2800	2824	2816	270
15°	2708	2679	2592	2543	2517	763
25°	2458	2375	2205	2100	2061	1130
35°	2118	1986	1760	1597	1540	1326
45°	1731	1559	1288	1105	1043	1337
55°	1316	1116	837	683	634	1176
65°	889	680	448	361	353	881
75°	474	294	206	188	186	501
85°	111	57	49	49	49	127
90°	2	27	72	68	70	13
95°	108	128	132	132	128	120
105°	445	451	455	459	459	469
115°	828	839	836	833	828	818
125°	1204	1222	1216	1209	1207	1076
135°	1557	1580	1584	1582	1576	1203
145°	1890	1905	1916	1919	1911	1181
155°	2161	2167	2174	2184	2177	995
165°	2351	2349	2349	2364	2353	663
175°	2446	2440	2436	2451	2438	232
180°	2451	2451	2451	2451	2451	

TEST NUMBER: P919482

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2846.8	2846.8	2846.8	2846.8	2846.8
2.5°	2859.6	2846.8	2818.4	2844.3	2839.1
5°	2846.8	2834.0	2800.3	2823.6	2815.9
7.5°	2823.6	2808.2	2772.2	2782.3	2769.4
10°	2792.6	2774.7	2723.3	2715.3	2700.0
12.5°	2754.2	2730.9	2661.2	2645.8	2617.4
15°	2707.7	2679.3	2591.8	2542.9	2517.1
17.5°	2653.5	2612.3	2504.0	2447.5	2406.1
20°	2591.8	2540.1	2411.4	2347.2	2290.3
22.5°	2524.8	2465.5	2316.0	2228.5	2189.9
25°	2457.8	2375.3	2205.3	2099.8	2061.0
27.5°	2378.0	2290.3	2102.2	1981.2	1921.8
30°	2293.0	2194.9	1988.8	1857.6	1787.9
32.5°	2210.4	2091.9	1880.8	1726.1	1661.6
35°	2117.8	1986.3	1759.7	1597.4	1540.5
37.5°	2027.6	1885.8	1646.3	1468.3	1404.1
40°	1932.3	1777.8	1527.7	1344.8	1277.8
42.5°	1834.4	1669.6	1409.3	1218.6	1154.3
45°	1731.3	1558.6	1288.2	1105.1	1043.4
47.5°	1633.5	1450.6	1172.3	989.2	932.6
50°	1525.2	1342.4	1058.9	881.0	827.1
52.5°	1419.4	1226.1	950.6	780.7	731.8
55°	1316.4	1115.5	837.2	682.8	633.9
57.5°	1210.9	1004.8	736.9	592.6	551.3
60°	1102.6	896.6	631.1	499.9	458.7
62.5°	997.1	791.0	541.0	417.4	396.9
65°	888.9	680.0	448.2	360.8	352.8
67.5°	785.8	577.0	360.8	316.8	309.2
70°	677.6	476.7	298.8	273.0	262.7
72.5°	574.5	383.7	249.9	229.4	224.1
75°	474.0	293.6	206.1	188.0	185.6
77.5°	373.7	208.5	162.4	152.0	146.8
80°	280.7	149.6	123.6	113.4	113.4
82.5°	195.7	100.6	85.0	79.8	79.8
85°	110.7	56.6	48.9	48.9	48.9
87.5°	41.2	20.5	20.5	18.1	18.1
90°	2.2	26.6	72.4	67.9	70.2
92.5°	45.8	62.1	64.3	66.5	66.5
95°	107.9	128.5	132.2	132.2	128.5
97.5°	179.5	198.7	206.9	206.9	206.9
100°	262.3	279.3	285.2	285.2	283.0
102.5°	349.5	362.0	370.1	372.4	370.1
105°	444.8	450.6	455.1	458.8	458.8
107.5°	539.3	548.2	548.2	549.7	539.3
110°	630.9	642.8	642.8	642.8	636.9

TEST NUMBER: P919482

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	730.0	742.5	740.3	734.4	730.0
115°	827.5	839.3	835.6	833.4	827.5
117.5°	924.3	940.6	930.2	924.3	918.3
120°	1021.8	1038.0	1021.8	1021.8	1015.1
122.5°	1110.4	1131.2	1120.8	1114.9	1110.4
125°	1203.6	1222.0	1216.2	1209.4	1207.3
127.5°	1294.4	1317.3	1309.2	1300.4	1294.4
130°	1379.4	1406.0	1402.3	1397.8	1389.7
132.5°	1474.7	1495.4	1496.8	1486.5	1480.7
135°	1556.7	1579.6	1584.1	1581.8	1576.0
137.5°	1648.3	1666.8	1670.5	1669.0	1660.2
140°	1728.9	1747.3	1757.6	1757.6	1749.5
142.5°	1811.6	1830.1	1836.0	1838.2	1830.1
145°	1890.0	1904.7	1916.5	1918.7	1910.6
147.5°	1960.1	1978.6	1987.4	1991.1	1983.1
150°	2032.6	2045.1	2053.2	2059.9	2053.2
152.5°	2096.8	2109.4	2119.7	2127.9	2119.7
155°	2161.1	2167.0	2173.7	2184.0	2177.4
157.5°	2216.5	2220.9	2224.6	2239.4	2229.0
160°	2266.0	2270.5	2272.7	2285.2	2276.3
162.5°	2311.8	2311.8	2314.0	2328.1	2317.7
165°	2351.0	2348.7	2348.7	2363.5	2353.2
167.5°	2386.4	2379.8	2379.8	2394.5	2384.2
170°	2413.0	2407.1	2404.9	2419.7	2407.1
172.5°	2431.5	2425.6	2423.4	2438.2	2425.6
175°	2446.3	2440.3	2435.9	2450.7	2438.2
177.5°	2454.4	2448.5	2444.0	2456.6	2444.0
180°	2450.7	2450.7	2450.7	2450.7	2450.7

TEST NUMBER: P919482

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.91	11.71	11.91	12.71	14.04	6.87	7.67	7.87	8.68	10.01
	3H	12.58	13.29	13.58	14.31	15.65	8.06	8.77	9.06	9.78	11.13
	4H	13.18	13.86	14.20	14.87	16.23	8.50	9.18	9.52	10.19	11.55
	6H	13.60	14.22	14.63	15.24	16.61	8.81	9.44	9.84	10.46	11.83
	8H	13.72	14.31	14.75	15.35	16.71	8.90	9.49	9.94	10.53	11.89
	12H	13.78	14.34	14.82	15.37	16.76	8.94	9.50	9.98	10.53	11.92
4H	2H	10.92	11.60	11.95	12.61	13.97	7.46	8.14	8.49	9.15	10.51
	3H	12.74	13.30	13.78	14.35	15.72	8.80	9.37	9.84	10.41	11.78
	4H	13.43	13.94	14.47	14.98	16.37	9.35	9.86	10.39	10.90	12.29
	6H	13.93	14.38	14.99	15.44	16.82	9.76	10.20	10.81	11.26	12.65
	8H	14.11	14.52	15.16	15.57	16.97	9.88	10.29	10.93	11.34	12.75
	12H	14.20	14.57	15.27	15.63	17.04	9.94	10.31	11.01	11.38	12.79
8H	4H	13.39	13.80	14.44	14.86	16.26	9.62	10.03	10.67	11.08	12.49
	6H	13.95	14.29	15.02	15.38	16.78	10.13	10.47	11.20	11.56	12.96
	8H	14.16	14.46	15.24	15.54	16.96	10.31	10.61	11.40	11.69	13.11
	12H	14.29	14.56	15.38	15.63	17.09	10.43	10.69	11.51	11.76	13.22
12H	4H	13.34	13.71	14.41	14.78	16.19	9.62	9.99	10.69	11.06	12.47
	6H	13.92	14.22	15.01	15.30	16.72	10.18	10.48	11.26	11.55	12.97
	8H	14.14	14.40	15.22	15.47	16.94	10.38	10.64	11.46	11.72	13.18

END OF REPORT