

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908830

Luminaire Tested: DFN2DIP-PN4F0-100D070US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908830
REPORT IS A COMBINATION OF REPORTS P899676 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D070US840-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14840.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 153.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908830

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908830

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3047	3047	3047
5°	3052	2999	3018
10°	3021	2940	2920
15°	2980	2843	2769
20°	2925	2710	2583
25°	2868	2560	2404
30°	2793	2406	2176
35°	2718	2241	1976
40°	2643	2070	1746
45°	2555	1881	1538
50°	2465	1689	1335
55°	2370	1484	1139
60°	2261	1270	938
65°	2135	1052	845
70°	1982	849	766
75°	1790	749	698
80°	1512	630	607
85°	1053	423	460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2555 cd/sqm

TEST NUMBER: P908830

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	2.6
10°-20°	1073.8	7.2
20°-30°	1507.6	10.2
30°-40°	1643.4	11.1
40°-50°	1510.5	10.2
50°-60°	1186.3	8.0
60°-70°	772.1	5.2
70°-80°	397.5	2.7
80°-90°	107.8	0.7
90°-100°	138.3	0.9
100°-110°	439.6	3.0
110°-120°	752.2	5.1
120°-130°	989.3	6.7
130°-140°	1110.5	7.5
140°-150°	1088.9	7.3
150°-160°	913.5	6.2
160°-170°	605.8	4.1
170°-180°	211.7	1.4
0°-30°	2972.6	20.0
0°-40°	4616.1	31.1
0°-60°	7312.8	49.3
0°-90°	8590.2	57.9
90°-120°	1330.1	9.0
90°-150°	4518.8	30.5
90°-180°	6250.0	42.1
0°-180°	14840.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4106	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3604	3482	3233	3078	3022	1657
35°	3105	2912	2580	2342	2259	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1636	1228	1001	929	1725
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	2	24	66	62	64	15
95°	98	117	121	121	117	109
105°	406	411	415	419	419	428
115°	755	766	762	760	755	747
125°	1098	1115	1109	1103	1101	981
135°	1420	1441	1445	1443	1438	1098
145°	1724	1738	1748	1750	1743	1077
155°	1972	1977	1983	1992	1986	907
165°	2145	2143	2143	2156	2147	605
175°	2232	2226	2222	2236	2224	212
180°	2236	2236	2236	2236	2236	

TEST NUMBER: P908830

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.8	4173.8	4173.8	4173.8	4173.8
2.5°	4192.6	4173.8	4132.1	4170.1	4162.6
5°	4173.8	4154.9	4105.6	4139.7	4128.4
7.5°	4139.7	4117.2	4064.3	4079.1	4060.4
10°	4094.4	4067.9	3992.6	3981.0	3958.6
12.5°	4037.9	4003.8	3901.6	3879.2	3837.5
15°	3969.8	3928.1	3799.8	3728.1	3690.5
17.5°	3890.4	3829.9	3671.3	3588.3	3527.8
20°	3799.8	3724.1	3535.3	3441.2	3357.8
22.5°	3701.7	3614.7	3395.5	3267.3	3210.8
25°	3603.5	3482.5	3233.2	3078.5	3021.6
27.5°	3486.5	3357.8	3082.1	2904.6	2817.6
30°	3361.8	3217.9	2915.8	2723.5	2621.3
32.5°	3240.9	3066.9	2757.5	2530.7	2436.1
35°	3104.9	2912.3	2580.0	2342.0	2258.6
37.5°	2972.7	2764.7	2413.7	2152.8	2058.6
40°	2832.9	2606.5	2239.8	1971.7	1873.5
42.5°	2689.4	2447.7	2066.3	1786.6	1692.3
45°	2538.3	2285.0	1888.8	1620.2	1529.6
47.5°	2394.9	2126.8	1718.8	1450.3	1367.4
50°	2236.1	1968.0	1552.5	1291.6	1212.6
52.5°	2081.0	1797.8	1393.8	1144.5	1072.8
55°	1930.0	1635.5	1227.5	1001.1	929.3
57.5°	1775.3	1473.1	1080.5	868.8	808.3
60°	1616.6	1314.4	925.3	733.0	672.5
62.5°	1461.9	1159.7	793.0	612.0	581.9
65°	1303.2	997.0	657.2	529.0	517.4
67.5°	1152.2	846.0	529.0	464.4	453.2
70°	993.4	698.9	438.0	400.3	385.2
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.9	430.4	302.2	275.7	272.1
77.5°	547.9	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	2.0	24.2	66.0	62.0	64.0
92.5°	41.8	56.7	58.7	60.7	60.7
95°	98.4	117.2	120.7	120.7	117.2
97.5°	163.8	181.3	188.7	188.7	188.7
100°	239.2	254.8	260.1	260.1	258.1
102.5°	318.8	330.2	337.7	339.7	337.7
105°	405.8	411.1	415.2	418.6	418.6
107.5°	492.0	500.1	500.1	501.5	492.0
110°	575.6	586.4	586.4	586.4	581.0



TEST NUMBER: P908830

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	665.9	677.4	675.4	669.9	665.9
115°	754.9	765.7	762.3	760.3	754.9
117.5°	843.1	858.0	848.6	843.1	837.8
120°	932.1	947.0	932.1	932.1	926.0
122.5°	1013.0	1031.9	1022.5	1017.0	1013.0
125°	1097.9	1114.8	1109.4	1103.4	1101.4
127.5°	1180.8	1201.7	1194.4	1186.3	1180.8
130°	1258.4	1282.6	1279.3	1275.3	1267.8
132.5°	1345.3	1364.2	1365.5	1356.1	1350.7
135°	1420.2	1441.0	1445.1	1443.0	1437.6
137.5°	1503.7	1520.6	1523.9	1522.6	1514.5
140°	1577.2	1594.1	1603.5	1603.5	1596.1
142.5°	1652.6	1669.5	1674.9	1676.9	1669.5
145°	1724.1	1737.6	1748.4	1750.4	1743.0
147.5°	1788.2	1805.0	1813.1	1816.4	1809.1
150°	1854.2	1865.6	1873.1	1879.2	1873.1
152.5°	1912.8	1924.3	1933.7	1941.2	1933.7
155°	1971.5	1976.8	1983.0	1992.4	1986.3
157.5°	2022.1	2026.1	2029.4	2043.0	2033.5
160°	2067.2	2071.2	2073.3	2084.7	2076.6
162.5°	2109.0	2109.0	2111.0	2123.7	2114.4
165°	2144.7	2142.6	2142.6	2156.2	2146.7
167.5°	2177.1	2171.0	2171.0	2184.4	2175.0
170°	2201.3	2196.0	2193.9	2207.4	2196.0
172.5°	2218.2	2212.7	2210.7	2224.2	2212.7
175°	2231.6	2226.2	2222.2	2235.6	2224.2
177.5°	2239.1	2233.6	2229.6	2241.1	2229.6
180°	2235.6	2235.6	2235.6	2235.6	2235.6

TEST NUMBER: P908830

CATALOG NUMBER: DFN2DIP-PN4F0-100D070US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.73	12.63	12.62	13.54	14.69	7.69	8.59	8.59	9.50	10.66
	3H	13.42	14.22	14.32	15.14	16.32	8.89	9.69	9.79	10.61	11.79
	4H	14.03	14.79	14.95	15.71	16.90	9.34	10.10	10.26	11.03	12.22
	6H	14.46	15.16	15.39	16.09	17.29	9.67	10.37	10.60	11.30	12.50
	8H	14.59	15.25	15.53	16.20	17.40	9.76	10.43	10.70	11.37	12.58
	12H	14.65	15.28	15.60	16.22	17.45	9.81	10.44	10.75	11.38	12.61
4H	2H	11.76	12.52	12.68	13.44	14.63	8.30	9.06	9.23	9.98	11.17
	3H	13.60	14.23	14.53	15.18	16.39	9.66	10.29	10.59	11.24	12.45
	4H	14.29	14.87	15.24	15.82	17.05	10.21	10.78	11.16	11.73	12.96
	6H	14.81	15.31	15.77	16.28	17.51	10.63	11.13	11.59	12.10	13.33
	8H	14.99	15.45	15.95	16.42	17.66	10.76	11.23	11.72	12.19	13.44
	12H	15.09	15.51	16.07	16.49	17.74	10.83	11.25	11.81	12.23	13.48
8H	4H	14.27	14.73	15.23	15.69	16.94	10.50	10.96	11.46	11.92	13.17
	6H	14.84	15.22	15.82	16.23	17.47	11.02	11.40	12.00	12.41	13.65
	8H	15.06	15.39	16.05	16.39	17.65	11.21	11.55	12.21	12.54	13.81
	12H	15.20	15.50	16.20	16.49	17.79	11.33	11.63	12.33	12.62	13.93
12H	4H	14.22	14.64	15.20	15.62	16.87	10.50	10.92	11.48	11.90	13.15
	6H	14.81	15.15	15.81	16.15	17.41	11.07	11.41	12.06	12.40	13.66
	8H	15.04	15.33	16.04	16.32	17.63	11.28	11.58	12.28	12.57	13.88

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8