

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922058

Luminaire Tested: DFN2DIP-PN3F0-030D060US940-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922058  
REPORT IS A COMBINATION OF REPORTS P899554 AND P896399  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-030D060US940-RLLFLL  
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7008.8 lumens  
Efficiency: N/A  
Efficacy: 100.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 69.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.099  
Total Harmonic Distortion (THDi): 0.979  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922058  
CATALOG NUMBER: DFN2DIP-PN3F0-030D060US940-RLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P922058

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US940-RLFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29	24				24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21				21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18				18
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19	16				16
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17	14				14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13				13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11				11
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10				10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1292	1292	1292
5°	1294	1271	1279
10°	1280	1245	1237
15°	1262	1203	1172
20°	1238	1146	1093
25°	1213	1081	1016
30°	1180	1015	919
35°	1148	944	834
40°	1115	871	736
45°	1077	790	648
50°	1038	709	562
55°	996	621	479
60°	948	530	394
65°	893	438	354
70°	826	351	319
75°	742	308	289
80°	621	256	249
85°	422	166	184

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1674 cd/sqm



TEST NUMBER: P922058

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US940-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.6	1.5
10°-20°	284.5	4.1
20°-30°	399.4	5.7
30°-40°	435.3	6.2
40°-50°	400.1	5.7
50°-60°	314.2	4.5
60°-70°	204.5	2.9
70°-80°	105.3	1.5
80°-90°	31.7	0.5
90°-100°	104.7	1.5
100°-110°	332.7	4.7
110°-120°	569.3	8.1
120°-130°	748.8	10.7
130°-140°	840.5	12.0
140°-150°	824.2	11.8
150°-160°	691.4	9.9
160°-170°	458.5	6.5
170°-180°	160.3	2.3
0°-30°	787.5	11.2
0°-40°	1222.8	17.4
0°-60°	1937.2	27.6
0°-90°	2278.7	32.5
90°-120°	1006.7	14.4
90°-150°	3420.1	48.8
90°-180°	4730.0	67.5
0°-180°	7008.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1106	1101	1088	1097	1094	105
15°	1052	1040	1007	988	978	296
25°	955	922	856	816	800	439
35°	822	771	683	620	598	515
45°	672	605	500	429	405	519
55°	511	433	325	265	246	457
65°	345	264	174	140	137	342
75°	184	114	80	73	72	195
85°	43	22	19	19	19	49
90°	2	18	50	47	48	7
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P922058

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US940-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1105.6	1105.6	1105.6	1105.6	1105.6
2.5°	1110.6	1105.6	1094.6	1104.7	1102.7
5°	1105.6	1100.6	1087.6	1096.6	1093.6
7.5°	1096.6	1090.7	1076.7	1080.6	1075.6
10°	1084.6	1077.6	1057.7	1054.5	1048.7
12.5°	1069.6	1060.6	1033.6	1027.6	1016.5
15°	1051.6	1040.5	1006.6	987.6	977.6
17.5°	1030.5	1014.6	972.5	950.6	934.5
20°	1006.6	986.5	936.5	911.6	889.5
22.5°	980.6	957.5	899.5	865.5	850.5
25°	954.6	922.5	856.5	815.5	800.4
27.5°	923.5	889.5	816.5	769.5	746.4
30°	890.6	852.5	772.4	721.5	694.4
32.5°	858.4	812.4	730.5	670.4	645.3
35°	822.5	771.4	683.4	620.4	598.3
37.5°	787.5	732.4	639.4	570.2	545.4
40°	750.5	690.5	593.3	522.3	496.3
42.5°	712.4	648.5	547.3	473.2	448.3
45°	672.4	605.3	500.3	429.2	405.2
47.5°	634.4	563.4	455.3	384.1	362.2
50°	592.4	521.3	411.3	342.1	321.2
52.5°	551.3	476.3	369.3	303.2	284.2
55°	511.2	433.2	325.1	265.2	246.2
57.5°	470.3	390.2	286.2	230.2	214.1
60°	428.2	348.2	245.1	194.1	178.2
62.5°	387.3	307.2	210.1	162.1	154.2
65°	345.2	264.1	174.1	140.1	137.1
67.5°	305.2	224.1	140.1	123.1	120.0
70°	263.1	185.1	116.0	106.0	102.0
72.5°	223.1	149.0	97.0	89.1	87.0
75°	184.0	114.0	80.1	73.0	72.1
77.5°	145.1	81.0	63.0	59.0	57.0
80°	109.1	58.1	48.0	44.1	44.1
82.5°	76.0	39.1	33.0	31.0	31.0
85°	43.0	21.9	19.0	19.0	19.0
87.5°	16.1	7.9	7.9	7.0	7.0
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7



TEST NUMBER: P922058

CATALOG NUMBER: DFN2DIP-PN3F0-030D060US940-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1



TEST NUMBER: P922058  
 CATALOG NUMBER: DFN2DIP-PN3F0-030D060US940-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.10	6.80	7.20	7.90	9.40	2.07	2.77	3.16	3.86	5.37
	3H	7.76	8.39	8.87	9.49	11.01	3.24	3.87	4.35	4.97	6.49
	4H	8.36	8.96	9.48	10.06	11.58	3.68	4.28	4.80	5.38	6.90
	6H	8.77	9.32	9.89	10.42	11.96	3.99	4.54	5.11	5.64	7.18
	8H	8.89	9.41	10.02	10.53	12.06	4.07	4.59	5.20	5.72	7.25
	12H	8.94	9.44	10.08	10.55	12.11	4.11	4.60	5.24	5.72	7.27
4H	2H	6.10	6.70	7.22	7.80	9.33	2.64	3.24	3.77	4.34	5.87
	3H	7.91	8.41	9.04	9.54	11.07	3.97	4.47	5.10	5.60	7.14
	4H	8.59	9.05	9.73	10.17	11.73	4.51	4.97	5.64	6.09	7.64
	6H	9.09	9.49	10.24	10.63	12.18	4.92	5.31	6.06	6.45	8.00
	8H	9.26	9.63	10.40	10.76	12.33	5.04	5.41	6.18	6.54	8.10
	12H	9.35	9.68	10.51	10.83	12.40	5.10	5.43	6.25	6.57	8.14
8H	4H	8.55	8.91	9.69	10.05	11.61	4.78	5.14	5.92	6.28	7.84
	6H	9.10	9.41	10.26	10.58	12.14	5.28	5.58	6.44	6.76	8.32
	8H	9.32	9.58	10.48	10.73	12.32	5.47	5.73	6.64	6.89	8.47
	12H	9.44	9.68	10.61	10.83	12.44	5.58	5.81	6.75	6.96	8.58
12H	4H	8.49	8.83	9.65	9.97	11.54	4.78	5.11	5.93	6.25	7.82
	6H	9.08	9.34	10.24	10.50	12.08	5.33	5.59	6.50	6.75	8.33
	8H	9.29	9.52	10.46	10.67	12.29	5.53	5.76	6.70	6.91	8.53