

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908867

Luminaire Tested: DFN2DIP-PN4F0-110D070US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908867
REPORT IS A COMBINATION OF REPORTS P901198 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D070US840-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16440.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 166.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908867

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908867

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		75	75	75		63	63	63
1	100	96	92	89		93	89	86	83		78	75	73		67	65	63		57	55	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		50	48	47
3	84	75	68	62		78	70	64	59		61	56	52		53	49	46		45	43	40
4	77	66	59	53		72	62	56	50		55	49	45		47	43	40		41	38	35
5	71	60	52	46		66	56	49	44		49	44	39		43	39	35		37	34	31
6	66	54	46	40		61	51	43	38		45	39	35		39	35	31		34	30	28
7	61	49	41	35		57	46	39	34		41	35	31		36	31	28		31	27	25
8	57	44	37	32		53	42	35	30		37	32	28		33	28	25		29	25	22
9	53	41	33	28		49	38	32	27		34	29	25		30	26	23		27	23	20
10	49	37	30	26		46	35	29	25		32	26	23		28	24	21		25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3351	3351	3351
5°	3357	3299	3320
10°	3323	3234	3212
15°	3278	3128	3046
20°	3217	2981	2842
25°	3155	2816	2644
30°	3072	2647	2393
35°	2990	2465	2173
40°	2907	2277	1921
45°	2811	2069	1692
50°	2711	1858	1468
55°	2607	1632	1253
60°	2487	1397	1032
65°	2348	1157	930
70°	2180	934	842
75°	1969	824	768
80°	1663	693	668
85°	1159	465	506

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2811 cd/sqm

TEST NUMBER: P908867

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.3	2.6
10°-20°	1181.2	7.2
20°-30°	1658.4	10.1
30°-40°	1807.8	11.0
40°-50°	1661.5	10.1
50°-60°	1304.9	7.9
60°-70°	849.4	5.2
70°-80°	437.2	2.7
80°-90°	115.8	0.7
90°-100°	78.7	0.5
100°-110°	293.3	1.8
110°-120°	777.8	4.7
120°-130°	1290.0	7.8
130°-140°	1370.3	8.3
140°-150°	1273.5	7.7
150°-160°	1023.9	6.2
160°-170°	659.7	4.0
170°-180°	227.1	1.4
0°-30°	3269.9	19.9
0°-40°	5077.7	30.9
0°-60°	8044.1	48.9
0°-90°	9446.4	57.5
90°-120°	1149.7	7.0
90°-150°	5083.5	30.9
90°-180°	6994.0	42.5
0°-180°	16440.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4591	4591	4591	4591	4591	
5°	4591	4570	4516	4554	4541	435
15°	4367	4321	4180	4101	4060	1231
25°	3964	3831	3556	3386	3324	1823
35°	3416	3203	2838	2576	2484	2138
45°	2792	2514	2078	1782	1683	2156
55°	2123	1799	1350	1101	1022	1897
65°	1434	1097	723	582	569	1421
75°	764	473	332	303	299	808
85°	178	91	79	79	79	205
90°	2	21	34	43	47	15
95°	112	55	67	76	74	133
105°	525	577	105	124	131	561
115°	993	1022	1065	266	142	977
125°	1403	1426	1459	1471	1476	1252
135°	1737	1764	1780	1797	1794	1342
145°	2015	2013	2042	2054	2046	1260
155°	2218	2203	2224	2234	2220	1022
165°	2337	2327	2332	2344	2332	660
175°	2391	2379	2382	2394	2377	228
180°	2386	2386	2386	2386	2386	

TEST NUMBER: P908867

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4591.2	4591.2	4591.2	4591.2	4591.2
2.5°	4611.9	4591.2	4545.3	4587.2	4578.8
5°	4591.2	4570.4	4516.2	4553.7	4541.4
7.5°	4553.7	4528.9	4470.8	4487.1	4466.3
10°	4503.9	4474.7	4391.9	4379.1	4354.4
12.5°	4441.7	4404.2	4291.8	4267.1	4221.2
15°	4366.8	4320.9	4179.8	4101.0	4059.5
17.5°	4279.5	4213.0	4038.4	3947.1	3880.5
20°	4179.8	4096.5	3888.9	3785.3	3693.6
22.5°	4071.9	3976.1	3735.1	3594.0	3531.8
25°	3963.8	3830.7	3556.5	3386.4	3323.8
27.5°	3835.2	3693.6	3390.3	3195.0	3099.4
30°	3698.0	3539.8	3207.4	2995.8	2883.4
32.5°	3564.9	3373.6	3033.2	2783.8	2679.8
35°	3415.5	3203.4	2838.0	2576.2	2484.5
37.5°	3270.0	3041.2	2655.0	2368.0	2264.5
40°	3116.1	2867.1	2463.8	2168.8	2060.8
42.5°	2958.3	2692.5	2272.9	1965.2	1861.6
45°	2792.2	2513.6	2077.6	1782.2	1682.6
47.5°	2634.3	2339.5	1890.7	1595.3	1504.1
50°	2459.7	2164.8	1707.8	1420.8	1333.9
52.5°	2289.2	1977.5	1533.2	1259.0	1180.0
55°	2122.9	1799.0	1350.2	1101.2	1022.3
57.5°	1952.9	1620.4	1188.4	955.7	889.1
60°	1778.3	1445.9	1017.8	806.3	739.7
62.5°	1608.1	1275.8	872.4	673.2	640.1
65°	1433.5	1096.7	723.0	581.9	569.1
67.5°	1267.4	930.6	581.9	510.9	498.6
70°	1092.8	768.8	481.8	440.4	423.6
72.5°	926.6	618.9	402.9	369.8	361.4
75°	764.4	473.4	332.3	303.3	299.3
77.5°	602.6	336.4	261.9	245.1	236.7
80°	452.7	241.2	199.2	183.0	183.0
82.5°	315.6	162.2	137.1	128.8	128.8
85°	178.5	91.3	78.9	78.9	78.9
87.5°	66.6	33.0	33.0	29.1	29.1
90°	1.6	20.7	34.4	43.2	46.6
92.5°	43.2	36.3	41.4	44.9	46.6
95°	112.1	55.1	67.3	76.0	74.2
97.5°	201.9	60.5	88.0	93.3	94.9
100°	305.7	69.1	98.4	112.1	115.6
102.5°	419.4	416.2	101.9	120.8	126.0
105°	524.8	576.6	105.3	124.2	131.2
107.5°	647.3	690.4	108.9	127.7	134.7
110°	764.9	800.9	302.2	129.6	136.3

TEST NUMBER: P908867

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.4	906.3	877.0	132.8	138.1
115°	992.6	1021.9	1065.1	265.9	141.7
117.5°	1094.5	1128.9	1158.4	911.4	459.2
120°	1208.4	1234.3	1265.5	1286.2	1053.1
122.5°	1304.9	1332.6	1367.4	1377.6	1379.4
125°	1403.4	1425.9	1458.8	1470.9	1475.9
127.5°	1493.2	1517.3	1543.4	1560.6	1562.3
130°	1577.8	1605.5	1624.4	1643.5	1641.8
132.5°	1664.2	1686.7	1705.6	1721.1	1719.5
135°	1736.7	1764.3	1779.8	1797.2	1793.7
137.5°	1812.5	1833.3	1850.7	1867.9	1862.8
140°	1886.7	1900.7	1919.6	1935.1	1926.5
142.5°	1949.0	1961.2	1983.5	1997.2	1988.6
145°	2014.7	2012.9	2042.2	2054.3	2045.7
147.5°	2071.4	2066.4	2095.7	2104.3	2097.5
150°	2126.8	2114.8	2142.4	2152.6	2144.0
152.5°	2173.3	2159.6	2185.5	2195.9	2183.8
155°	2218.3	2202.8	2223.5	2233.8	2220.1
157.5°	2254.5	2240.8	2256.3	2268.5	2254.5
160°	2285.7	2275.2	2285.7	2295.9	2283.8
162.5°	2313.2	2302.9	2311.5	2323.6	2308.0
165°	2337.3	2327.1	2332.2	2344.3	2332.2
167.5°	2356.4	2345.9	2351.3	2363.4	2347.8
170°	2372.0	2361.6	2365.0	2377.1	2361.6
172.5°	2382.3	2372.0	2375.5	2387.5	2372.0
175°	2390.9	2378.7	2382.3	2394.3	2377.1
177.5°	2394.3	2382.3	2384.1	2396.2	2380.6
180°	2385.7	2385.7	2385.7	2385.7	2385.7

TEST NUMBER: P908867

CATALOG NUMBER: DFN2DIP-PN4F0-110D070US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.02	12.92	12.92	13.83	15.00	7.99	8.89	8.89	9.80	10.96
	3H	13.71	14.51	14.62	15.43	16.62	9.18	9.98	10.09	10.91	12.10
	4H	14.32	15.08	15.25	16.01	17.21	9.64	10.39	10.56	11.32	12.52
	6H	14.75	15.45	15.69	16.38	17.59	9.96	10.66	10.90	11.59	12.80
	8H	14.88	15.54	15.82	16.49	17.70	10.06	10.72	11.00	11.67	12.88
	12H	14.95	15.58	15.89	16.52	17.75	10.10	10.73	11.05	11.68	12.91
4H	2H	12.05	12.81	12.98	13.73	14.93	8.60	9.35	9.53	10.28	11.48
	3H	13.89	14.52	14.83	15.48	16.69	9.95	10.58	10.89	11.54	12.75
	4H	14.59	15.16	15.54	16.11	17.35	10.50	11.08	11.45	12.03	13.27
	6H	15.11	15.60	16.07	16.58	17.81	10.93	11.42	11.89	12.40	13.63
	8H	15.29	15.75	16.25	16.72	17.97	11.06	11.52	12.02	12.49	13.74
	12H	15.39	15.80	16.37	16.79	18.04	11.13	11.54	12.11	12.53	13.78
8H	4H	14.56	15.02	15.52	15.99	17.24	10.79	11.25	11.76	12.22	13.47
	6H	15.13	15.51	16.12	16.52	17.77	11.31	11.69	12.30	12.70	13.95
	8H	15.35	15.68	16.35	16.69	17.95	11.50	11.84	12.50	12.84	14.11
	12H	15.49	15.79	16.50	16.78	18.10	11.63	11.92	12.63	12.92	14.23
12H	4H	14.51	14.93	15.50	15.92	17.17	10.80	11.21	11.78	12.20	13.46
	6H	15.11	15.44	16.11	16.44	17.71	11.36	11.70	12.36	12.70	13.97
	8H	15.33	15.63	16.33	16.62	17.94	11.58	11.87	12.58	12.87	14.18

END OF REPORT