

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908883

Luminaire Tested: DFN2DIP-PN4F0-110D110US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908883
REPORT IS A COMBINATION OF REPORTS P901270 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-110D110US840-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20439.6 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 205.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908883

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908883

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3351	3351	3351
5°	3357	3299	3320
10°	3323	3234	3212
15°	3278	3128	3046
20°	3217	2981	2842
25°	3155	2816	2644
30°	3072	2647	2393
35°	2990	2465	2173
40°	2907	2277	1921
45°	2811	2069	1692
50°	2711	1858	1468
55°	2607	1632	1253
60°	2487	1397	1032
65°	2348	1157	930
70°	2180	934	842
75°	1969	824	768
80°	1663	693	668
85°	1159	465	506

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2811 cd/sqm

TEST NUMBER: P908883

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.3	2.1
10°-20°	1181.2	5.8
20°-30°	1658.4	8.1
30°-40°	1807.8	8.8
40°-50°	1661.5	8.1
50°-60°	1304.9	6.4
60°-70°	849.4	4.2
70°-80°	437.2	2.1
80°-90°	118.2	0.6
90°-100°	123.6	0.6
100°-110°	460.8	2.3
110°-120°	1222.2	6.0
120°-130°	2027.1	9.9
130°-140°	2153.3	10.5
140°-150°	2001.2	9.8
150°-160°	1608.9	7.9
160°-170°	1036.7	5.1
170°-180°	356.8	1.7
0°-30°	3269.9	16.0
0°-40°	5077.7	24.8
0°-60°	8044.1	39.4
0°-90°	9448.8	46.2
90°-120°	1806.7	8.8
90°-150°	7988.3	39.1
90°-180°	10991.0	53.8
0°-180°	20439.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4591	4591	4591	4591	4591	
5°	4591	4570	4516	4554	4541	435
15°	4367	4321	4180	4101	4060	1231
25°	3964	3831	3556	3386	3324	1823
35°	3416	3203	2838	2576	2484	2138
45°	2792	2514	2078	1782	1683	2156
55°	2123	1799	1350	1101	1022	1897
65°	1434	1097	723	582	569	1421
75°	764	473	332	303	299	808
85°	178	91	79	79	79	205
90°	3	32	54	68	73	19
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1536
125°	2205	2241	2292	2311	2319	1967
135°	2729	2773	2797	2824	2819	2108
145°	3166	3163	3209	3228	3215	1980
155°	3486	3462	3494	3510	3489	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3744	3763	3736	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P908883

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4591.2	4591.2	4591.2	4591.2	4591.2
2.5°	4611.9	4591.2	4545.3	4587.2	4578.8
5°	4591.2	4570.4	4516.2	4553.7	4541.4
7.5°	4553.7	4528.9	4470.8	4487.1	4466.3
10°	4503.9	4474.7	4391.9	4379.1	4354.4
12.5°	4441.7	4404.2	4291.8	4267.1	4221.2
15°	4366.8	4320.9	4179.8	4101.0	4059.5
17.5°	4279.5	4213.0	4038.4	3947.1	3880.5
20°	4179.8	4096.5	3888.9	3785.3	3693.6
22.5°	4071.9	3976.1	3735.1	3594.0	3531.8
25°	3963.8	3830.7	3556.5	3386.4	3323.8
27.5°	3835.2	3693.6	3390.3	3195.0	3099.4
30°	3698.0	3539.8	3207.4	2995.8	2883.4
32.5°	3564.9	3373.6	3033.2	2783.8	2679.8
35°	3415.5	3203.4	2838.0	2576.2	2484.5
37.5°	3270.0	3041.2	2655.0	2368.0	2264.5
40°	3116.1	2867.1	2463.8	2168.8	2060.8
42.5°	2958.3	2692.5	2272.9	1965.2	1861.6
45°	2792.2	2513.6	2077.6	1782.2	1682.6
47.5°	2634.3	2339.5	1890.7	1595.3	1504.1
50°	2459.7	2164.8	1707.8	1420.8	1333.9
52.5°	2289.2	1977.5	1533.2	1259.0	1180.0
55°	2122.9	1799.0	1350.2	1101.2	1022.3
57.5°	1952.9	1620.4	1188.4	955.7	889.1
60°	1778.3	1445.9	1017.8	806.3	739.7
62.5°	1608.1	1275.8	872.4	673.2	640.1
65°	1433.5	1096.7	723.0	581.9	569.1
67.5°	1267.4	930.6	581.9	510.9	498.6
70°	1092.8	768.8	481.8	440.4	423.6
72.5°	926.6	618.9	402.9	369.8	361.4
75°	764.4	473.4	332.3	303.3	299.3
77.5°	602.6	336.4	261.9	245.1	236.7
80°	452.7	241.2	199.2	183.0	183.0
82.5°	315.6	162.2	137.1	128.8	128.8
85°	178.5	91.3	78.9	78.9	78.9
87.5°	66.6	33.0	33.0	29.1	29.1
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.2
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.9	160.1	189.8	198.1
105°	824.7	906.2	165.6	195.2	206.2
107.5°	1017.3	1084.9	171.1	200.7	211.7
110°	1201.8	1258.6	474.8	203.6	214.2

TEST NUMBER: P908883

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.5	1424.1	1378.1	208.7	217.1
115°	1559.7	1605.8	1673.9	417.8	222.6
117.5°	1719.9	1774.0	1820.4	1432.2	721.5
120°	1899.0	1939.5	1988.5	2021.0	1654.8
122.5°	2050.7	2094.2	2148.6	2164.7	2167.7
125°	2205.3	2240.8	2292.3	2311.3	2319.4
127.5°	2346.4	2384.4	2425.3	2452.4	2455.0
130°	2479.4	2522.9	2552.5	2582.5	2580.0
132.5°	2615.0	2650.5	2680.2	2704.6	2702.1
135°	2729.2	2772.6	2796.7	2824.2	2818.6
137.5°	2848.3	2880.8	2908.2	2935.3	2927.2
140°	2965.0	2986.8	3016.5	3040.9	3027.4
142.5°	3062.8	3081.8	3116.9	3138.6	3125.0
145°	3165.9	3163.0	3209.0	3228.1	3214.6
147.5°	3255.2	3247.1	3293.2	3306.7	3296.1
150°	3342.2	3323.2	3366.6	3382.7	3369.2
152.5°	3415.3	3393.7	3434.2	3450.7	3431.7
155°	3485.9	3461.6	3494.1	3510.3	3488.7
157.5°	3542.8	3521.2	3545.7	3564.7	3542.8
160°	3591.8	3575.3	3591.8	3607.8	3588.9
162.5°	3634.9	3618.9	3632.4	3651.4	3626.9
165°	3673.0	3656.8	3664.9	3683.9	3664.9
167.5°	3702.9	3686.5	3694.9	3713.9	3689.4
170°	3727.4	3711.0	3716.4	3735.5	3711.0
172.5°	3743.5	3727.4	3732.9	3751.9	3727.4
175°	3757.0	3738.0	3743.5	3762.6	3735.5
177.5°	3762.6	3743.5	3746.4	3765.4	3740.9
180°	3749.0	3749.0	3749.0	3749.0	3749.0

TEST NUMBER: P908883

CATALOG NUMBER: DFN2DIP-PN4F0-110D110US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.99	11.79	11.99	12.80	14.12	6.96	7.76	7.95	8.76	10.09
	3H	12.67	13.39	13.68	14.40	15.75	8.14	8.86	9.15	9.87	11.22
	4H	13.28	13.96	14.30	14.97	16.33	8.59	9.27	9.61	10.29	11.64
	6H	13.70	14.33	14.73	15.34	16.71	8.91	9.54	9.94	10.56	11.92
	8H	13.83	14.42	14.86	15.46	16.82	9.00	9.60	10.04	10.63	12.00
	12H	13.89	14.45	14.93	15.48	16.87	9.05	9.61	10.09	10.64	12.03
4H	2H	11.01	11.68	12.03	12.70	14.05	7.55	8.23	8.58	9.24	10.60
	3H	12.84	13.40	13.87	14.44	15.81	8.90	9.46	9.93	10.51	11.87
	4H	13.53	14.04	14.57	15.08	16.47	9.45	9.96	10.49	11.00	12.39
	6H	14.05	14.49	15.10	15.55	16.93	9.87	10.31	10.92	11.37	12.75
	8H	14.22	14.64	15.27	15.69	17.09	9.99	10.41	11.05	11.46	12.86
	12H	14.32	14.69	15.39	15.76	17.16	10.06	10.43	11.13	11.50	12.90
8H	4H	13.50	13.91	14.55	14.96	16.36	9.73	10.14	10.78	11.19	12.59
	6H	14.06	14.40	15.14	15.50	16.90	10.25	10.59	11.32	11.68	13.08
	8H	14.28	14.58	15.36	15.66	17.08	10.44	10.74	11.52	11.81	13.23
	12H	14.42	14.69	15.51	15.76	17.22	10.56	10.82	11.64	11.89	13.35
12H	4H	13.45	13.82	14.52	14.88	16.29	9.73	10.10	10.80	11.17	12.58
	6H	14.04	14.34	15.12	15.42	16.83	10.30	10.59	11.38	11.67	13.09
	8H	14.26	14.52	15.35	15.60	17.06	10.51	10.77	11.59	11.84	13.30