

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922095

Luminaire Tested: DFN2DIP-PN3F0-040D080US940-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P922095  
REPORT IS A COMBINATION OF REPORTS P901104 AND P897955  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN3F0-040D080US940-RLONL  
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10094.2 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 96.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9972  
Total Harmonic Distortion (THDi): 0.128  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P922095  
CATALOG NUMBER: DFN2DIP-PN3F0-040D080US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P922095

CATALOG NUMBER: DFN2DIP-PN3F0-040D080US940-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	18	16	15	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11	14	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1723	1723	1723
5°	1725	1695	1706
10°	1707	1660	1650
15°	1682	1604	1563
20°	1650	1527	1457
25°	1617	1442	1355
30°	1574	1354	1226
35°	1531	1259	1112
40°	1487	1162	982
45°	1436	1054	864
50°	1383	945	749
55°	1328	828	638
60°	1265	707	525
65°	1191	584	471
70°	1102	469	425
75°	990	410	385
80°	827	340	332
85°	562	221	245

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1626 cd/sqm



TEST NUMBER: P922095

CATALOG NUMBER: DFN2DIP-PN3F0-040D080US940-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.2	1.4
10°-20°	379.3	3.8
20°-30°	532.5	5.3
30°-40°	580.5	5.8
40°-50°	533.5	5.3
50°-60°	419.0	4.2
60°-70°	272.7	2.7
70°-80°	140.4	1.4
80°-90°	40.1	0.4
90°-100°	79.4	0.8
100°-110°	295.9	2.9
110°-120°	784.9	7.8
120°-130°	1301.8	12.9
130°-140°	1382.8	13.7
140°-150°	1285.1	12.7
150°-160°	1033.2	10.2
160°-170°	665.8	6.6
170°-180°	229.2	2.3
0°-30°	1049.9	10.4
0°-40°	1630.4	16.2
0°-60°	2582.9	25.6
0°-90°	3036.1	30.1
90°-120°	1160.2	11.5
90°-150°	5129.9	50.8
90°-180°	7058.0	69.9
0°-180°	10094.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	2	21	35	44	47	9
95°	113	56	68	77	75	134
105°	530	582	106	125	132	566
115°	1002	1031	1075	268	143	986
125°	1416	1439	1472	1484	1489	1263
135°	1753	1780	1796	1814	1810	1354
145°	2033	2031	2061	2073	2064	1272
155°	2238	2223	2244	2254	2240	1032
165°	2359	2348	2354	2366	2354	666
175°	2413	2400	2404	2416	2399	230
180°	2408	2408	2408	2408	2408	



TEST NUMBER: P922095

CATALOG NUMBER: DFN2DIP-PN3F0-040D080US940-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	1.7	20.9	34.8	43.6	47.0
92.5°	43.6	36.6	41.8	45.3	47.0
95°	113.2	55.6	67.9	76.8	74.9
97.5°	203.8	61.0	88.7	94.2	95.8
100°	308.4	69.7	99.3	113.2	116.6
102.5°	423.3	419.9	102.8	121.8	127.2
105°	529.6	581.9	106.3	125.4	132.4
107.5°	653.3	696.7	109.9	128.9	135.9
110°	771.9	808.2	305.0	130.7	137.6



TEST NUMBER: P922095

CATALOG NUMBER: DFN2DIP-PN3F0-040D080US940-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	883.3	914.5	885.0	134.0	139.5
115°	1001.7	1031.3	1074.9	268.3	142.9
117.5°	1104.5	1139.2	1169.0	919.7	463.4
120°	1219.5	1245.5	1277.0	1297.9	1062.7
122.5°	1316.9	1344.9	1379.8	1390.2	1392.0
125°	1416.2	1439.0	1472.0	1484.3	1489.4
127.5°	1506.8	1531.2	1557.6	1574.8	1576.5
130°	1592.2	1620.1	1639.2	1658.5	1656.8
132.5°	1679.4	1702.1	1721.2	1736.9	1735.2
135°	1752.6	1780.5	1796.0	1813.6	1810.1
137.5°	1829.2	1850.0	1867.6	1885.0	1879.8
140°	1904.0	1918.1	1937.2	1952.8	1944.1
142.5°	1966.9	1979.1	2001.6	2015.5	2006.8
145°	2033.1	2031.2	2060.8	2073.0	2064.3
147.5°	2090.4	2085.3	2114.8	2123.5	2116.7
150°	2146.3	2134.0	2162.0	2172.3	2163.6
152.5°	2193.3	2179.3	2205.4	2216.0	2203.8
155°	2238.5	2223.0	2243.9	2254.2	2240.4
157.5°	2275.1	2261.3	2277.0	2289.2	2275.1
160°	2306.6	2296.1	2306.6	2316.9	2304.7
162.5°	2334.3	2324.0	2332.6	2344.8	2329.1
165°	2358.8	2348.4	2353.6	2365.7	2353.6
167.5°	2377.9	2367.4	2372.8	2385.0	2369.3
170°	2393.7	2383.1	2386.7	2398.9	2383.1
172.5°	2404.1	2393.7	2397.2	2409.4	2393.7
175°	2412.7	2400.5	2404.1	2416.2	2398.9
177.5°	2416.2	2404.1	2405.8	2418.1	2402.4
180°	2407.5	2407.5	2407.5	2407.5	2407.5



TEST NUMBER: P922095  
 CATALOG NUMBER: DFN2DIP-PN3F0-040D080US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.78	7.47	7.89	8.58	10.11	2.74	3.43	3.86	4.54	6.07
	3H	8.44	9.06	9.56	10.17	11.72	3.92	4.53	5.04	5.65	7.20
	4H	9.04	9.62	10.17	10.74	12.29	4.35	4.94	5.49	6.06	7.61
	6H	9.45	9.98	10.59	11.10	12.67	4.66	5.20	5.81	6.32	7.89
	8H	9.57	10.08	10.71	11.21	12.77	4.75	5.26	5.89	6.39	7.95
	12H	9.62	10.11	10.77	11.23	12.81	4.78	5.27	5.93	6.40	7.98
4H	2H	6.78	7.36	7.92	8.48	10.03	3.32	3.90	4.46	5.02	6.57
	3H	8.59	9.07	9.73	10.22	11.78	4.65	5.14	5.80	6.28	7.84
	4H	9.27	9.72	10.42	10.85	12.43	5.19	5.63	6.34	6.77	8.35
	6H	9.77	10.15	10.93	11.31	12.88	5.59	5.97	6.75	7.13	8.71
	8H	9.94	10.30	11.09	11.44	13.04	5.71	6.07	6.87	7.22	8.81
	12H	10.02	10.35	11.19	11.51	13.10	5.77	6.09	6.94	7.25	8.85
8H	4H	9.22	9.58	10.38	10.73	12.32	5.45	5.81	6.61	6.96	8.55
	6H	9.78	10.07	10.95	11.26	12.85	5.96	6.25	7.13	7.44	9.03
	8H	9.99	10.25	11.17	11.41	13.02	6.14	6.40	7.32	7.57	9.18
	12H	10.12	10.34	11.30	11.51	13.15	6.25	6.48	7.43	7.64	9.28
12H	4H	9.17	9.49	10.34	10.65	12.25	5.45	5.77	6.62	6.93	8.53
	6H	9.75	10.01	10.93	11.18	12.79	6.01	6.26	7.19	7.43	9.04
	8H	9.96	10.19	11.15	11.35	13.00	6.20	6.43	7.39	7.59	9.24