

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911334

Luminaire Tested: DFN2DIP-PN4F0-040D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911334
REPORT IS A COMBINATION OF REPORTS P899628 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-040D050US850-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8677.9 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 71
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911334
CATALOG NUMBER: DFN2DIP-PN4F0-040D050US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P911334

CATALOG NUMBER: DFN2DIP-PN4F0-040D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44			44
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37			37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32			32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24			24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21			21
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22	19			19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17			17
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15			15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14			14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1338	1338	1338
5°	1340	1317	1326
10°	1327	1292	1283
15°	1309	1249	1216
20°	1285	1190	1135
25°	1260	1125	1056
30°	1227	1057	956
35°	1194	985	868
40°	1161	909	767
45°	1123	826	676
50°	1083	742	586
55°	1041	652	500
60°	993	558	412
65°	938	462	371
70°	871	373	336
75°	786	329	307
80°	664	276	267
85°	463	186	202

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1372 cd/sqm



TEST NUMBER: P911334

CATALOG NUMBER: DFN2DIP-PN4F0-040D050US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.8	2.0
10°-20°	471.7	5.4
20°-30°	662.3	7.6
30°-40°	721.9	8.3
40°-50°	663.5	7.6
50°-60°	521.1	6.0
60°-70°	339.2	3.9
70°-80°	174.6	2.0
80°-90°	49.6	0.6
90°-100°	108.5	1.3
100°-110°	344.8	4.0
110°-120°	590.1	6.8
120°-130°	776.0	8.9
130°-140°	871.0	10.0
140°-150°	854.2	9.8
150°-160°	716.5	8.3
160°-170°	475.2	5.5
170°-180°	166.1	1.9
0°-30°	1305.8	15.0
0°-40°	2027.7	23.4
0°-60°	3212.2	37.0
0°-90°	3775.6	43.5
90°-120°	1043.4	12.0
90°-150°	3544.6	40.8
90°-180°	4902.0	56.5
0°-180°	8677.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1825	1804	1818	1814	174
15°	1744	1726	1669	1638	1621	491
25°	1583	1530	1420	1352	1327	728
35°	1364	1279	1133	1029	992	854
45°	1115	1004	830	712	672	861
55°	848	718	539	440	408	758
65°	572	438	289	232	227	568
75°	305	189	133	121	120	323
85°	71	36	32	32	32	82
90°	2	19	52	49	50	9
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P911334

CATALOG NUMBER: DFN2DIP-PN4F0-040D050US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1833.4	1833.4	1833.4	1833.4	1833.4
2.5°	1841.7	1833.4	1815.1	1831.8	1828.4
5°	1833.4	1825.1	1803.5	1818.4	1813.5
7.5°	1818.4	1808.6	1785.4	1791.8	1783.6
10°	1798.6	1786.9	1753.8	1748.7	1738.9
12.5°	1773.7	1758.8	1713.8	1704.0	1685.7
15°	1743.8	1725.5	1669.2	1637.7	1621.1
17.5°	1709.0	1682.4	1612.6	1576.2	1549.6
20°	1669.2	1635.9	1552.9	1511.6	1475.0
22.5°	1626.0	1587.9	1491.5	1435.2	1410.4
25°	1582.9	1529.8	1420.2	1352.3	1327.3
27.5°	1531.5	1475.0	1353.9	1275.9	1237.6
30°	1476.7	1413.5	1280.8	1196.3	1151.5
32.5°	1423.6	1347.2	1211.2	1111.7	1070.1
35°	1364.0	1279.2	1133.3	1028.7	992.1
37.5°	1305.8	1214.5	1060.2	945.6	904.3
40°	1244.4	1144.9	983.9	866.1	823.0
42.5°	1181.3	1075.2	907.6	784.7	743.4
45°	1115.0	1003.8	829.6	711.8	671.9
47.5°	1052.0	934.2	755.0	637.1	600.6
50°	982.2	864.5	681.9	567.4	532.7
52.5°	914.1	789.7	612.3	502.7	471.2
55°	847.8	718.4	539.2	439.7	408.2
57.5°	779.8	647.1	474.5	381.6	355.1
60°	710.1	577.3	406.4	321.9	295.4
62.5°	642.2	509.5	348.3	268.8	255.6
65°	572.5	437.9	288.7	232.3	227.2
67.5°	506.1	371.6	232.3	204.1	199.1
70°	436.4	307.0	192.4	175.9	169.1
72.5°	370.1	247.2	160.9	147.7	144.4
75°	305.2	189.1	132.7	121.1	119.6
77.5°	240.7	134.3	104.6	97.9	94.5
80°	180.8	96.3	79.5	73.1	73.1
82.5°	126.1	64.8	54.8	51.3	51.3
85°	71.3	36.5	31.5	31.5	31.5
87.5°	26.6	13.2	13.2	11.6	11.6
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P911334

CATALOG NUMBER: DFN2DIP-PN4F0-040D050US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P911334
 CATALOG NUMBER: DFN2DIP-PN4F0-040D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.53	8.31	8.54	9.33	10.69	3.49	4.27	4.51	5.29	6.66
	3H	9.20	9.90	10.23	10.93	12.32	4.68	5.37	5.70	6.41	7.79
	4H	9.81	10.47	10.85	11.50	12.90	5.13	5.79	6.17	6.82	8.21
	6H	10.23	10.84	11.28	11.88	13.28	5.45	6.05	6.49	7.09	8.49
	8H	10.36	10.94	11.41	11.99	13.39	5.53	6.11	6.59	7.17	8.56
	12H	10.42	10.97	11.48	12.02	13.44	5.58	6.13	6.64	7.17	8.59
4H	2H	7.54	8.20	8.58	9.23	10.62	4.08	4.74	5.13	5.78	7.17
	3H	9.37	9.92	10.42	10.98	12.38	5.43	5.98	6.48	7.04	8.44
	4H	10.06	10.56	11.12	11.61	13.04	5.98	6.48	7.04	7.53	8.96
	6H	10.57	11.01	11.64	12.08	13.50	6.39	6.82	7.46	7.90	9.32
	8H	10.75	11.15	11.82	12.22	13.66	6.52	6.92	7.59	7.99	9.43
	12H	10.84	11.21	11.93	12.29	13.73	6.58	6.95	7.67	8.03	9.47
8H	4H	10.02	10.43	11.09	11.49	12.93	6.25	6.66	7.32	7.72	9.16
	6H	10.59	10.92	11.68	12.03	13.47	6.77	7.10	7.86	8.21	9.65
	8H	10.81	11.10	11.91	12.19	13.65	6.96	7.25	8.06	8.35	9.80
	12H	10.95	11.20	12.05	12.29	13.79	7.08	7.34	8.18	8.43	9.92
12H	4H	9.97	10.34	11.06	11.42	12.86	6.26	6.62	7.34	7.70	9.14
	6H	10.57	10.86	11.67	11.95	13.40	6.82	7.11	7.92	8.21	9.66
	8H	10.79	11.04	11.89	12.13	13.62	7.03	7.29	8.13	8.38	9.87