

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922201

Luminaire Tested: DFN2DIP-PN3F0-080D070US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922201
REPORT IS A COMBINATION OF REPORTS P901097 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D070US940-FLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13241.9 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922201
CATALOG NUMBER: DFN2DIP-PN3F0-080D070US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P922201

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59	53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	50	50	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	42	42	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	36	36	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31	31	31	31	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27	27	27	27	24
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24	24	24	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	21	21	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	19	19	19	17
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	17	17	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3245	3245	3245
5°	3248	3197	3220
10°	3220	3152	3175
15°	3171	3098	3105
20°	3105	3023	3034
25°	3039	2935	2952
30°	2957	2852	2848
35°	2880	2755	2739
40°	2784	2657	2634
45°	2689	2559	2527
50°	2585	2455	2403
55°	2476	2336	2289
60°	2352	2194	2158
65°	2217	2047	2003
70°	2045	1868	1837
75°	1808	1653	1681
80°	1521	1378	1387
85°	1072	912	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2689 cd/sqm



TEST NUMBER: P922201

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	2.0
10°-20°	735.1	5.6
20°-30°	1080.3	8.2
30°-40°	1254.7	9.5
40°-50°	1253.1	9.5
50°-60°	1092.7	8.3
60°-70°	807.7	6.1
70°-80°	457.0	3.5
80°-90°	124.3	0.9
90°-100°	69.5	0.5
100°-110°	259.0	2.0
110°-120°	686.8	5.2
120°-130°	1139.1	8.6
130°-140°	1209.9	9.1
140°-150°	1124.5	8.5
150°-160°	904.1	6.8
160°-170°	582.6	4.4
170°-180°	200.5	1.5
<hr/>		
0°-30°	2076.6	15.7
0°-40°	3331.3	25.2
0°-60°	5677.0	42.9
0°-90°	7066.1	53.4
90°-120°	1015.2	7.7
90°-150°	4488.7	33.9
90°-180°	6176.0	46.6
0°-180°	13241.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	1	18	30	38	41	12
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	



TEST NUMBER: P922201

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4



TEST NUMBER: P922201

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6



TEST NUMBER: P922201
 CATALOG NUMBER: DFN2DIP-PN3F0-080D070US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.63	12.52	12.56	13.47	14.69	11.19	12.08	12.12	13.03	14.25
	3H	13.28	14.09	14.22	15.04	16.29	12.80	13.60	13.74	14.56	15.80
	4H	13.87	14.63	14.82	15.59	16.84	13.38	14.14	14.34	15.10	16.36
	6H	14.27	14.96	15.23	15.93	17.20	13.78	14.48	14.74	15.44	16.71
	8H	14.37	15.03	15.34	16.02	17.28	13.88	14.54	14.85	15.53	16.79
	12H	14.42	15.05	15.39	16.03	17.32	13.92	14.55	14.90	15.53	16.82
4H	2H	12.09	12.85	13.05	13.81	15.06	11.74	12.50	12.70	13.46	14.71
	3H	13.95	14.58	14.92	15.57	16.84	13.55	14.18	14.52	15.17	16.44
	4H	14.66	15.24	15.64	16.22	17.52	14.25	14.82	15.22	15.81	17.10
	6H	15.17	15.67	16.16	16.68	17.97	14.75	15.25	15.74	16.25	17.55
	8H	15.32	15.79	16.31	16.79	18.09	14.89	15.36	15.89	16.36	17.66
	12H	15.39	15.81	16.40	16.83	18.14	14.95	15.37	15.97	16.39	17.70
8H	4H	14.86	15.32	15.85	16.32	17.63	14.49	14.95	15.48	15.95	17.26
	6H	15.48	15.87	16.50	16.91	18.21	15.11	15.49	16.12	16.53	17.84
	8H	15.70	16.04	16.72	17.07	18.39	15.32	15.66	16.34	16.68	18.01
	12H	15.83	16.13	16.86	17.15	18.52	15.43	15.73	16.46	16.75	18.12
12H	4H	14.84	15.26	15.85	16.28	17.59	14.48	14.90	15.49	15.92	17.23
	6H	15.51	15.85	16.54	16.88	18.20	15.15	15.49	16.17	16.51	17.84
	8H	15.75	16.05	16.78	17.07	18.44	15.38	15.68	16.41	16.70	18.07