

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911399

Luminaire Tested: DFN2DIP-PN4F0-050D120US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911399
REPORT IS A COMBINATION OF REPORTS P901276 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-050D120US850-RLLONL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17888.2 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 147.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911399

CATALOG NUMBER: DFN2DIP-PN4F0-050D120US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911399

CATALOG NUMBER: DFN2DIP-PN4F0-050D120US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		70	70	70		52	52	52		34	34	34
1	93	89	85	82		83	79	76	74		62	60	58		46	44	43		31	30	29
2	85	78	72	67		75	70	65	61		54	51	48		40	38	36		27	26	25
3	77	68	62	56		69	61	56	51		48	44	41		36	33	31		24	23	22
4	71	61	53	47		63	54	48	43		43	38	35		32	29	27		22	20	19
5	65	54	46	41		58	49	42	37		38	34	30		29	26	23		20	18	17
6	60	48	41	35		53	44	37	32		35	30	26		26	23	20		18	16	15
7	55	44	36	31		49	39	33	28		31	27	23		24	20	18		17	15	13
8	51	39	32	27		46	36	29	25		28	24	20		22	18	16		15	13	12
9	48	36	29	24		42	33	26	22		26	21	18		20	17	14		14	12	11
10	44	33	26	21		40	30	24	20		24	19	16		18	15	13		13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1673	1673	1673
5°	1676	1647	1657
10°	1659	1614	1603
15°	1636	1561	1520
20°	1606	1488	1418
25°	1575	1406	1320
30°	1533	1321	1195
35°	1493	1231	1085
40°	1451	1137	959
45°	1403	1032	844
50°	1353	927	733
55°	1302	815	626
60°	1241	697	515
65°	1172	578	464
70°	1088	466	421
75°	983	411	383
80°	830	346	333
85°	579	232	253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2395 cd/sqm

TEST NUMBER: P911399

CATALOG NUMBER: DFN2DIP-PN4F0-050D120US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	1.2
10°-20°	589.6	3.3
20°-30°	827.8	4.6
30°-40°	902.4	5.0
40°-50°	829.4	4.6
50°-60°	651.3	3.6
60°-70°	424.0	2.4
70°-80°	218.2	1.2
80°-90°	63.6	0.4
90°-100°	148.1	0.8
100°-110°	552.1	3.1
110°-120°	1464.2	8.2
120°-130°	2428.5	13.6
130°-140°	2579.6	14.4
140°-150°	2397.5	13.4
150°-160°	1927.5	10.8
160°-170°	1242.0	6.9
170°-180°	427.5	2.4
0°-30°	1632.2	9.1
0°-40°	2534.6	14.2
0°-60°	4015.3	22.4
0°-90°	4721.2	26.4
90°-120°	2164.4	12.1
90°-150°	9570.0	53.5
90°-180°	13167.0	73.6
0°-180°	17888.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2281	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	3	39	65	81	88	17
95°	211	104	126	143	140	250
105°	988	1086	198	234	247	1056
115°	1869	1924	2005	500	267	1840
125°	2642	2684	2746	2769	2779	2356
135°	3269	3322	3350	3383	3377	2526
145°	3793	3789	3844	3867	3851	2372
155°	4176	4147	4186	4205	4180	1924
165°	4400	4381	4390	4413	4390	1243
175°	4501	4478	4485	4508	4475	428
180°	4491	4491	4491	4491	4491	

TEST NUMBER: P911399

CATALOG NUMBER: DFN2DIP-PN4F0-050D120US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.7	2291.7	2291.7	2291.7	2291.7
2.5°	2302.1	2291.7	2268.9	2289.8	2285.5
5°	2291.7	2281.4	2254.4	2273.0	2266.9
7.5°	2273.0	2260.7	2231.6	2239.8	2229.4
10°	2248.2	2233.6	2192.3	2185.9	2173.5
12.5°	2217.1	2198.5	2142.4	2130.1	2107.1
15°	2179.7	2156.9	2086.5	2047.1	2026.4
17.5°	2136.2	2103.0	2015.8	1970.2	1937.0
20°	2086.5	2044.9	1941.2	1889.5	1843.7
22.5°	2032.6	1984.8	1864.5	1794.0	1763.0
25°	1978.6	1912.1	1775.3	1690.3	1659.1
27.5°	1914.4	1843.7	1692.3	1594.9	1547.2
30°	1845.9	1767.0	1601.1	1495.4	1439.3
32.5°	1779.5	1684.0	1514.1	1389.6	1337.7
35°	1704.9	1599.1	1416.6	1285.9	1240.2
37.5°	1632.2	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.8	1082.6	1028.7
42.5°	1476.7	1344.0	1134.5	980.9	929.2
45°	1393.8	1254.7	1037.0	889.6	839.8
47.5°	1314.9	1167.8	943.8	796.4	750.8
50°	1227.9	1080.6	852.5	709.2	665.8
52.5°	1142.7	987.1	765.3	628.5	589.1
55°	1059.8	898.0	673.9	549.6	510.3
57.5°	974.8	808.9	593.2	477.1	443.8
60°	887.6	721.7	508.0	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.5	547.5	360.9	290.4	284.1
67.5°	632.6	464.6	290.4	255.1	248.9
70°	545.5	383.7	240.5	219.8	211.5
72.5°	462.6	309.0	201.2	184.6	180.4
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.8	122.3	118.1
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.2	45.6	39.4	39.4	39.4
87.5°	33.3	16.5	16.5	14.5	14.5
90°	3.1	38.9	64.9	81.4	87.6
92.5°	81.4	68.3	78.0	84.5	87.6
95°	211.0	103.8	126.5	143.2	139.7
97.5°	380.2	113.9	165.6	175.6	178.7
100°	575.3	130.1	185.2	211.0	217.7
102.5°	789.6	783.4	191.7	227.3	237.3
105°	987.9	1085.6	198.4	233.9	247.0
107.5°	1218.7	1299.7	204.9	240.4	253.5
110°	1439.8	1507.8	568.8	243.9	256.6

TEST NUMBER: P911399

CATALOG NUMBER: DFN2DIP-PN4F0-050D120US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1647.9	1706.1	1651.0	250.1	260.1
115°	1868.6	1923.8	2005.2	500.5	266.7
117.5°	2060.4	2125.3	2180.8	1715.7	864.5
120°	2275.0	2323.6	2382.2	2421.3	1982.4
122.5°	2456.8	2508.9	2574.1	2593.4	2596.8
125°	2642.0	2684.4	2746.2	2769.0	2778.6
127.5°	2811.0	2856.6	2905.6	2938.0	2941.1
130°	2970.3	3022.5	3058.0	3093.9	3090.8
132.5°	3132.8	3175.3	3210.8	3240.2	3237.1
135°	3269.4	3321.6	3350.5	3383.3	3376.8
137.5°	3412.3	3451.2	3484.0	3516.4	3506.8
140°	3552.0	3578.2	3613.7	3643.1	3626.9
142.5°	3669.2	3692.1	3734.1	3760.0	3743.8
145°	3792.8	3789.3	3844.5	3867.3	3851.0
147.5°	3899.7	3890.0	3945.3	3961.5	3948.7
150°	4003.8	3981.1	4033.2	4052.5	4036.3
152.5°	4091.4	4065.6	4114.3	4133.9	4111.2
155°	4175.9	4147.0	4186.0	4205.3	4179.5
157.5°	4244.3	4218.4	4247.8	4270.5	4244.3
160°	4302.9	4283.3	4302.9	4322.2	4299.5
162.5°	4354.7	4335.4	4351.6	4374.3	4345.1
165°	4400.2	4380.9	4390.5	4413.4	4390.5
167.5°	4436.1	4416.4	4426.5	4449.2	4419.9
170°	4465.4	4445.8	4452.3	4475.0	4445.8
172.5°	4484.7	4465.4	4472.0	4494.8	4465.4
175°	4500.9	4478.1	4484.7	4507.5	4475.0
177.5°	4507.5	4484.7	4488.2	4511.0	4481.7
180°	4491.3	4491.3	4491.3	4491.3	4491.3

TEST NUMBER: P911399

CATALOG NUMBER: DFN2DIP-PN4F0-050D120US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.19	6.86	7.33	7.98	9.56	2.15	2.82	3.29	3.95	5.52
	3H	7.86	8.45	9.00	9.59	11.18	3.33	3.93	4.48	5.06	6.65
	4H	8.46	9.03	9.62	10.16	11.76	3.77	4.34	4.93	5.48	7.07
	6H	8.87	9.40	10.04	10.54	12.14	4.09	4.61	5.25	5.75	7.35
	8H	9.00	9.49	10.17	10.65	12.25	4.17	4.67	5.34	5.82	7.42
	12H	9.06	9.53	10.23	10.67	12.29	4.21	4.68	5.38	5.83	7.45
4H	2H	6.19	6.75	7.35	7.89	9.49	2.73	3.30	3.90	4.43	6.03
	3H	8.00	8.48	9.17	9.64	11.25	4.07	4.54	5.24	5.70	7.31
	4H	8.69	9.13	9.86	10.28	11.90	4.61	5.04	5.78	6.19	7.82
	6H	9.20	9.57	10.38	10.75	12.36	5.02	5.39	6.20	6.56	8.18
	8H	9.37	9.72	10.55	10.89	12.52	5.15	5.49	6.32	6.66	8.29
	12H	9.46	9.78	10.66	10.95	12.59	5.20	5.52	6.40	6.69	8.33
8H	4H	8.65	8.99	9.82	10.16	11.79	4.88	5.23	6.05	6.39	8.02
	6H	9.21	9.50	10.41	10.70	12.33	5.39	5.68	6.59	6.89	8.51
	8H	9.43	9.68	10.63	10.86	12.51	5.58	5.83	6.78	7.02	8.67
	12H	9.56	9.78	10.77	10.96	12.65	5.70	5.91	6.90	7.10	8.78
12H	4H	8.59	8.91	9.78	10.08	11.72	4.88	5.19	6.07	6.37	8.00
	6H	9.19	9.43	10.39	10.62	12.27	5.44	5.69	6.64	6.88	8.52
	8H	9.40	9.62	10.60	10.80	12.48	5.65	5.86	6.85	7.05	8.73

END OF REPORT