

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924811

Luminaire Tested: DFN2DIP-PN3F0-040D050US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924811
REPORT IS A COMBINATION OF REPORTS P901062 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-040D050US950-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7965.9 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924811

CATALOG NUMBER: DFN2DIP-PN3F0-040D050US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924811

CATALOG NUMBER: DFN2DIP-PN3F0-040D050US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	105	105	105	105		96	96	96	96		78	78	78		62	62	62		48	48	48
1	96	92	88	85		87	84	81	78		69	67	65		55	54	53		43	42	41
2	88	81	75	70		80	74	69	65		61	57	54		49	47	44		38	36	35
3	80	71	64	59		73	65	59	54		54	50	46		44	41	38		34	32	30
4	74	63	56	50		67	58	52	46		48	43	40		39	36	33		31	28	26
5	68	57	49	43		62	52	45	40		43	38	34		35	32	29		28	25	23
6	62	51	43	37		57	47	40	35		39	34	30		32	28	25		25	23	21
7	58	46	38	33		53	42	36	31		36	30	27		29	25	23		23	21	19
8	54	42	34	29		49	39	32	27		33	27	24		27	23	20		21	19	17
9	50	38	31	26		46	35	29	24		30	25	21		25	21	18		20	17	15
10	47	35	28	23		43	32	26	22		28	23	19		23	19	17		18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1844	1844	1844
5°	1846	1813	1825
10°	1826	1776	1765
15°	1800	1716	1673
20°	1766	1634	1559
25°	1730	1542	1450
30°	1683	1448	1311
35°	1638	1347	1190
40°	1591	1243	1051
45°	1536	1127	924
50°	1480	1011	801
55°	1421	886	683
60°	1353	756	561
65°	1274	624	504
70°	1179	501	455
75°	1059	439	412
80°	885	364	355
85°	601	237	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1536 cd/sqm

TEST NUMBER: P924811

CATALOG NUMBER: DFN2DIP-PN3F0-040D050US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	1.9
10°-20°	405.8	5.1
20°-30°	569.7	7.2
30°-40°	621.0	7.8
40°-50°	570.8	7.2
50°-60°	448.2	5.6
60°-70°	291.8	3.7
70°-80°	150.2	1.9
80°-90°	41.2	0.5
90°-100°	53.1	0.7
100°-110°	197.9	2.5
110°-120°	524.8	6.6
120°-130°	870.4	10.9
130°-140°	924.6	11.6
140°-150°	859.3	10.8
150°-160°	690.9	8.7
160°-170°	445.2	5.6
170°-180°	153.2	1.9
0°-30°	1123.3	14.1
0°-40°	1744.3	21.9
0°-60°	2763.3	34.7
0°-90°	3246.4	40.8
90°-120°	775.8	9.7
90°-150°	3430.2	43.1
90°-180°	4719.0	59.2
0°-180°	7965.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	1	14	23	29	31	7
95°	76	37	45	51	50	90
105°	354	389	71	84	88	378
115°	670	690	719	179	96	659
125°	947	962	984	992	996	845
135°	1172	1191	1201	1213	1210	905
145°	1359	1358	1378	1386	1380	850
155°	1497	1486	1500	1507	1498	690
165°	1577	1570	1574	1582	1574	446
175°	1613	1605	1608	1616	1604	154
180°	1610	1610	1610	1610	1610	

TEST NUMBER: P924811

CATALOG NUMBER: DFN2DIP-PN3F0-040D050US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	1.1	13.9	23.3	29.2	31.4
92.5°	29.2	24.5	28.0	30.3	31.4
95°	75.7	37.2	45.4	51.3	50.1
97.5°	136.2	40.8	59.3	63.0	64.0
100°	206.3	46.7	66.4	75.7	78.0
102.5°	283.1	280.8	68.8	81.5	85.1
105°	354.1	389.1	71.1	83.9	88.5
107.5°	436.8	465.8	73.5	86.1	90.9
110°	516.1	540.4	203.9	87.4	92.0

TEST NUMBER: P924811

CATALOG NUMBER: DFN2DIP-PN3F0-040D050US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.6	611.5	591.8	89.7	93.2
115°	669.8	689.6	718.7	179.4	95.6
117.5°	738.5	761.8	781.7	614.9	309.9
120°	815.4	832.8	853.8	867.9	710.5
122.5°	880.5	899.2	922.6	929.6	930.8
125°	946.9	962.2	984.3	992.4	996.0
127.5°	1007.5	1023.8	1041.5	1053.0	1054.2
130°	1064.7	1083.4	1096.1	1108.9	1107.9
132.5°	1123.0	1138.1	1150.8	1161.4	1160.3
135°	1171.9	1190.6	1200.9	1212.7	1210.3
137.5°	1223.0	1237.1	1248.8	1260.4	1257.0
140°	1273.1	1282.6	1295.2	1305.7	1300.0
142.5°	1315.2	1323.4	1338.5	1347.7	1341.9
145°	1359.4	1358.2	1378.0	1386.2	1380.3
147.5°	1397.8	1394.3	1414.1	1419.9	1415.4
150°	1435.1	1427.0	1445.6	1452.6	1446.7
152.5°	1466.5	1457.2	1474.7	1481.8	1473.5
155°	1496.8	1486.4	1500.4	1507.3	1498.1
157.5°	1521.2	1512.0	1522.5	1530.7	1521.2
160°	1542.3	1535.3	1542.3	1549.2	1541.1
162.5°	1560.8	1554.0	1559.7	1567.9	1557.4
165°	1577.2	1570.3	1573.7	1581.8	1573.7
167.5°	1590.0	1583.0	1586.6	1594.7	1584.2
170°	1600.5	1593.5	1595.9	1604.0	1593.5
172.5°	1607.5	1600.5	1602.9	1611.0	1600.5
175°	1613.3	1605.1	1607.5	1615.6	1604.0
177.5°	1615.6	1607.5	1608.7	1616.8	1606.3
180°	1609.8	1609.8	1609.8	1609.8	1609.8

TEST NUMBER: P924811

CATALOG NUMBER: DFN2DIP-PN3F0-040D050US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.31	9.07	9.34	10.11	11.51	4.27	5.03	5.31	6.07	7.47
	3H	9.97	10.65	11.02	11.70	13.12	5.45	6.13	6.50	7.18	8.60
	4H	10.57	11.22	11.63	12.27	13.69	5.89	6.53	6.95	7.59	9.01
	6H	10.99	11.58	12.06	12.63	14.07	6.20	6.80	7.27	7.85	9.29
	8H	11.11	11.67	12.18	12.74	14.17	6.29	6.85	7.36	7.92	9.36
	12H	11.16	11.70	12.24	12.76	14.22	6.33	6.86	7.41	7.93	9.38
4H	2H	8.31	8.96	9.38	10.01	11.43	4.85	5.50	5.92	6.55	7.98
	3H	10.13	10.66	11.20	11.74	13.18	6.19	6.73	7.27	7.81	9.24
	4H	10.81	11.30	11.89	12.37	13.83	6.73	7.22	7.81	8.29	9.75
	6H	11.32	11.74	12.41	12.83	14.29	7.14	7.56	8.23	8.65	10.11
	8H	11.49	11.88	12.58	12.97	14.44	7.26	7.66	8.35	8.74	10.21
	12H	11.58	11.93	12.68	13.03	14.51	7.32	7.68	8.43	8.78	10.25
8H	4H	10.77	11.17	11.86	12.25	13.72	7.00	7.40	8.09	8.48	9.95
	6H	11.33	11.65	12.44	12.78	14.25	7.51	7.83	8.62	8.96	10.43
	8H	11.54	11.83	12.66	12.94	14.42	7.70	7.98	8.81	9.09	10.58
	12H	11.67	11.92	12.79	13.03	14.55	7.81	8.06	8.93	9.16	10.69
12H	4H	10.72	11.08	11.83	12.18	13.65	7.00	7.36	8.11	8.46	9.93
	6H	11.31	11.59	12.42	12.70	14.19	7.56	7.84	8.68	8.95	10.44
	8H	11.52	11.77	12.64	12.87	14.40	7.76	8.01	8.88	9.11	10.64