

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911541

Luminaire Tested: DFN2DIP-PN4F0-090D120US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911541
REPORT IS A COMBINATION OF REPORTS P901283 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-090D120US850-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23056.1 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 191.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911541

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911541

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	32	52	41	34	29	35	29	25	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2835	2835	2835
5°	2839	2796	2815
10°	2816	2759	2777
15°	2775	2713	2718
20°	2719	2651	2658
25°	2663	2576	2588
30°	2594	2506	2499
35°	2528	2423	2404
40°	2446	2340	2315
45°	2365	2257	2223
50°	2276	2169	2117
55°	2183	2068	2019
60°	2078	1948	1907
65°	1964	1823	1775
70°	1818	1672	1634
75°	1616	1490	1504
80°	1373	1259	1254
85°	992	859	839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2395 cd/sqm

TEST NUMBER: P911541

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.5	1.6
10°-20°	1028.5	4.5
20°-30°	1511.4	6.6
30°-40°	1755.4	7.6
40°-50°	1753.3	7.6
50°-60°	1528.8	6.6
60°-70°	1130.1	4.9
70°-80°	639.4	2.8
80°-90°	176.7	0.8
90°-100°	148.1	0.6
100°-110°	552.1	2.4
110°-120°	1464.2	6.4
120°-130°	2428.5	10.5
130°-140°	2579.6	11.2
140°-150°	2397.5	10.4
150°-160°	1927.5	8.4
160°-170°	1242.0	5.4
170°-180°	427.5	1.9
0°-30°	2905.4	12.6
0°-40°	4660.9	20.2
0°-60°	7942.9	34.5
0°-90°	9889.1	42.9
90°-120°	2164.4	9.4
90°-150°	9570.0	41.5
90°-180°	13167.0	57.1
0°-180°	23056.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3884	3884	3884	3884	3884	
5°	3884	3869	3828	3858	3850	369
15°	3697	3675	3626	3641	3622	1041
25°	3346	3316	3253	3260	3253	1540
35°	2887	2850	2790	2767	2748	1803
45°	2349	2323	2267	2226	2211	1813
55°	1778	1755	1710	1666	1647	1589
65°	1199	1176	1139	1106	1087	1185
75°	627	620	601	579	586	670
85°	153	149	146	134	131	171
90°	3	39	65	81	88	21
95°	211	104	126	143	140	250
105°	988	1086	198	234	247	1056
115°	1869	1924	2005	500	267	1840
125°	2642	2684	2746	2769	2779	2356
135°	3269	3322	3350	3383	3377	2526
145°	3793	3789	3844	3867	3851	2372
155°	4176	4147	4186	4205	4180	1924
165°	4400	4381	4390	4413	4390	1243
175°	4501	4478	4485	4508	4475	428
180°	4491	4491	4491	4491	4491	

TEST NUMBER: P911541

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3883.6	3883.6	3883.6	3883.6	3883.6
2.5°	3906.2	3887.6	3846.5	3883.6	3876.5
5°	3883.6	3869.0	3827.8	3857.5	3850.3
7.5°	3857.5	3835.4	3794.1	3824.3	3816.7
10°	3816.7	3790.6	3745.8	3775.5	3764.4
12.5°	3760.4	3738.2	3693.5	3712.0	3704.6
15°	3697.1	3674.9	3626.1	3641.2	3622.5
17.5°	3618.6	3596.4	3547.7	3566.3	3547.7
20°	3532.6	3510.4	3458.1	3469.2	3454.5
22.5°	3447.0	3413.4	3364.6	3364.6	3357.1
25°	3346.0	3316.2	3252.9	3260.0	3252.9
27.5°	3233.8	3207.7	3159.4	3148.3	3129.7
30°	3122.2	3092.0	3036.1	3025.0	3010.0
32.5°	3002.5	2980.3	2920.4	2897.9	2882.8
35°	2886.8	2849.6	2789.7	2767.2	2748.5
37.5°	2756.1	2722.4	2662.5	2636.4	2617.8
40°	2621.7	2591.6	2531.7	2498.5	2483.5
42.5°	2490.9	2460.9	2401.4	2363.8	2341.7
45°	2349.1	2323.0	2266.7	2225.9	2210.9
47.5°	2210.9	2184.7	2124.8	2083.7	2061.5
50°	2065.1	2046.4	1994.1	1941.9	1923.2
52.5°	1923.2	1897.1	1848.7	1807.6	1781.4
55°	1777.8	1755.2	1710.4	1665.7	1647.1
57.5°	1632.0	1613.4	1564.7	1519.9	1504.8
60°	1486.2	1471.5	1419.2	1378.0	1367.0
62.5°	1344.3	1318.2	1280.9	1243.7	1228.7
65°	1198.9	1176.3	1139.1	1105.5	1086.8
67.5°	1049.6	1030.6	997.2	971.2	956.1
70°	911.3	896.2	862.6	836.4	821.8
72.5°	769.4	754.3	735.7	709.6	698.6
75°	627.3	620.0	601.1	578.9	586.4
77.5°	500.4	485.4	477.9	466.8	455.7
80°	373.6	369.6	362.1	351.0	343.6
82.5°	254.0	254.0	250.4	235.3	235.3
85°	152.9	149.4	145.8	134.3	130.8
87.5°	67.3	59.8	52.3	41.3	37.3
90°	3.1	38.9	64.9	81.4	87.6
92.5°	81.4	68.3	78.0	84.5	87.6
95°	211.0	103.8	126.5	143.2	139.7
97.5°	380.2	113.9	165.6	175.6	178.7
100°	575.3	130.1	185.2	211.0	217.7
102.5°	789.6	783.4	191.7	227.3	237.3
105°	987.9	1085.6	198.4	233.9	247.0
107.5°	1218.7	1299.7	204.9	240.4	253.5
110°	1439.8	1507.8	568.8	243.9	256.6

TEST NUMBER: P911541

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1647.9	1706.1	1651.0	250.1	260.1
115°	1868.6	1923.8	2005.2	500.5	266.7
117.5°	2060.4	2125.3	2180.8	1715.7	864.5
120°	2275.0	2323.6	2382.2	2421.3	1982.4
122.5°	2456.8	2508.9	2574.1	2593.4	2596.8
125°	2642.0	2684.4	2746.2	2769.0	2778.6
127.5°	2811.0	2856.6	2905.6	2938.0	2941.1
130°	2970.3	3022.5	3058.0	3093.9	3090.8
132.5°	3132.8	3175.3	3210.8	3240.2	3237.1
135°	3269.4	3321.6	3350.5	3383.3	3376.8
137.5°	3412.3	3451.2	3484.0	3516.4	3506.8
140°	3552.0	3578.2	3613.7	3643.1	3626.9
142.5°	3669.2	3692.1	3734.1	3760.0	3743.8
145°	3792.8	3789.3	3844.5	3867.3	3851.0
147.5°	3899.7	3890.0	3945.3	3961.5	3948.7
150°	4003.8	3981.1	4033.2	4052.5	4036.3
152.5°	4091.4	4065.6	4114.3	4133.9	4111.2
155°	4175.9	4147.0	4186.0	4205.3	4179.5
157.5°	4244.3	4218.4	4247.8	4270.5	4244.3
160°	4302.9	4283.3	4302.9	4322.2	4299.5
162.5°	4354.7	4335.4	4351.6	4374.3	4345.1
165°	4400.2	4380.9	4390.5	4413.4	4390.5
167.5°	4436.1	4416.4	4426.5	4449.2	4419.9
170°	4465.4	4445.8	4452.3	4475.0	4445.8
172.5°	4484.7	4465.4	4472.0	4494.8	4465.4
175°	4500.9	4478.1	4484.7	4507.5	4475.0
177.5°	4507.5	4484.7	4488.2	4511.0	4481.7
180°	4491.3	4491.3	4491.3	4491.3	4491.3

TEST NUMBER: P911541

CATALOG NUMBER: DFN2DIP-PN4F0-090D120US850-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.20	11.01	11.22	12.03	13.40	9.76	10.57	10.78	11.59	12.96
	3H	11.86	12.58	12.89	13.61	15.00	11.38	12.10	12.40	13.13	14.52
	4H	12.45	13.13	13.49	14.17	15.56	11.96	12.64	13.00	13.68	15.08
	6H	12.85	13.48	13.90	14.52	15.93	12.36	12.98	13.41	14.02	15.43
	8H	12.95	13.55	14.01	14.61	16.01	12.46	13.06	13.51	14.11	15.52
	12H	13.00	13.57	14.06	14.62	16.05	12.50	13.07	13.56	14.12	15.55
4H	2H	10.66	11.34	11.70	12.38	13.77	10.31	10.99	11.35	12.02	13.42
	3H	12.52	13.09	13.58	14.15	15.56	12.12	12.69	13.17	13.75	15.16
	4H	13.24	13.76	14.30	14.81	16.24	12.82	13.34	13.88	14.39	15.83
	6H	13.75	14.20	14.82	15.28	16.70	13.33	13.77	14.40	14.85	16.28
	8H	13.90	14.32	14.97	15.39	16.83	13.47	13.89	14.54	14.96	16.40
	12H	13.97	14.35	15.06	15.44	16.88	13.53	13.91	14.62	15.00	16.44
8H	4H	13.43	13.85	14.50	14.92	16.36	13.06	13.48	14.13	14.55	15.99
	6H	14.06	14.41	15.15	15.52	16.96	13.68	14.03	14.78	15.14	16.58
	8H	14.28	14.59	15.38	15.68	17.14	13.90	14.20	15.00	15.30	16.76
	12H	14.41	14.68	15.52	15.77	17.27	14.01	14.28	15.11	15.37	16.87
12H	4H	13.41	13.79	14.50	14.87	16.32	13.05	13.43	14.14	14.51	15.96
	6H	14.09	14.39	15.19	15.49	16.95	13.73	14.03	14.82	15.12	16.58
	8H	14.33	14.60	15.43	15.69	17.19	13.96	14.23	15.06	15.32	16.82