

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903174

Luminaire Tested: DFN2DIP-PN4F0-040D110US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903174
REPORT IS A COMBINATION OF REPORTS P899736 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-040D110US830-RLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12380.2 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 125
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903174

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903174

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	89	85	82	82	79	76	73	62	60	58	45	44	43	30	30	29
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	21
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15
7	55	43	36	31	49	39	33	28	31	26	23	24	20	18	16	14	13
8	51	39	32	27	46	36	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1137	1137	1137
5°	1139	1120	1127
10°	1128	1098	1090
15°	1112	1062	1034
20°	1092	1012	964
25°	1071	956	897
30°	1043	898	812
35°	1015	837	738
40°	987	773	652
45°	954	702	574
50°	920	631	498
55°	885	554	425
60°	844	474	350
65°	797	393	315
70°	740	317	286
75°	668	280	261
80°	564	235	227
85°	393	158	172

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2567 cd/sqm

TEST NUMBER: P903174

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.2
10°-20°	400.9	3.2
20°-30°	562.8	4.5
30°-40°	613.5	5.0
40°-50°	563.9	4.6
50°-60°	442.9	3.6
60°-70°	288.3	2.3
70°-80°	148.4	1.2
80°-90°	47.2	0.4
90°-100°	202.9	1.6
100°-110°	644.7	5.2
110°-120°	1103.3	8.9
120°-130°	1451.0	11.7
130°-140°	1628.6	13.2
140°-150°	1597.1	12.9
150°-160°	1339.7	10.8
160°-170°	888.5	7.2
170°-180°	310.5	2.5
0°-30°	1109.8	9.0
0°-40°	1723.3	13.9
0°-60°	2730.1	22.1
0°-90°	3213.9	26.0
90°-120°	1950.9	15.8
90°-150°	6627.6	53.5
90°-180°	9166.0	74.0
0°-180°	12380.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1546	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	721	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	3	36	97	91	94	12
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2114	2119	2116	2109	1610
145°	2529	2548	2564	2567	2556	1580
155°	2892	2899	2908	2922	2913	1331
165°	3146	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	

TEST NUMBER: P903174

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.2	1558.2	1558.2	1558.2	1558.2
2.5°	1565.3	1558.2	1542.7	1556.9	1554.0
5°	1558.2	1551.1	1532.8	1545.5	1541.3
7.5°	1545.5	1537.1	1517.4	1522.9	1515.9
10°	1528.6	1518.7	1490.5	1486.2	1477.9
12.5°	1507.5	1494.8	1456.6	1448.2	1432.7
15°	1482.1	1466.5	1418.6	1391.9	1377.8
17.5°	1452.5	1429.8	1370.6	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.7	1253.6
22.5°	1382.0	1349.5	1267.6	1219.7	1198.7
25°	1345.3	1300.1	1207.0	1149.3	1128.0
27.5°	1301.7	1253.6	1150.7	1084.4	1051.9
30°	1255.1	1201.4	1088.5	1016.7	978.6
32.5°	1209.9	1145.0	1029.4	944.8	909.5
35°	1159.2	1087.2	963.2	874.3	843.2
37.5°	1109.8	1032.2	901.1	803.7	768.5
40°	1057.6	973.1	836.2	736.1	699.5
42.5°	1004.0	913.8	771.4	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.6	482.2	452.7
52.5°	776.9	671.2	520.4	427.3	400.5
55°	720.6	610.6	458.3	373.7	346.9
57.5°	662.8	550.0	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.1	228.5	217.3
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.3	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	609.0	613.9	613.9
107.5°	721.6	733.5	733.5	735.5	721.6
110°	844.2	860.1	860.1	860.1	852.2

TEST NUMBER: P903174

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	976.7	993.4	990.5	982.6	976.7
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.4	1244.5	1236.7	1228.8
120°	1367.2	1388.9	1367.2	1367.2	1358.3
122.5°	1485.8	1513.4	1499.6	1491.7	1485.8
125°	1610.3	1635.0	1627.1	1618.3	1615.2
127.5°	1731.9	1762.6	1751.7	1739.8	1731.9
130°	1845.6	1881.2	1876.2	1870.3	1859.4
132.5°	1973.1	2000.8	2002.8	1989.0	1981.0
135°	2082.8	2113.5	2119.4	2116.5	2108.6
137.5°	2205.5	2230.1	2235.1	2233.1	2221.3
140°	2313.2	2337.9	2351.7	2351.7	2340.9
142.5°	2423.9	2448.6	2456.5	2459.5	2448.6
145°	2528.7	2548.4	2564.3	2567.2	2556.4
147.5°	2622.6	2647.3	2659.2	2664.1	2653.3
150°	2719.5	2736.3	2747.1	2756.1	2747.1
152.5°	2805.5	2822.3	2836.1	2847.0	2836.1
155°	2891.5	2899.4	2908.3	2922.2	2913.2
157.5°	2965.6	2971.6	2976.5	2996.2	2982.4
160°	3031.9	3037.8	3040.7	3057.6	3045.7
162.5°	3093.1	3093.1	3096.2	3114.9	3101.1
165°	3145.5	3142.5	3142.5	3162.3	3148.5
167.5°	3193.0	3184.1	3184.1	3203.9	3190.0
170°	3228.6	3220.7	3217.7	3237.4	3220.7
172.5°	3253.3	3245.4	3242.4	3262.2	3245.4
175°	3273.1	3265.2	3259.2	3279.0	3262.2
177.5°	3283.9	3276.0	3270.1	3286.9	3270.1
180°	3279.0	3279.0	3279.0	3279.0	3279.0

TEST NUMBER: P903174

CATALOG NUMBER: DFN2DIP-PN4F0-040D110US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.78	5.44	5.92	6.57	8.15	0.74	1.41	1.88	2.54	4.12
	3H	6.44	7.04	7.60	8.18	9.77	1.92	2.51	3.07	3.65	5.25
	4H	7.05	7.61	8.21	8.75	10.35	2.36	2.93	3.52	4.07	5.66
	6H	7.46	7.98	8.63	9.12	10.73	2.67	3.19	3.84	4.34	5.95
	8H	7.59	8.08	8.76	9.24	10.84	2.76	3.25	3.93	4.41	6.01
	12H	7.64	8.11	8.82	9.26	10.89	2.80	3.27	3.97	4.42	6.04
4H	2H	4.77	5.34	5.94	6.48	8.08	1.32	1.88	2.49	3.02	4.62
	3H	6.59	7.06	7.76	8.23	9.84	2.65	3.12	3.83	4.29	5.90
	4H	7.28	7.71	8.45	8.87	10.50	3.20	3.63	4.37	4.78	6.41
	6H	7.79	8.16	8.97	9.33	10.95	3.61	3.98	4.79	5.15	6.77
	8H	7.96	8.31	9.14	9.47	11.11	3.73	4.08	4.91	5.25	6.88
	12H	8.05	8.37	9.24	9.54	11.18	3.79	4.10	4.98	5.28	6.92
8H	4H	7.24	7.58	8.41	8.75	10.39	3.47	3.81	4.64	4.98	6.62
	6H	7.80	8.08	9.00	9.29	10.93	3.98	4.26	5.18	5.47	7.11
	8H	8.02	8.26	9.22	9.45	11.11	4.17	4.42	5.37	5.60	7.26
	12H	8.15	8.37	9.36	9.55	11.24	4.28	4.50	5.49	5.68	7.37
12H	4H	7.18	7.49	8.37	8.67	10.31	3.46	3.78	4.66	4.95	6.60
	6H	7.77	8.02	8.98	9.21	10.86	4.03	4.28	5.23	5.46	7.12
	8H	7.99	8.21	9.19	9.39	11.08	4.23	4.45	5.44	5.63	7.32

END OF REPORT