

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911572

Luminaire Tested: DFN2DIP-PN4F0-100D110US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911572
REPORT IS A COMBINATION OF REPORTS P899747 AND P896497
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-100D110US850-FLLFLL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 21775.2 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 192.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911572
CATALOG NUMBER: DFN2DIP-PN4F0-100D110US850-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P911572
 CATALOG NUMBER: DFN2DIP-PN4F0-100D110US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57	57	57	57	50
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48	50	49	48	42
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	35	32	30	26
5	68	57	49	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3150	3150	3150
5°	3155	3106	3128
10°	3129	3065	3086
15°	3083	3015	3020
20°	3021	2945	2953
25°	2959	2862	2875
30°	2882	2784	2776
35°	2808	2693	2671
40°	2718	2600	2572
45°	2628	2508	2470
50°	2529	2410	2352
55°	2426	2298	2244
60°	2309	2164	2119
65°	2182	2026	1973
70°	2020	1857	1815
75°	1795	1656	1671
80°	1525	1399	1394
85°	1103	955	932

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 3021 cd/sqm



TEST NUMBER: P911572

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.1	1.9
10°-20°	1142.7	5.2
20°-30°	1679.4	7.7
30°-40°	1950.5	9.0
40°-50°	1948.1	8.9
50°-60°	1698.7	7.8
60°-70°	1255.7	5.8
70°-80°	710.4	3.3
80°-90°	198.5	0.9
90°-100°	238.7	1.1
100°-110°	758.6	3.5
110°-120°	1298.1	6.0
120°-130°	1707.2	7.8
130°-140°	1916.3	8.8
140°-150°	1879.1	8.6
150°-160°	1576.3	7.2
160°-170°	1045.4	4.8
170°-180°	365.4	1.7
0°-30°	3228.3	14.8
0°-40°	5178.7	23.8
0°-60°	8825.5	40.5
0°-90°	10990.1	50.5
90°-120°	2295.4	10.5
90°-150°	7798.0	35.8
90°-180°	10785.0	49.5
0°-180°	21775.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4315	4315	4315	4315	4315	
5°	4315	4299	4253	4286	4278	410
15°	4108	4083	4029	4046	4025	1157
25°	3718	3685	3614	3622	3614	1711
35°	3208	3166	3100	3075	3054	2003
45°	2610	2581	2518	2473	2456	2014
55°	1975	1950	1900	1851	1830	1766
65°	1332	1307	1266	1228	1208	1317
75°	697	689	668	643	652	744
85°	170	166	162	149	145	190
90°	3	42	114	107	110	21
95°	170	202	208	208	202	189
105°	700	710	716	722	722	739
115°	1303	1321	1316	1312	1303	1288
125°	1895	1924	1914	1904	1900	1693
135°	2451	2487	2494	2490	2481	1894
145°	2975	2998	3017	3021	3008	1859
155°	3402	3411	3422	3438	3428	1566
165°	3701	3698	3698	3721	3704	1044
175°	3851	3842	3835	3858	3838	366
180°	3858	3858	3858	3858	3858	



TEST NUMBER: P911572

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US850-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4315.2	4315.2	4315.2	4315.2	4315.2
2.5°	4340.3	4319.6	4273.8	4315.2	4307.2
5°	4315.2	4298.9	4253.1	4286.2	4278.2
7.5°	4286.2	4261.4	4215.6	4249.1	4240.8
10°	4240.8	4211.8	4162.0	4195.0	4182.7
12.5°	4178.3	4153.6	4103.9	4124.6	4116.2
15°	4107.8	4083.2	4029.0	4045.7	4025.1
17.5°	4020.7	3996.1	3941.8	3962.6	3941.8
20°	3925.1	3900.5	3842.4	3854.7	3838.4
22.5°	3830.0	3792.7	3738.4	3738.4	3730.1
25°	3717.8	3684.8	3614.3	3622.2	3614.3
27.5°	3593.2	3564.1	3510.4	3498.1	3477.4
30°	3469.1	3435.6	3373.5	3361.2	3344.4
32.5°	3336.1	3311.5	3244.9	3219.9	3203.1
35°	3207.6	3166.2	3099.7	3074.6	3053.9
37.5°	3062.3	3024.8	2958.4	2929.3	2908.6
40°	2913.0	2879.5	2813.1	2776.2	2759.4
42.5°	2767.7	2734.2	2668.3	2626.4	2601.8
45°	2610.1	2581.1	2518.5	2473.2	2456.5
47.5°	2456.5	2427.5	2361.0	2315.1	2290.5
50°	2294.5	2273.8	2215.7	2157.6	2136.9
52.5°	2136.9	2107.9	2054.1	2008.4	1979.3
55°	1975.4	1950.3	1900.5	1850.7	1830.1
57.5°	1813.3	1792.6	1738.5	1688.8	1672.0
60°	1651.3	1635.0	1576.9	1531.1	1518.8
62.5°	1493.7	1464.7	1423.3	1381.9	1365.2
65°	1332.1	1307.1	1265.7	1228.2	1207.6
67.5°	1166.2	1145.0	1108.1	1079.1	1062.3
70°	1012.5	995.8	958.4	929.3	913.0
72.5°	854.9	838.2	817.6	788.5	776.1
75°	696.9	689.0	667.8	643.2	651.5
77.5°	556.1	539.3	530.9	518.6	506.3
80°	415.1	410.8	402.3	390.0	381.7
82.5°	282.2	282.2	278.2	261.5	261.5
85°	169.9	166.0	162.0	149.3	145.3
87.5°	74.9	66.4	58.1	45.8	41.4
90°	3.4	41.9	114.0	107.0	110.5
92.5°	72.1	97.7	101.1	104.7	104.7
95°	169.8	202.4	208.2	208.2	202.4
97.5°	282.7	312.8	325.7	325.7	325.7
100°	412.9	439.6	448.9	448.9	445.5
102.5°	550.2	569.9	582.8	586.2	582.8
105°	700.2	709.5	716.5	722.3	722.3
107.5°	849.1	863.0	863.0	865.4	849.1
110°	993.3	1012.0	1012.0	1012.0	1002.6



TEST NUMBER: P911572

CATALOG NUMBER: DFN2DIP-PN4F0-100D110US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1149.1	1168.9	1165.4	1156.1	1149.1
115°	1302.7	1321.3	1315.5	1312.1	1302.7
117.5°	1455.1	1480.6	1464.3	1455.1	1445.8
120°	1608.6	1634.2	1608.6	1608.6	1598.2
122.5°	1748.2	1780.7	1764.4	1755.1	1748.2
125°	1894.7	1923.8	1914.5	1904.0	1900.5
127.5°	2037.8	2073.8	2061.1	2047.1	2037.8
130°	2171.5	2213.5	2207.6	2200.6	2187.8
132.5°	2321.6	2354.2	2356.5	2340.2	2330.9
135°	2450.7	2486.7	2493.7	2490.3	2480.9
137.5°	2594.9	2624.0	2629.8	2627.4	2613.6
140°	2721.7	2750.8	2767.1	2767.1	2754.3
142.5°	2852.0	2881.1	2890.4	2893.8	2881.1
145°	2975.2	2998.5	3017.1	3020.6	3007.8
147.5°	3085.8	3114.8	3128.8	3134.6	3121.8
150°	3199.8	3219.5	3232.3	3242.8	3232.3
152.5°	3300.9	3320.7	3337.0	3349.8	3337.0
155°	3402.2	3411.4	3421.9	3438.2	3427.7
157.5°	3489.4	3496.3	3502.1	3525.4	3509.1
160°	3567.3	3574.3	3577.7	3597.6	3583.6
162.5°	3639.4	3639.4	3643.0	3665.0	3648.7
165°	3701.1	3697.5	3697.5	3720.8	3704.5
167.5°	3756.8	3746.4	3746.4	3769.7	3753.4
170°	3798.8	3789.5	3786.0	3809.2	3789.5
172.5°	3827.8	3818.5	3815.1	3838.4	3818.5
175°	3851.1	3841.8	3834.8	3858.1	3838.4
177.5°	3863.9	3854.6	3847.6	3867.4	3847.6
180°	3858.1	3858.1	3858.1	3858.1	3858.1



TEST NUMBER: P911572
 CATALOG NUMBER: DFN2DIP-PN4F0-100D110US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.31	12.17	12.26	13.14	14.41	10.87	11.73	11.82	12.70	13.97
	3H	12.97	13.75	13.94	14.73	16.01	12.49	13.26	13.45	14.24	15.53
	4H	13.56	14.30	14.54	15.28	16.57	13.07	13.81	14.05	14.79	16.09
	6H	13.96	14.64	14.95	15.63	16.94	13.47	14.15	14.46	15.14	16.44
	8H	14.07	14.71	15.06	15.72	17.02	13.58	14.22	14.57	15.23	16.53
	12H	14.12	14.73	15.12	15.73	17.06	13.62	14.23	14.62	15.23	16.56
4H	2H	11.77	12.50	12.75	13.49	14.78	11.42	12.15	12.40	13.14	14.43
	3H	13.64	14.25	14.63	15.26	16.57	13.24	13.85	14.23	14.86	16.17
	4H	14.36	14.92	15.36	15.92	17.25	13.94	14.50	14.94	15.50	16.84
	6H	14.87	15.36	15.89	16.38	17.71	14.45	14.93	15.46	15.96	17.29
	8H	15.03	15.48	16.04	16.50	17.84	14.60	15.05	15.61	16.07	17.41
	12H	15.10	15.51	16.13	16.54	17.89	14.66	15.07	15.69	16.10	17.45
8H	4H	14.55	15.00	15.57	16.03	17.37	14.18	14.63	15.20	15.65	17.00
	6H	15.19	15.56	16.23	16.62	17.97	14.81	15.18	15.85	16.25	17.59
	8H	15.41	15.74	16.46	16.79	18.15	15.03	15.35	16.07	16.40	17.76
	12H	15.54	15.83	16.59	16.88	18.28	15.14	15.43	16.19	16.47	17.88
12H	4H	14.54	14.95	15.57	15.98	17.33	14.18	14.58	15.21	15.62	16.97
	6H	15.22	15.55	16.26	16.60	17.96	14.85	15.18	15.90	16.23	17.59
	8H	15.46	15.75	16.51	16.79	18.20	15.09	15.38	16.14	16.42	17.83