

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P914073

Luminaire Tested: DFN2DIP-PN4F0-040D080US927-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P914073  
REPORT IS A COMBINATION OF REPORTS P901201 AND P898053  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN4F0-040D080US927-FLLONL  
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9411.1 lumens  
Efficiency: N/A  
Efficacy: 103.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 91.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P914073  
CATALOG NUMBER: DFN2DIP-PN4F0-040D080US927-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P914073

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US927-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29	24				24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20				20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17				17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15				15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13				13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12				12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10				10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9				9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	900	900	900
5°	901	888	894
10°	894	876	882
15°	881	861	863
20°	863	842	844
25°	846	818	822
30°	823	796	793
35°	802	769	763
40°	777	743	735
45°	751	716	706
50°	723	689	672
55°	693	657	641
60°	660	618	606
65°	623	579	564
70°	577	531	519
75°	513	473	478
80°	436	400	398
85°	315	273	266

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1140 cd/sqm



TEST NUMBER: P914073

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US927-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.0	1.2
10°-20°	326.5	3.5
20°-30°	479.8	5.1
30°-40°	557.3	5.9
40°-50°	556.6	5.9
50°-60°	485.3	5.2
60°-70°	358.8	3.8
70°-80°	203.0	2.2
80°-90°	57.3	0.6
90°-100°	70.5	0.7
100°-110°	262.9	2.8
110°-120°	697.3	7.4
120°-130°	1156.5	12.3
130°-140°	1228.4	13.1
140°-150°	1141.7	12.1
150°-160°	917.9	9.8
160°-170°	591.5	6.3
170°-180°	203.6	2.2
0°-30°	922.4	9.8
0°-40°	1479.7	15.7
0°-60°	2521.7	26.8
0°-90°	3140.8	33.4
90°-120°	1030.7	11.0
90°-150°	4557.3	48.4
90°-180°	6270.0	66.6
0°-180°	9411.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	2	18	31	39	42	9
95°	100	49	60	68	66	119
105°	470	517	94	111	118	503
115°	890	916	955	238	127	876
125°	1258	1278	1308	1319	1323	1122
135°	1557	1582	1596	1611	1608	1203
145°	1806	1804	1831	1842	1834	1130
155°	1989	1975	1993	2003	1990	916
165°	2096	2086	2091	2102	2091	592
175°	2143	2133	2136	2146	2131	204
180°	2139	2139	2139	2139	2139	



TEST NUMBER: P914073

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US927-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	1.5	18.5	30.9	38.7	41.7
92.5°	38.7	32.6	37.2	40.2	41.7
95°	100.5	49.4	60.3	68.2	66.5
97.5°	181.0	54.2	78.8	83.7	85.1
100°	274.0	61.9	88.2	100.5	103.6
102.5°	376.0	373.0	91.3	108.2	113.0
105°	470.5	517.0	94.4	111.4	117.6
107.5°	580.4	618.9	97.6	114.5	120.7
110°	685.7	718.0	270.9	116.1	122.2



TEST NUMBER: P914073

CATALOG NUMBER: DFN2DIP-PN4F0-040D080US927-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	784.7	812.5	786.2	119.1	123.9
115°	889.9	916.2	954.9	238.4	127.0
117.5°	981.2	1012.1	1038.5	817.1	411.7
120°	1083.4	1106.5	1134.5	1153.0	944.0
122.5°	1169.9	1194.8	1225.8	1235.0	1236.7
125°	1258.1	1278.3	1307.7	1318.6	1323.2
127.5°	1338.6	1360.3	1383.7	1399.1	1400.6
130°	1414.5	1439.3	1456.3	1473.4	1471.9
132.5°	1491.9	1512.1	1529.1	1543.0	1541.5
135°	1557.0	1581.7	1595.5	1611.2	1608.0
137.5°	1625.0	1643.5	1659.1	1674.6	1670.0
140°	1691.5	1704.0	1720.9	1734.9	1727.1
142.5°	1747.4	1758.2	1778.2	1790.6	1782.8
145°	1806.2	1804.5	1830.8	1841.7	1833.9
147.5°	1857.1	1852.5	1878.7	1886.5	1880.4
150°	1906.7	1895.8	1920.6	1929.8	1922.1
152.5°	1948.4	1936.1	1959.2	1968.6	1957.8
155°	1988.7	1974.9	1993.4	2002.6	1990.4
157.5°	2021.2	2008.9	2022.8	2033.7	2021.2
160°	2049.1	2039.8	2049.1	2058.3	2047.5
162.5°	2073.8	2064.6	2072.3	2083.1	2069.2
165°	2095.5	2086.3	2090.9	2101.7	2090.9
167.5°	2112.5	2103.2	2107.9	2118.8	2104.8
170°	2126.5	2117.1	2120.3	2131.1	2117.1
172.5°	2135.7	2126.5	2129.6	2140.5	2126.5
175°	2143.4	2132.6	2135.7	2146.5	2131.1
177.5°	2146.5	2135.7	2137.3	2148.2	2134.2
180°	2138.8	2138.8	2138.8	2138.8	2138.8



TEST NUMBER: P914073  
 CATALOG NUMBER: DFN2DIP-PN4F0-040D080US927-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.14	5.87	6.23	6.96	8.45	4.70	5.43	5.79	6.52	8.01
	3H	6.79	7.45	7.89	8.54	10.05	6.31	6.96	7.41	8.06	9.57
	4H	7.38	8.00	8.48	9.09	10.61	6.89	7.51	8.00	8.61	10.12
	6H	7.77	8.34	8.89	9.44	10.97	7.28	7.85	8.40	8.95	10.48
	8H	7.87	8.42	8.99	9.53	11.05	7.38	7.92	8.50	9.04	10.56
	12H	7.92	8.43	9.04	9.54	11.09	7.42	7.93	8.54	9.04	10.59
4H	2H	5.59	6.21	6.70	7.30	8.82	5.23	5.85	6.35	6.95	8.46
	3H	7.44	7.96	8.56	9.08	10.61	7.04	7.56	8.16	8.68	10.21
	4H	8.15	8.63	9.28	9.74	11.29	7.74	8.21	8.86	9.32	10.87
	6H	8.66	9.07	9.80	10.21	11.75	8.24	8.65	9.37	9.78	11.32
	8H	8.81	9.19	9.94	10.32	11.87	8.38	8.76	9.51	9.89	11.45
	12H	8.88	9.23	10.03	10.36	11.92	8.44	8.78	9.59	9.92	11.48
8H	4H	8.34	8.72	9.47	9.85	11.40	7.97	8.35	9.10	9.48	11.03
	6H	8.97	9.28	10.12	10.45	12.00	8.59	8.91	9.74	10.08	11.63
	8H	9.19	9.46	10.35	10.61	12.19	8.81	9.08	9.96	10.23	11.80
	12H	9.32	9.56	10.48	10.70	12.31	8.92	9.16	10.08	10.30	11.91
12H	4H	8.32	8.66	9.47	9.80	11.36	7.96	8.30	9.10	9.44	11.00
	6H	9.00	9.27	10.16	10.42	11.99	8.63	8.91	9.79	10.06	11.63
	8H	9.24	9.48	10.40	10.62	12.23	8.86	9.10	10.03	10.25	11.86